

# Data Sheet

## FUJITSU Notebook LIFEBOOK S937

### Your Stylish and Durable Business Partner

---

The FUJITSU Notebook LIFEBOOK S937 is a touch-enabled notebook for frequent travelers with highest demands. Lightweight from 1.19 kg (2.62 lbs), with a battery runtime up to 21 hours, a crystal clear 33.8 cm (13.3-inch) WQHD or FHD anti-glare display option and unique palm vein sensor option empower you to work with confidence wherever you are.

#### Flexible functionality

Choose and exchange your desired modular bay element

- Extend battery runtime up to 24 hours with a second battery option and primary battery, further options are a second hard disk drive, Blu-ray Disc™ or DVD Super Multi drive

#### Superb flexibility and mobility

Work and be online anywhere with confidence and ease

- Exceptionally lightweight starting from 1.19 kg (2.62 lbs), with a sturdy magnesium housing and aluminum palm rest, optional 4G/LTE connectivity and NFC
- Latest processor and DDR4 memory technology up to 20 GB RAM

#### Ultimate security

Protect your notebook and company data against unauthorized access

- Embedded palm vein sensor or fingerprint sensor option, integrated SmartCard reader, encrypted disk, ATP, TPM option

#### Best-in-class ergonomics

Enjoy comfortable viewing and touch panel options

- A crystal clear resolution WQHD (2560x1440) or FHD (1920 x 1080) IGZO display with anti-glare, non-touch or glare, touch option, backlit keyboard



# Components

## Operating systems

**Operating system** Windows 10 Pro. Fujitsu recommends Windows 10 Pro.

## Processor

Intel® Core™ i7-7600U processor (2.9 GHz, up to 3.9 GHz, 4 MB)

Intel® Core™ i5-7300U processor (2.6 GHz, up to 3.5 GHz, 3 MB)

Intel® Core™ i5-7200U processor (2.5 GHz, up to 3.1 GHz, 3 MB)

\*Processor only for retail, SMB, education and government

## Hard disk drives (internal)

SSD SATA III, 512 GB, M.2 module

SSD SATA III, 256 GB, M.2 module

SSD SATA III, 128 GB, M.2 module

SATA, 5,400 rpm, 500 GB, 2.5-inch, S.M.A.R.T.

SATA, 5,400 rpm, 1 TB, 2.5-inch, S.M.A.R.T.

## Hard disk notes

One Gigabyte equals one billion bytes, when referring to hard disk drive capacity.

Accessible capacity may vary, also depending on used software.

Up to 20 GB of HDD space is reserved for system recovery

Internal storage interface: S-ATA III (6GBit/s)

2nd battery

Blu-ray Disc™ Triple Writer

DVD Super Multi

Weight saver

## Interface add on cards/components (optional)

**3G/4G (optional)** LTE Sierra Wireless EM7305 (Downlink speed up to 100 Mbit/s, Uplink speed up to 50 Mbit/s)

**Display**

33.8 cm (13.3-inch), LED backlight, (WQHD), Glare IGZO touch display, magnesium, 2,560 x 1,440 pixel, 350 cd/m<sup>2</sup>

33.8 cm (13.3-inch), LED backlight, (WQHD), Anti-glare IGZO non-touch display, magnesium, 2,560 x 1,440 pixel, 350 cd/m<sup>2</sup>

33.8 cm (13.3-inch), LED backlight, (Full HD), Glare IGZO touch display, magnesium, 1,920 x 1,080 pixel, 330 cd/m<sup>2</sup>

33.8 cm (13.3-inch), LED backlight, (Full HD), Anti-glare IGZO non-touch display, magnesium, 1,920 x 1,080 pixel, 330 cd/m<sup>2</sup>

## Multimedia

**Camera** Built-in webcam, HD (Microsoft® Lync™)

# Base unit

## General system information

**Chipset** Integrated

**Supported capacity RAM (max.)** 24 GB

**Memory slots** 1 DIMM (DDR4)

**Memory notes** DDR4 - 2133 MHz

**LAN** Built-in 10/100/1,000 MBit/s Intel® I219LM

**BIOS features** InsydeH2O Bios

**Audio type** On board

**Audio codec** Realtek ALC255

**Audio features** Stereo speakers

## Display

Display notes	ISO 9241-307 - Pixel class II
---------------	-------------------------------

### Graphics

TFT resolution (HDMI)	up to 3840 x 2160 @ 30 Hz
TFT resolution (VGA)	up to 1,920 x 1,200
TFT resolution (DVI on Port Replicator)	up to 1,920 x 1,200
TFT resolution (DisplayPort on Port Replicator)	up to 4,096 x 2,160
Graphics brand name	Intel® HD Graphics 620
Graphics features	3 Display Support (2 external, 1 internal)
Graphics notes	Shared memory depending on main memory size and operating system

### Interfaces

DC-in	1
Audio: line-out / headphone	1 (combo port with Audio line-in)
Audio: line-in / microphone	1 (combo port with Audio line-out)
Internal microphones	2 (digital)
USB 3.1 Gen1 (USB 3.0) total	3 (1 with Anytime USB Charge functionality)
VGA	1
HDMI	1
Ethernet (RJ-45)	1
Memory card slots	1 (SD up to 2GB, SDHC up to 32GB, SDXC up to 128GB)
SmartCard slot	1
SIM card slot	1 (only for models with integrated 4G/LTE module)

### Port Replicator interfaces (optional)

DC-in	1 (19V)
Power on switch	1
USB 3.1 Gen1 (USB 3.0) total	4
DisplayPort	1 (up to 4096 x 2160)
VGA	1 (up to 1920 x 1200)
DVI	1 (up to 1920 x 1200)
Ethernet (RJ-45)	1 (10/100/1000)
Kensington Lock support	1x (Port rep only)
Notes	Port replicator supports 0-Watts functionality

### Keyboard and pointing devices

Backlit isolation keyboard  
 Number of keyboard keys: 85, Keyboard pitch: 19 mm, Keyboard stroke: 1.2 mm  
 Multi gesture touchpad with integrated mouse button functionality  
 EcoButton  
 Status LED

### Wireless technologies

Antennas	2 Dual band WLAN antennas, 2 UMTS/LTE antennas optional, 1 Bluetooth antenna shared with WLAN
Bluetooth	v4.2
WLAN encryption	WEP, WPA, WPA2
WLAN notes	Import and usage according to country-specific regulations.
NFC	optional
WiDi support	Yes (with Intel W-LAN)

### Power supply

Notes	65W AC Adapter for usage with system/ min. 80W AC Adapter for usage with Port Replicator
1st battery options	Li-Ion battery 4-cell, 3,550 mAh, 51 Wh Li-Ion battery 6-cell, 7,100 mAh, 77 Wh
2nd battery (optional)	Li-Ion battery 6-cell, 2,600, mAh, 28 Wh
Runtime 1st battery	up to 15 h
Runtime 1st + 2nd battery	up to 21 h

**Power supply**

<b>Battery notes</b>	Battery runtime information is based on worldwide acknowledged BAPCo® MobileMark® 2014 (office productivity). Refer to <a href="http://www.bapco.com">www.bapco.com</a> for additional details. The BAPCo® MobileMark® Benchmark provides results that enable direct product comparisons between manufacturers. It does not guarantee any specific battery runtime which actually can be lower and may vary depending on product model, configuration, application and power management settings. The battery capacity decreases slightly with every re-charge and over its lifetime.
----------------------	--

**Noise emission**

<b>Noise emission</b>	Please refer to the Eco Declaration
-----------------------	-------------------------------------

**Dimensions / Weight / Environmental**

<b>Dimensions (W x D x H)</b>	316 x 214 x 28.9 mm 12.44 x 8.43 x 1.13 inch
<b>Weight</b>	1.19 kg with non-touch display, 1.32 kg with touch display
<b>Weight (lbs)</b>	2.62 lbs with non-touch display, with touch display 2.91 lbs
<b>Weight notes</b>	Weight may vary depending on actual configuration
<b>Operating ambient temperature</b>	5 - 35 °C (41 - 95 °F)
<b>Operating relative humidity</b>	20 - 85 %

**Product**

<b>Compliance link</b>	<a href="https://sp.ts.fujitsu.com/sites/certificates">https://sp.ts.fujitsu.com/sites/certificates</a>
------------------------	---

**Additional Software****Manageability**

<b>Manageability technology</b>	DeskUpdate Driver management PXE 2.1 Boot code Wake up from S5 (off mode) Intel® vPro™ technology WoL (Wake on LAN) iAMT 11.6 (depending on processor)
<b>Manageability software</b>	DeskView Client DeskView Instant BIOS Management
<b>DeskView components</b>	Inventory Management BIOS Management Driver Management Security Management Alarm Management
<b>Supported standards</b>	WMI (Windows Management Instrumentation) PXE (Preboot Execution Environment) DMI (Desktop Management Interface) SMBIOS (System Management BIOS) WBEM (Web Based Enterprise Management) CIM (Common Information Model) BootP (made4you)
<b>Manageability link</b>	<a href="http://www.fujitsu.com/fts/manageability">http://www.fujitsu.com/fts/manageability</a>

**Security**

<b>User Security</b>	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution) Embedded fingerprint sensor (optional) Embedded palm vein sensor (optional) Smartcard reader (integrated) SystemLock 3 SmartCard Security (optional): BIOS based pre-boot/ two-factor authentication for high level of access protection
----------------------	--

**Warranty**

<b>Warranty Terms &amp; Conditions</b>	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>
--	---

**Product Support Services - the perfect extension**

**Warranty**

<b>Recommended Service</b>	9x5, Onsite Response Time: Next Business Day
<b>Service Weblink</b>	<a href="http://ts.fujitsu.com/Supportservice">http://ts.fujitsu.com/Supportservice</a>

## Recommended Accessories

<p><b>Sneaker Sleeve 14</b></p> 	<p>The Sneaker Sleeve 14 protects notebooks with up to 14-inch screens. The front half of the bag has dedicated compartments for your notebook, power cord, office supplies and personal items. The back half of the bag has an expanding, divided compartment for your files.</p>	<p>Order Code: S26361-F1650-L202</p> <p>Order Code: S26391-F1194-L401</p>
<p><b>Wireless Mouse W1200</b></p> 	<p>The Wireless Mouse W1200 uses the latest wireless 2.4 GHz technology, and a high-resolution 1000 dpi optical sensor to give you the precision and reliability you need. Sporting a compact design with a stylish black finish, the W1200 wireless mouse is well suited to all environments and to each user whether right or left handed.</p>	<p>Order Code: S26381-K462-L100</p>
<p><b>UC&amp;C USB Value Headset</b></p> 	<p>The FUJITSU UC&amp;C USB Value Headset is a lightweight bi-aural full-size stereo headset with high wearing comfort. This Lync-tested USB-Headset has an appropriate Inline-Controller which supports easy call management. A noise cancelling microphone facilitates undisturbing clear phone calls.</p>	<p>Order Code: S26391-F7139-L20</p>
<p><b>Wireless Keyboard Set LX901</b></p> 	<p>The Wireless Keyboard LX901 is a top of the line desktop solution for lifestyle orientated customers, who want only the best for their desk. This superb keyboard set offers ambitious users more functions, security and better features than a conventional interface device. It even includes 2.4 GHz technology and 128 AES encryption.</p>	<p>S26381-K565-L4** (**: Country specific variation)</p>

# More information

## Fujitsu OPTIMIZATION Services

In addition to FUJITSU Notebook LIFEBOOK S937, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

### Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

### Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

### Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about FUJITSU Notebook LIFEBOOK S937, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.  
[www.fujitsu.com/fts/mobile](http://www.fujitsu.com/fts/mobile)

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment/>



## Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH

## Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

## CONTACT

Fujitsu Technology Solutions GmbH  
Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)  
2017-03-20 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)  
© 2017 Fujitsu Technology Solutions GmbH