

Product data sheet

Specifications



Rack PDU, Metered, 2U, 30A, 120V, (16) 5-20



AP7802B

Overview

Lead time Usually in Stock

Main

Product or Component Type	PDU
PDU Type	Metered
Cord length	12 ft (3.7 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets User Manual

Complementary

Input Voltage	100 V 120 V
Height	3.5 in (8.8 cm)
Width	17.5 in (44.4 cm)
Output Voltage	120 V
Depth	4.4 in (11.2 cm)
Net Weight	7.41 lb(US) (3.36 kg)
mounting location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA L5-30P
Mounting Mode	Rack-mounted
Rack units	2U
Mounting position	Horizontal
Line Rated Current	24 A
Input current limits	30 A
Load Capacity	2880 VA
Input Frequency	50/60 Hz
Outlet type and quantity	16 NEMA 5-20R

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL Listed CSA UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950
Ambient Air Temperature for Operation	23.0000000000...113.0000000000 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13.0000000000...149.0000000000 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304331476
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 in (14 cm)
Package 1 Width	14.5 in (36.8 cm)
Package 1 Length	20.0000000000 in (50.8 cm)
Package 1 Weight	11.93 lb(US) (5.41 kg)

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH


Resource performance


 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
