

# Product data sheet

Specifications



## Rack PDU, Switched, 1U, 20A, 120V, (8)5-20



AP7901B

### Overview

**Lead time** Usually in Stock

### Main

**Color** Black

**Product or Component Type** PDU

**PDU Type** Switched

**Cord length** 12 ft (3.7 m)

**Number of cables** 1

**Provided Equipment** Cord retention bracket(s)  
Horizontal mounting brackets  
User Manual  
Installation guide

### Complementary

**Input Voltage** 100 V  
120 V

**Height** 1.7 in (4.4 cm)

**Width** 17.5 in (44.5 cm)

**Output Voltage** 120 V

**Depth** 4.3 in (10.8 cm)

**Net Weight** 5.004 lb(US) (2.27 kg)

**mounting location** Front  
Rear

**Mounting preference** No preference

**Input Plug Type** NEMA L5-20P

**Mounting Mode** Rack-mounted

**Rack units** 1U

**Mounting position** Horizontal

**Line Rated Current** 16 A

**Acceptable Input Voltage** 100...120 V

**Input current limits** 20 A

**Load Capacity** 1900 VA

**Input Frequency** 50/60 Hz

**Outlet type and quantity** 8 NEMA 5-20R

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

<b>Product Certifications</b>	cUL Listed CSA Industry Canada UL Listed
<b>Standards</b>	FCC Part 15 class A ICES-003 UL 60950
<b>Ambient Air Temperature for Operation</b>	32.0000000000...113.0000000000 °F (0...45 °C)
<b>Relative Humidity</b>	0...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...149.0000000000 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	0...95 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>GTIN</b>	731304331575
-------------	--------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	2.8 in (7 cm)
<b>Package 1 Width</b>	13.5 in (34.3 cm)
<b>Package 1 Length</b>	18.5 in (47 cm)
<b>Package 1 Weight</b>	7.61 lb(US) (3.45 kg)

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

 Energy Efficient Product

---


 Take-Back Program Available

---


## Well-being performance

 Lead Free

---

 Mercury Free

---

 Rohs Exemption Information [Yes](#)

---

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

---

Eu Rohs Directive Compliant with Exemptions

---

Environmental Disclosure [Product Environmental Profile](#)

---

Circularity Profile [End of Life Information](#)

---