




# Planar PS5562T

55" Interactive Large Format Display

The Planar® PS5562T is a 55" Full HD commercial-grade, multi-touch LCD display offering up to 20 touch points. The display is the ideal combination of value, performance and 24x7 reliability for interactive applications.



SPECIFICATION	DETAIL
Product Name	PS5562T
Planar Part Number	997-8556-00
Viewable Size	55" diagonal
Aspect Ratio	16:9
Display Resolution	FHD 1080p (1920 x 1080)
Brightness (Typical)	500 cd/m <sup>2</sup>
Contrast Ratio (typ)	4000:1
Response Time (typ)	6.5 ms
Viewing Angle (typ)	178°
External Connections	DisplayPort, HDMI x2, VGA, USB
Power Requirements	100 - 240V; 50/60Hz
Power Consumption (max)	160W
Service and Support/Warranty	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
Recommended Usage	Up to 24x7 operation
Product Approvals	FCC Class A, UL, CE
VESA Compatible/Location	400 mm x 200 mm; 4 holes
Audio Input	PC Audio in (Jack)
Audio Output	R/L Line out (Jack)
Bezel Width	0.8" (21mm)
Cabinet Dimensions (W x H x D)	49.6" x 28.5" x 2.9" (1259mm x 725mm x 73mm)

<b>Display Control</b>	RS232in, IR, Keypad, LAN
<b>Display Weight</b>	86.0 lbs (39 kg)
<b>Shipping weight</b>	104 lbs (47 kg)
<b>Display Type</b>	Edge-Lit LED LCD
<b>Refresh Rate</b>	60 Hz
<b>Operating Temperature</b>	5-35°C (41 -95°F)
<b>Palette</b>	1.073B colors (10 bit)
<b>Pixel Pitch</b>	0.1323mm
<b>Orientation</b>	Landscape/Portrait
<b>Speakers</b>	10W x 2 built-in
<b>Fanless</b>	Yes
<b>Touchscreen Type</b>	IR 20-point touch
<b>OS Compatibility</b>	Windows 10, 8, 7, Vista, XP, Mac OSX and Linux
<b>Features</b>	On/off scheduling, TAA compliant
<b>In the Box</b>	PS5562T display, power cord, VGA cable, IR extender cable, remote control, and USB (A to B) cable
<b>UPC</b>	8 10689 00333 5

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 4/25/2017*

*© Copyright 2017 Planar Systems, Inc. All rights reserved*