



Planar PS6562

65" LCD Display

The Planar® PS6562 is a slim 65" Full HD LCD display designed for demanding digital signage and commercial applications. The Planar PS6562 is the ideal combination of value, performance and 24x7 reliability with the design and energy-saving benefits of LED backlight technology.



SPECIFICATION	DETAIL
Product Name	PS6562
Planar Part Number	997-8557-00
Viewable Size	65" diagonal
Aspect Ratio	16:9
Display Resolution	FHD 1080p (1920 x 1080)
Brightness (Typical)	500 cd/m ²
Contrast Ratio (typ)	4000:1
Response Time (typ)	8 ms
Viewing Angle (typ)	178°
External Connections	DisplayPort, HDMI x2, VGA
Power Requirements	100 - 240V; 50/60Hz
Power Consumption (max)	230W
Service and Support/Warranty	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
Product Approvals	FCC Class A, cTUVus, CE
VESA Compatible/Location	400 mm x 200 mm; 4 holes
Audio Input	PC Audio in (Jack)
Audio Output	R/L Line out (Jack)
Bezel Width	0.7" (17 mm)
Cabinet Dimensions (W x H x D)	57.7" x 33.0" x 3.2" (1464mm x 839mm x 82mm)
Display Control	RS232in, IR, Keypad, LAN

Display Weight	84 lbs (38 kg)
Shipping weight	111 lbs (50 kg)
Display Type	Direct-Lit LED LCD
Refresh Rate	60 Hz
Operating Temperature	5-35°C (41 -95°F)
Palette	1.073B colors (10 bit)
Pixel Pitch	0.1323mm
Orientation	Landscape/Portrait
Speakers	10W x 2 built-in
Fanless	Yes
Features	On/off scheduling, TAA compliant
In the Box	PS6562 display, power cord, VGA cable, IR extender cable, and remote control
Warranty	3-year, 2-day advance replacement
Recommended Usage	Up to 24x7 operation
UPC	8 10689 00334 2

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 6/14/2017

© Copyright 2017 Planar Systems, Inc. All rights reserved