

Model: DXOC 58C3B Product No: 31008079 EAN: 8016361947788 Commodity Code: 84501190 Replacement: New Introduction Date: July 2017	
---	---

Key Features

8kg Load Capacity	Load Capacity	8kg
1500 rpm	Maximum Spin Speed (rpm)	1500
14 minute quick wash	Colour	Black
	Door Colour	Chrome
	Intelligent Wash System	Yes
	KG Mode	Yes
	Touch Display	Yes
	NFC	Yes
	WIFI	No
	Display lock	Yes
	Energy	A+++
	Programs - 15	
	Rapid 14 Minute Wash	Yes
	Rapid 30 Minute Wash	Yes
	Rapid 44 Minute Wash	Yes
	Daily 59 Minute Wash	Yes
	Whites + Prewash	Yes
	Dark Colours	Yes
	Sports	Yes
	Baby Hygiene 60°	Yes
	ActivEcho 20°	Yes
	Drain & Spin	Yes
	Hand Wash & Wool	Yes
	Rinse	Yes
	Delicates	Yes
	One Touch	Yes
	Buttons	
	Temperature Selection	Yes
	Spin Selection	Yes
	Easy Iron	Yes
	Extra Rinse	Yes
	Time Delay	24hrs
	Time Remaining	Yes
	Start & Pause	Yes
Dimensions		
Packed: 68.5kg		
Unpacked: 66.5kg		
Weight		
Packed: 890x650x560		
Unpacked: 850x600x520		
Packaging		Technical Specification
Paper, Carton		Energy Consumption (kwh/cycle - wash) (full load@ 60 degree)
PS (Polystyrene)	1.210	Annual Energy Consumption
LDPE (Low Density Polythelene)	0.331	Water Consumption (litres/annum)
Other Plastic		Water Consumption (litres/cycle 220 washes)
Wood	0.160	Moisture Content After Spin (% dry load)
Metal - Iron		Noise dBA
Metal - Aluminium		Noise dBA
Glass Shelves		Wash Time - full load @ 60 degree (short programme)
Performance		Cold Fill
Energy Efficiency	A+++	Electrical Supply (volts)
Wash Performance	A	Rated Loads (watts)
Spin Drying Performance	A	Motor