

Lenovo™ ThinkPad® X1 YOGA™

WORLD'S LIGHTEST 14" BUSINESS CONVERTIBLE

A convertible that's a laptop, tablet, and beyond.

Lenovo



Laptop Mode



Stand Mode



Tent Mode



Tablet Mode

Enjoy the freedom of working the way you want, wherever you are, with the amazingly light and versatile ThinkPad® X1 YOGA™. Use it as a Laptop, Tablet, Tent or Stand mode for easy-viewing of the stunning display. The world's first convertible with an OLED display, it delivers the most intense colors and stunning contrast. It's fully connected with super-fast 4G LTE-A and totally versatile with a convenient retractable keyboard. With integrated Stylus Pen with Lenovo™ WRITEit software, you can enjoy the lightning-fast writing experience, just 15 seconds of charging gives up to 100 minutes of use.

WHY YOU SHOULD BUY THE LENOVO™ THINKPAD® X1 YOGA™



Thin and light

X1 YOGA™ is just 1.27 kg light, thanks to advanced carbon fiber, housing a 14" OLED display - intense color and contrast.



But adaptable

Work in comfort anywhere with the versatility of four usage modes - Work, Present, Connect and Create. The retractable, spill-resistant keyboard adds functionality and convenience.



Not just fast

Powerful processors up to Intel® Core™ i7 vPro™, up to 1 TB PCIe NVMe storage, open and save large files 2x faster than standard SSD. Optional high speed WWAN at 4G LTE-A standard.



But intuitive

A dockable stylus pen that recharges when connected—just 15 seconds of charging gives up to 100 minutes of use. With WRITEit the system can auto-suggest and correct your writing.



Lenovo™ ThinkPad® X1 YOGA™

SPECIFICATIONS

PERFORMANCE

Processor
Intel® Core™ i5-6200U Processor
(3M Cache, up to 2.80 GHz) + 4GB DDR3 RAM
Intel® Core™ i5-6200U Processor
(3M Cache, up to 2.80 GHz) + 8GB DDR3 RAM
Intel® Core™ i5-6300U Processor
(3M Cache, up to 3.00 GHz) vPRO + 4GB DDR3 RAM
Intel® Core™ i5-6300U Processor
(3M Cache, up to 3.00 GHz) vPRO + 8GB DDR3 RAM
Intel® Core™ i7-6500U Processor
(4M Cache, up to 3.10 GHz) + 8GB DDR3 RAM
Intel® Core™ i7-6600U Processor
(4M Cache, up to 3.40 GHz) vPRO + 8GB DDR3 RAM
Intel® Core™ i7-6600U Processor
(4M Cache, up to 3.40 GHz) vPRO + 16GB DDR3 RAM
Operating System
Windows 10 Pro 64-bit
Windows 7 Pro 64-bit
Graphics
Intel® HD Graphics 520
Memory
Up to 16 GB DDR3
Storage
Up to 1 TB PCIe NVMe SSD
Camera / Microphone
720p / Digital Array Microphone
Battery¹
IPS: Up to 11 hours (52 Whr)
OLED: Up to 9 hours (56 Whr)

DESIGN

Display
14" WQHD (2560 x 1440) OLED,
Touch, 300 nits
14" WQHD (2560 x 1440) IPS,
Anti-Glare, 270 nits
14" FHD (1920 x 1080) IPS,
Touch, 270 nits
Dimensions (W x D x H)
(mm) : 333 x 229 x 16.8
(inches) : 13.11" x 9.01" x 0.66"
OLED Version
(mm) : 333 x 229 x 17
(inches) : 13.11" x 9.01" x 0.67"
Weight
Starting at 2.8 lbs (1270 g)
Security and Manageability
TPM
Kensington® Lock
Touch Fingerprint Reader
Intel® vPro™ Technology
Other Unique Features
Dockable Stylus Pen²

CONNECTIVITY

I/O (Input/Output) Ports
WiGig
OneLink+
Mini DisplayPort™
HDMI™
3 x USB 3.0
microSD™
WLAN
Intel 8260 2x2 AC +
Bluetooth® 4.1 (vPro)
Intel 8260 2x2 AC +
Bluetooth® 4.1 (Non-vPro)
Intel 8260 2x2 AC
(WiGig² / WiFi / Bluetooth® 4.1 Combo)
WWAN²
Sierra Wireless EM7455 Qualcomm®
Snapdragon™ X7 LTE-A
Huawei ME906s LTE
Bluetooth®
Bluetooth® 4.1

¹ Battery life (and recharge times) will vary based on many factors including system settings and usage. A description of the environment under which the test was performed is available upon request.

² Optional

RECOMMENDED SERVICES

Lenovo™ offers a comprehensive portfolio of services to support and protect your ThinkPad® investment. Succeed with substance and let Lenovo's Service support you all the way.

PRIORITY TECHNICAL SUPPORT²
Makes your priority, our priority. 24/7 priority call routing to advanced-level technicians, electronic incident tracking and escalation management services.

WARRANTY UPGRADES - ONSITE AND
NEXT BUSINESS DAY
Maximizes PC uptime and productivity by providing convenient, fast repair service at your place of business.

WARRANTY EXTENSIONS
(UP TO 5 YEARS TOTAL DURATION)
This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and lower the cost of ownership over time.

ACCIDENTAL DAMAGE PROTECTION²
Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

KEEP YOUR DRIVE
Retain your drive if it should happen to fail, giving you the peace of mind to know that your valuable data is secure.

ASSET TAGGING
Systems come equipped with a professional, flexible asset tag based on your exact specifications. PCs are easily identifiable and trackable right out of the box.

OPTIONS & ACCESSORIES



Stylus Pen
A precise writing experience



ThinkPad® X1
In Ear Headphones
Superior sound quality with a comfortable fit



ThinkPad® WiGig Dock
Wirelessly connect and expand the function of your device



ThinkPad® X1
Wireless Touch Mouse
Dual-modes for input and presenting

² Not available in all regions.

