

# HEIC 3C26 C UK

12NC: F153331

EAN code: 5054645533312

Hotpoint



## MAIN FEATURES

|                                                |                      |
|------------------------------------------------|----------------------|
| Construction type                              | Built-in             |
| Installation type                              | Full-integrated      |
| Type of control                                | Electronic           |
| Type of control setting and signalling devices | -                    |
| Removable work top                             | N/A                  |
| Door decor panel                               | Not possible         |
| Main colour of product                         | Silver               |
| Connection rating (W)                          | 1900                 |
| Current (A)                                    | 13                   |
| Voltage (V)                                    | 220-240              |
| Frequency (Hz)                                 | 50                   |
| Length of Electrical Supply Cord (cm)          | 130                  |
| Plug type                                      | UK                   |
| Length inlet hose (cm)                         | 155                  |
| Length outlet hose (cm)                        | 150                  |
| Adjustable plinth                              | No                   |
| Height of removable worktop (mm)               | 0                    |
| Adjustable feet                                | Yes - all from front |
| Height of the product                          | 820                  |
| Width of the product                           | 595                  |
| Depth of the product                           | 570                  |
| Depth with open door 90 degree (mm)            | -                    |
| Minimum niche height                           | 820                  |
| Maximum niche height                           | 900                  |
| Minimum niche width                            | 600                  |
| Maximum niche width                            | 600                  |
| Niche depth                                    | 570                  |
| Net weight (kg)                                | 35.50                |
| Gross weight (kg)                              | 37.50                |

## TECHNICAL FEATURES

|                                           |            |
|-------------------------------------------|------------|
| Automatic programmes                      | Yes        |
| Maximum temperature for water intake (°C) | 60         |
| Start delay options                       | Continuous |
| Start delay time max. (h)                 | 12         |
| Progress indicator                        | -          |
| Digital countdown indicator               | Yes        |
| Salt light indicator                      | Yes        |
| Rinse aid light indicator                 | Yes        |
| Safety device                             | No         |
| Adjustable upper basket                   | Yes        |
| Largest loadable dish upper basket (cm)   | 0          |
| Largest loadable dish lower basket (cm)   | 0          |

## PERFORMANCES

|                                                          |      |
|----------------------------------------------------------|------|
| Energy efficiency class - NEW (2010/30/EC)               | A++  |
| Energy consumption annual (kWh/annum) - NEW (2010/30/EC) | 265  |
| Duration of the left-on mode - NEW (2010/30/EC)          | 12   |
| Power consumption in left-on mode - NEW (2010/30/EC)     | 5    |
| Power consumption in off-mode - NEW (2010/30/EC)         | 0.50 |
| Water consumption annual (l/annum) - NEW (2010/30/EC)    | 2520 |
| Noise level (dB(A) re 1 pW)                              | 46   |