



Planar PS6562T

Interactive LCD Display

The Planar® PS6562T is a 65" Full HD commercial-grade, multi-touch LCD display offering up to 20 touch points. The display is the ideal combination of value, performance and 24x7 reliability for interactive applications.



SPECIFICATION	DETAIL
Product Name	PS6562T
Planar Part Number	997-8558-00
Viewable Size	65" diagonal
Aspect Ratio	16:9
Display Resolution	FHD 1080p (1920 x 1080)
Brightness (Typical)	500 cd/m ²
Contrast Ratio (typ)	4000:1
Response Time (typ)	8 ms
Viewing Angle (typ)	178°
External Connections	DisplayPort, HDMI x2, VGA, USB
Power Requirements	100 - 240V; 50/60Hz
Power Consumption (max)	230W
Service and Support/Warranty	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
Recommended Usage	Up to 24x7 operation
Product Approvals	FCC Class A, cTUVus, CE
VESA Compatible/Location	400 mm x 200 mm; 4 holes
Audio Input	PC Audio in (Jack)
Audio Output	R/L Line out (Jack)
Bezel Width	0.9" (22mm)
Cabinet Dimensions (W x H x D)	58.1" x 33.6" x 3.8" (1477mm x 853mm x 97mm)

Display Control	RS232in, IR, Keypad, LAN
Display Weight	TBD lbs (TBD kg)
Shipping weight	135 lbs (61 kg)
Display Type	Direct-Lit LED LCD
Refresh Rate	60 Hz
Operating Temperature	5-35°C (41 -95°F)
Palette	1.073B colors (10 bit)
Pixel Pitch	0.1323mm
Orientation	Landscape/Portrait
Speakers	10W x 2 built-in
Fanless	Yes
Touchscreen Type	IR 20-point touch
OS Compatibility	Windows 10, 8, 7, Vista, XP, Mac OSX and Linux
Features	On/off scheduling, TAA compliant
In the Box	PS6562T display, power cord, VGA cable, IR extender cable, remote control, and USB (A to B) cable
UPC	8 10689 00335 9

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 7/7/2017

© Copyright 2017 Planar Systems, Inc. All rights reserved