

# Data Sheet

## FUJITSU Notebook LIFEBOOK U937

### Your Light Yet Powerful Business Companion

With its extraordinarily light design, weighing only 920g and an all-day battery runtime, the Fujitsu Notebook LIFEBOOK U937 is an ultra-mobile notebook for business professionals who are always on the move. The solid magnesium housing ensures durability while security features such as the integrated palm vein sensor keep your business data protected. The powerful performance and the optional embedded 4G/LTE provide you with best-in-class user experience.

#### Outstanding ultra-slim and robust design

Extraordinarily lightweight design for business professionals who are always on the move

- A remarkably slim 15.5mm notebook weighing only 920g with a robust magnesium housing
- The best viewing experience is guaranteed by an anti-glare 13.3-inch FHD (1920 x 1080) display, optionally with glare touch



#### Ultimate security features

Protect your notebook and business data from unauthorized access at all times

- Embedded palm vein or fingerprint sensor, SmartCard reader, TPM 2.0



#### Excellent connectivity

Be flexible and stay productive in a hyper-connected world

- Full set of interfaces with a full-sized HDMI, full-sized LAN connector and USB Type-C
- Embedded WLAN, Bluetooth, optional 4G/LTE and DDR4 memory technology up to 20 GB



#### Convenient mobility on the go

Highest productivity on business trips

- All-day battery runtime offers you exceptional mobility that you need when on the move
- Anytime USB Charge functionality to charge telephones and other media devices even when the system is turned off
- Powerful performance, thanks to integrated SSDs, helps process data faster

# Components

## Operating systems

Operating system	Windows 10 Pro. Fujitsu recommends Windows 10 Pro.
------------------	--

Processor	Intel® Core™ i7-7600U processor (2.9 GHz, up to 3.9 GHz, 4 MB) Intel® Core™ i5-7300U processor (2.6 GHz, up to 3.5 GHz, 3 MB) Intel® Core™ i5-7200U processor (2.5 GHz, up to 3.1 GHz, 3 MB) *
-----------	--

\*Processor only for retail, SMB, education and government

Memory modules	4 GB (1 module(s) 4 GB) DDR4, 2,133 MHz, SO DIMM 8 GB (1 module(s) 8 GB) DDR4, 2,133 MHz, SO DIMM 16 GB (1 module(s) 16 GB) DDR4, 2,133 MHz, SO DIMM
----------------	--

Hard disk drives (internal)	SSD SATA III, 512 GB, M.2 module, SED SSD SATA III, 256 GB, M.2 module, SED SSD SATA III, 256 GB, M.2 module SSD SATA III, 128 GB, M.2 module PCIe-SSD, 512 GB, M.2 module, SED PCIe-SSD, 256 GB, M.2 module, SED
-----------------------------	--

Hard disk notes	One Gigabyte equals one billion bytes, when referring to hard disk drive capacity. Accessible capacity may vary, also depending on used software. Up to 20 GB of HDD space is reserved for system recovery Internal storage interface: S-ATA III or PCIe
-----------------	---

## Interface add on cards/components (optional)

Display	33.8 cm (13.3-inch),LED backlight,(Full HD),magnesium,1,920 x 1,080 pixel,300cd/m <sup>2</sup> 33.8 cm (13.3-inch),LED backlight,(Full HD),Anti-glare IPS display,magnesium,1,920 x 1,080 pixel,330cd/m <sup>2</sup>
---------	---

## Multimedia

Camera	Built-in webcam, HD
--------	---------------------

# Base unit

## General system information

Chipset	Integrated in CPU
Built-in memory	4 GB
Supported capacity RAM (max.)	20 GB
Memory slots	1 DIMM (DDR4)
Memory notes	DDR4 - 2133 MHz
LAN	10/100/1,000 MBit/s Intel® I219LM
BIOS features	InsydeH20 Bios
Audio type	On board
Audio codec	Realtek ALC255
Audio features	Stereo speakers

## Graphics

Graphics brand name	Intel® HD Graphics 620
Graphics features	3 Display Support
Graphics notes	Shared memory depending on main memory size and operating system

**Interfaces**

DC-in	1
Audio: line-out / headphone	1 (combo port with Audio line-in)
Audio: line-in / microphone	1 (combo port with Audio line-out)
Internal microphones	2x digital array microphones
USB 3.1 Gen1 (USB 3.0) total	2 x Typ-A (1 with Anytime USB charge functionality) 1 x Typ-C (with Power Delivery functionality)
HDMI	1
Ethernet (RJ-45)	1 (pull out)
Memory card slots	1 SD4.0
SmartCard slot	1
SIM card slot	1 (only for models with integrated 4G/LTE module)

**Keyboard and pointing devices**

Keyboard w/o touchstick (spill-resistant)
Multi gesture touchpad with integrated mouse button functionality
Status LED

**Wireless technologies**

Antennas	2 Dual band WLAN antennas, 2 LTE antennas optional
Bluetooth	v4.2
WLAN encryption	WEP, WPA, WPA2
WLAN notes	Import and usage according to country-specific regulations.

**Power supply**

1st battery options	Lithium polymer battery 4-cell, 50 Wh
1st battery	50 Wh
Runtime 1st battery	up to 11 h
Battery notes	Battery runtime information is based on worldwide acknowledged BAPCo® MobileMark® 2014 (office productivity). Refer to <a href="http://www.bapco.com">www.bapco.com</a> for additional details. The BAPCo® MobileMark® Benchmark provides results that enable direct product comparisons between manufacturers. It does not guarantee any specific battery runtime which actually can be lower and may vary depending on product model, configuration, application and power management settings. The battery capacity decreases slightly with every re-charge and over its lifetime.

**Noise emission**

Noise emission	Please refer to the Eco Declaration
----------------	-------------------------------------

**Dimensions / Weight / Environmental**

Dimensions (W x D x H)	309.3 x 213.5 x 15.5 mm 12.18 x 8.40 x 0.61 inch
Weight	starting at 920 g
Weight (lbs)	starting at 2.02 lbs
Weight notes	Weight may vary depending on actual configuration
Operating ambient temperature	5 - 35 °C (41 - 95 °F)
Operating relative humidity	20 - 85 %

**Product**

Compliance link	<a href="https://sp.ts.fujitsu.com/sites/certificates">https://sp.ts.fujitsu.com/sites/certificates</a>
-----------------	---

**Additional Software****Manageability**

Manageability technology	DeskUpdate Driver management iAMT 11.6 (depending on processor) PXE 2.1 Boot code Wake-on-LAN Intel® vPro™ technology
--------------------------	---

## Manageability

DeskView components	Inventory Management BIOS Management Driver Management Security Management Alarm Management
Supported standards	WMI (Windows Management Instrumentation) PXE (Preboot Execution Environment) DMI (Desktop Management Interface) SMBIOS (System Management BIOS) WBEM (Web Based Enterprise Management) CIM (Common Information Model) BootP (made4you)
Manageability link	<a href="http://www.fujitsu.com/fts/manageability">http://www.fujitsu.com/fts/manageability</a>

## Security

User Security	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution) Embedded fingerprint sensor (optional) Embedded palm vein sensor (optional) Smartcard reader (integrated) SystemLock 3 SmartCard Security (optional): BIOS based pre-boot/ two-factor authentication for high level of access protection
---------------	--

## Warranty

Warranty Terms & Conditions	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>
<b>Product Support Services - the perfect extension</b>	
Recommended Service	9x5, Onsite Response Time: Next Business Day
Service Weblink	<a href="http://ts.fujitsu.com/Supportservice">http://ts.fujitsu.com/Supportservice</a>

## Recommended Accessories

Sneaker Sleeve 12.5		The Sneaker Sleeve 12.5 protects notebooks or tablets with up to 12.5-inch screens. The front half of the bag has dedicated compartments for your notebook, power cord, office supplies and personal items. The back half of the bag has an expanding, divided compartment for your files. It is designed to combine fashion and functionality.	Order Code: S26391-F1667-L100
Wireless Notebook Mouse WI410		The Wireless Notebook Mouse WI410 is the perfect mouse for road warriors who don't want to bother with cables. It is compact enough to easily slip into a notebook bag or briefcase without getting in the way. It features two buttons and a scroll wheel which can also be used as a third button.	Order Code: S26381-K464-L100

**UC&C USB Headset Stereo  
H650e**



The UC&C USB Headset Stereo H650e is the ultimate in style and functionality. Long, uncomfortable work calls are a thing of the past thanks to the cushioned ear pads and crystal clear sound. Adjustable headband and microphone provides the perfect fit for everyone. Optimized for Microsoft® Lync™ the headset displays a red 'in-call' LED to let your co-workers know when you're available, thus helping to boost office productivity.

Order Code:  
S26391-F7139-L10

**Wireless Keyboard Set LX901**



The Wireless Keyboard LX901 is a top of the line desktop solution for lifestyle orientated customers, who want only the best for their desk. This superb keyboard set offers ambitious users more functions, security and better features than a conventional interface device. It even includes 2.4 GHz technology and 128 AES encryption.

S26381-K565-L4\*\* (\*\*:  
Country specific variation)

# More information

## Fujitsu OPTIMIZATION Services

In addition to FUJITSU Notebook LIFEBOOK U937, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

## Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

## Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

## Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about FUJITSU Notebook LIFEBOOK U937, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

[www.fujitsu.com/fts/mobile](http://www.fujitsu.com/fts/mobile)

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment/>



**Green  
Policy  
Innovation**

## Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH

## Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

## CONTACT

Fujitsu Technology Solutions GmbH

Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)

2017-03-20 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH