

Product data sheet

Specifications



APC Smart-UPS On-Line, 1500VA, Tower, 120V, 6x 5-15R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit

SRT1500XLA

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Rated power in W	1350 W
Rated power in VA	1500 VA
Input Connection Type	NEMA 5-15P
Output connection type	6 NEMA 5-15R
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Communication Cable Documentation CD Installation guide Removable support feet USB cable Warranty card

Batteries & Runtime

Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Voltage	48V
Battery Charge Power (Watts)	91 W rated
Battery power in VAh	273 VAh runtime
Battery life	3...5 year(s)
Replacement battery	APCRBC155
Battery option	SRT48BP 1 819 VAh SRT48BP 2 1365 VAh SRT48BP 3 1910 VAh SRT48BP 4 2456 VAh SRT48BP 5 3002 VAh SRT48BP 6 3548 VAh

Extendable Run Time 0

General

Product web sub-family High density

Number of power module free slots 0

Number of power module filled slots 0

Redundant No

Physical

Color Black

Height 17.01 in (43.2 cm)

Width 3.35 in (8.5 cm)

Depth 20.00 in (50.8 cm)

Product Weight 48.50 lb(US) (22 kg)

Mounting preference No preference

Mounting Mode Rack-mounted with kit

Two post mountable 0

USB compatible Yes

Mounting position Vertical

Input

Input Frequency 40 - 70 Hz auto-sensing

Efficiency at full load 108...150 V
50...150 V 40% load

Output

Max Configurable Power (Watts) 1350 W

Harmonic distortion Less than 2%

Output Frequency (sync to mains) 50/60 Hz +/- 3 Hz sync to mains

Crest factor 3 : 1

Topology Double Conversion Online

Waveform Type Sine wave

Bypass type Built-in Bypass

Maximum configurable power in VA 1500 VA

Conformance

Product Certifications ENERGY STAR V2.0 (USA)

Environmental

Ambient Air Temperature for Operation 32...104 °F (0...40 °C)

Relative Humidity 0...95 % non-condensing

Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	50 dBA
Online Thermal Dissipation	463 Btu/h
IP degree of protection	IP20

Communications & Management

Free slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	432 J
---------------------	-------


Ordering and shipping details

GTIN	731304330097
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.69 in (24.6 cm)
Package 1 Width	29.49 in (74.9 cm)
Package 1 Length	23.39 in (59.4 cm)
Package 1 Weight	65.26 lb(US) (29.6 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA) 
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Recommended replacement(s)