

CLEAN SEAL MEDICAL BACKLIT KEYBOARD WITH CONTACTLESS SMART CARD READER

Model: SSKSV207GRC13.56

Top-of-the-line Clean Seal Medical-Grade Backlit Keyboards with a built-in Smart Card Reader from Seal Shield. Keyboards have a 100% waterproof & dishwasher-safe rating that is IP68-certified (highest rating), and compatible with medical-grade cleaners & disinfectants. Standard keyboard design for smooth and natural functionality. Features a Quick Connect Cable with Seal Cap™ for easy plug-and-play and a contact-free built-in Smart Card Reader for added security.

FEATURES:



100% Waterproof
& Dishwasher Safe



USB Quick Connect Cable
with Seal Cap™



Full-Size Numeric
Keypad and
Laser Etched Keycaps



Compatible with
Hospital Cleaners &
Disinfectants



Non-Touch Built-in
Smart Card Reader



LED Backlit Keys



Keyboard is
IP68 Certified
(highest waterproof rating)



SSKSV207GRC13.56

MEDICAL-GRADE CLEANING CAPABILITIES

- Dishwasher-Safe (Hot & Cold settings)
- Bleach compatible. Clorox® approved.
(including Clorox HealthCare Products)
- Disinfectants & Sporicides
(including Lysol® products EPA-certified to kill COVID-19)
- Solvents, Corrosives and Acids
- Alcohol and H. Peroxide



CLEAN SEAL MEDICAL BACKLIT KEYBOARD WITH CONTACTLESS SMART CARD READER

Model: SSKSV207GRC13.56

TECHNICAL DATA:

Compatibility:	Window®s, (USB Models)
Construction:	ABS Plastic (Standard Style)
Key Layout:	104 US Language
Net Dimensions L x W x H:	18.07 x 6.85 x 1.38 in (45.9 x 17.4 x 3.5 cm)
Gross Dimensions L x W x H:	18.74 x 7.76 x 1.75 in (47.6 x 19.7 x 4.45 cm)
Net Weight:	1.77 lb (0.802 kg)
Gross Weight:	1.99 lb (0.906 kg)
Cable Length:	6 in (15 cm) Quick Connect Cable with 6 ft
Connection Type:	Gold Plated USB (can support PS/2 technology)
Key Switch Type:	Membrane Key Switch with Tactile Feedback
Key Switch Force:	53 ± 7 gf
Key Switch Life Cycle:	Greater than 10 Million Keystrokes
Keycaps Imaging Type:	Laser Etched
Total Key Travel:	4.0 ± 0.2 mm
Operating Voltage:	+ 5VDC ± 5%
Power Consumption:	150mA Max
Supported Smart Cards:	HID iCLASS, ISO 14443A, MIFARE®, ISO 15693, NFC 1 (Topaz), FeliCa (NFC 3), ISO 14443B, CEPAS, MIFARE® DESFire® (Cards other than HID iCLASS require Card Reader to be Specially Formatted)
Card Reader Type:	pcProx® Nano 13.56 MHz Contactless Reader
Card Reader Speed:	13.56MHz
Backlighting Features:	Off, Low, Med. High Settings
Storage Temperature:	-5° - 140° F (-20° to 60° C)
EMI - RFI:	Conforms to FCC Rules for Class B Device
Waterproof/Dustproof Ratings:	100% Waterproof & Dustproof (IP68, NEMA 4X)
Approvals/Certifications:	IP68, FCC



Copyright© 2020, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners.

Limited 2-Year Warranty