

## Serie | 2 Fridge-Freezer-Combination

### No Frost, Fridge freezer

**KGN34NW3AG**

**White**



**A++**

### The NoFrost bottom freezer with MultiBox: Has enough room for all your food

- **MultiBox:** transparent drawer with wave bottom, ideal for the storage of fruits and vegetables
- LED lighting - with soft start, lasts for the lifetime of the appliance.
- **Perfect Fit:** The appliance can be positioned right next to side walls and furniture - flexible installation possible

#### Technical Data



Construction type :	Free-standing
Door panel options :	Not possible
Height (mm) :	1860
Width of the product (mm) :	600
Depth of the product :	660
Net weight (kg) :	65.0
Connection rating (W) :	100
Current (A) :	10
Door hinge :	Right reversible
Voltage (V) :	220-240
Frequency (Hz) :	50
Approval certificates :	CE, VDE
Length of electrical supply cord (cm) :	240
Storage Period in Event of Power Failure (h) :	19
Number of compressors :	1
Number of independent cooling systems :	1
Interior ventilator :	No
Reversible Door Hinge :	Yes
Number of Adjustable Shelves in fridge compartment (Stck) :	2
Shelves for Bottles :	No
EAN code :	4242005053438
Brand :	Bosch
Product name / Commercial code :	KGN34NW3AG
Energy efficiency class (2010/30/EC) :	A++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) :	242
Refrigerator Net capacity (l) - NEW (2010/30/EC) :	192
Freezer Net capacity (l) - NEW (2010/30/EC) :	105
Frost free system :	Fridge and freezer
Temperature rise time (h) :	19
Freezing capacity (kg/24h) - NEW (2010/30/EC) :	11
Climate class :	SN-T
Noise level (dB(A) re 1 pW) :	42
Installation type :	N/A

#### Included accessories

3 x egg tray  
1 x ice cube tray with lid



4 242005 053438

## Serie | 2 Fridge-Freezer-Combination

### No Frost, Fridge freezer

**KGN34NW3AG**

**White**

### The NoFrost bottom freezer with MultiBox: Has enough room for all your food

#### Performance and Consumption

- Energy Efficiency Class: A++ at a range of energy efficiency classes from A+++ to D. Actual consumption will depend on how the appliance is used and where it is located.
- Total net capacity: 297 litres
- Net fridge capacity: 192 litres
- Net freezer capacity: 105 litres
- Noise level dB(A) re 1 pW: 42

#### Dimension and installation

- Climate class SN-T (suitable for ambient temperatures between 10 to 43°C)
- Connection value 100 W
- Height adjustable front feet
- Dimensions: 186 cm H x 60 cm W x 66 cm D
- Based on the results of the standard 24-hour test. Actual consumption depends on usage/position of the appliance.
- To achieve the declared energy consumption, the distanceholders have to be used. As a result, the appliance depth increases by about 3.5 cm. The appliance used without the distance holder is fully functional, but has a slightly higher energy consumption.

#### Design features

- White doors and white side panels
- High-door design, Cambered door
- Indoor LED electronic control
- Integrated horizontal handle
- Right hinged door, door reversible
- Removable magnetic door seals - easy to clean

#### Food freshness system

- MultiAirflow system - improves circulation of air around the fridge
- 1 compressor

#### Key features - Fridge section

- 1 MultiBox - Transparent drawer with a rippled bottom, ideal for storing fruits and vegetables.
- Bright interior LED fridge light
- 4 safety glass shelves in fridge compartment of which 2 are height adjustable
- Door trays in fridge door: 1 large and 2 small.

#### Key features - Freezer section

- White
- Automatic defrost freezer
- SuperFreezing function with automatic deactivation
- 3 freezer drawers
- 1 BigBox extra large drawer
- 4 star freezer rating
- Freezing capacity in 24 hours: 11 kg
- Maximum freezer storage time in power failure: 19 hours
- Freezer malfunction warning signal: optical and acoustical warning system

#### Included accessories

- 3 x egg tray, 1 x ice cube tray with lid


## Serie | 2 Fridge-Freezer-Combination

### No Frost, Fridge freezer

**KGN34NW3AG**

**White**

Appliance name	a	b	c	d	e	f	g
KGN36 (inner handle)	1860	600	660	590	600	1210	660
KGN36 (outer handle)	1860	600	660	590	640	1210	700



Specification
a Height
b Width
c Depth with door closed, without handle
d Cabinet depth
e Width with door opened to 90°
f Depth with door opened
g Depth with door closed, with handle

measurements in mm