

# SLA-T-M940DN

4K Varifocal Lens



SLA-T-M940DN

IMAGING	
Focal Length	9-40mm
Resolution	True 4K, up to 12MP, check sensor size below
F-Stop	F/1.5 to close
IR Correction	IR Corrected for true Day/Night operation
Lens length	<50mm
Minimum Focal Distance	2.5m - infinity
Iris Cable Length	30cm
Lens Type	DC Auto Iris
Mount Type	CS Mount
Operating Temperature / Humidity	-20°C ~ +60°C (-4°F ~ +140°F) <70% humidity, non-condensing
Storage Temperature / Humidity	-30°C ~ +70°C (-22°F ~ +158°F) <90% humidity, non-condensing

Sensor size	1/3"	1/2.7"	1/2.5"
Field of view (H)	30° - 7.1°	37° - 8.6°	36° - 8.5°
Field of view (V)	22° - 5.3°	20° - 4.8°	27° - 6.3°
Field of view (D)	38° - 8.8°	42° - 9.9°	46° - 10.6°

\* The latest product information / specification can be found at [hanwhasecurity.com](http://hanwhasecurity.com)  
 \* Design and specifications are subject to change without notice.

## Key Features

- High resolution optics
- True 4K resolution, 12MP support
- 9-40mm varifocal lens
- DC Auto Iris
- IR corrected for true Day/Night operation
- CS-mount with slip ring for ease of installation and positioning

## Dimensions

Unit : mm (inch)

