

# Lenovo™ ThinkCentre M910z


## CUTTING-EDGE PERFORMANCE MEETS ENTERPRISE MANAGEABILITY

Powerful, dependable, manageable and secure... ThinkCentre M910z AIOs boost your organization's efficiency and productivity.

Packed with the latest Intel® up to Core™ i7 processor and vPro™ technology, Lenovo ThinkCentre M910z AIO is built for enterprise. With PCIe SSD and Intel® Optane™ technology\*, M910z AIO enables you carry out intensive task with ease. MIL-SPEC tested, meaning your AIO can still be reliable even in the most challenging environments. Plus built-in data security – these easy-to-use machines keep your workforce on task, and improve productivity.

\*Intel® Optane™ Memory will be launch in June 2017

### WHY YOU SHOULD BUY THE LENOVO™ THINKCENTRE M910Z



#### Powerful

Tackle spreadsheets, multiple presentations and photo editing with ease with the latest 7<sup>th</sup> generation vPro™-enabled up to Intel® Core™ i7 processors.



#### Easy Remote Management

With Intel® vPro™ you can remotely access your fleet of desktops – saving time and hassle on desk-side visits, and cutting down management costs.



#### Extreme Dependability

Put through a range of military-spec tests and over 200 reliability tests in everything from tropical climates to rough transportation conditions – rest assured ThinkCentre AIOs can handle almost any environment.



#### Reliable and Secure

Smart USB Protection prevents data from being transferred from USB ports while still allowing you to connect peripheral devices – so your data stays confidential. Plus, you can lock the inbuilt privacy camera with the flick of a switch for your peace of mind and privacy.



#### Twice As Easy to Service

Taking off the back cover, stand, and want to remove HDD, memory, all you need is your hand without tools. Tool less design makes repairing and replacing easier than ever.



### WHO NEEDS THE LENOVO™ THINKCENTRE M910Z?

**1** Progressive ITDMs who want powerful, reliable and secure devices: ThinkCentre M-series AIO is enterprise ready delivering reliable performance in a single solution

**2** Busy professionals requiring desktop-standard performance with plenty of horsepower and upgrade options

**3** IT managers who value the ease of remote fleet management to save on hands-on time and operational costs



Lenovo

# Lenovo™ ThinkCentre M910z

## WHAT'S IN A THINKCENTRE®



Lowest failure rates in the industry<sup>1</sup>



The highest % of recycled materials



Intelligent Cooling Engine (ICE)



Gold plated pins<sup>2</sup> for signal quality

## SPECIFICATIONS

### Lenovo™ ThinkCentre M910z

#### PERFORMANCE

##### Operating System

Windows 10 Pro

Support Windows 10 Downgrade to Windows 7 (not available with 7<sup>th</sup> generation Intel® processor)

##### Processor

Up to 7<sup>th</sup> generation Intel® Core™ i7 Vpro™ processor

##### Storage

2.5" HDD (500GB / 1TB)  
2.5" SSD (128GB)  
M.2 OPAL SSD(256G/512G)  
M.2 Non-OPAL SSD(128G)  
Slim ODD Rambo / DVD ROM

##### Memory

DDR4, 2 x SODIMM, up to 32GB

##### Camera

1080p / digital array

##### Audio

2 x 3W with Dolby® solution

##### Graphics

Discrete – NVIDIA® 940MX 2GB gDDR5 for SpB

##### Power Adapter PSU

###### Internal

150W 85% for integrate graphics model  
180W 92% for discrete graphics model

#### SECURITY

Kensington lock; Cable lock (for KB & mouse cables)

TPM; USB smart protection; USB port disable (individually); Intrusion switch; Computrace

#### CONNECTIVITY

##### Ports

2 x USB3.0 with 1 always on rapid charge / Type C for option / Headphone & Mic combo / 9-in-1 card reader

4 x USB3.0 / serial port / DP in & out combo / LAN / AC in

1 x M.2 2280 & 2242 for SSD and Intel® Optane™

##### Connectivity

1 x M.2 2230 for WiFi

#### DESIGN

##### Display

23.8" WVA WLED, 1920 x 1080 FHD, 250 nit

##### Dimension (W x H x D) / Weight

With multi-touch, non-stand:  
584 mm x 390 mm x 45 mm / 7.8 kg

Without multi-touch, non-stand:  
584 mm x 390 mm x 45 mm / 6.8 kg

With multi-touch, UltraFlex II Stand:  
584 mm x 505 mm x 253 mm / 10.3 kg

Without multi-touch, Basic Monitor Stand:  
584 mm x 458 mm x 245 mm / 8.8 kg

Without multi-touch, UltraFlex II Stand:  
584 mm x 505 mm x 253 mm / 9.4 kg

##### Stand

Basic monitor stand, tilt only with -5 degrees - 45 degrees.

UltraFlex II stand, tilt with -5 degrees - 60 degrees; Swivel with 90 degrees; Height with 110 mm

##### MIL-SPEC

8 items (low altitude, high/low temperature, temperature shock, humidity, sand and dust, vibration, shock)

##### Ease of Use (Too-less Access)

Yes (Rear cover; HDD; Memory; Stand)

#### SOFTWARE

##### Windows 10 Preloads

Cyberlink PowerDVD  
Cyberlink PowerDVD Create (Power2Go and Power Producer)

Lenovo Audit Date

Lenovo Companion

Lenovo ID

Lenovo Setting

Lenovo Vision Guard

Microsoft Office Trial (except Japan)

##### Windows 7 Preloads

Adobe  
Create Recovery Media  
Cyberlink PowerDVD Create (Power2Go and Power Producer)  
Lenovo Solution Center  
Lenovo ThinkVantage Tools  
Lenovo Vision Guard  
ThinkVantage System Update  
Microsoft Office Trial (except Japan)

#### GREEN CERTIFICATION

65% PCC  
Energy star 6.1  
TCO2.0 / TCO Edge  
ULE / EPEAT Gold (NA only)  
EuP 2015  
Green Guard  
Low Blue Light Certification

#### RECOMMENDED SERVICES

Lenovo offers a comprehensive portfolio of services to support and protect your investment. Succeed with substance and let Lenovo Service support you all the way.

##### PRIORITY TECHNICAL SUPPORT

Makes your priority, our priority. 24 x 7 priority call routing to advanced-level technicians, electronic incident tracking, and escalation management services.

##### WARRANTY UPGRADES—ON-SITE AND NEXT BUSINESS DAY

Maximizes PC uptime and productivity by providing convenient and fast repair service at your place of business.

##### WARRANTY EXTENSIONS (1-3 YEARS TOTAL DURATION)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment, and lower the cost of ownership over time.

##### ACCIDENTAL DAMAGE PROTECTION

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops, or damage to the integrated screen.

##### KEEP YOUR DRIVE

Retain your drive if it should happen to fail, giving you the peace of mind of knowing that your valuable data is secure.

##### ASSET TAGGING

Systems come equipped with a professional, flexible asset tag based on your exact specifications. PCs are easily identifiable and trackable right out of the box.

#### OPTIONS & ACCESSORIES



Lenovo Privacy Filter  
for ThinkCentre AIO  
from 3M



Lenovo Professional  
Wireless Combo



Lenovo Stereo  
Headset

<sup>1</sup> TBR Large Enterprise Repair Rate Study 2011.

<sup>2</sup> CPU Socket is not included.



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit [www.lenovo.com](http://www.lenovo.com). Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. AMD, the AMD Arrow logo and combinations thereof are trademarks of Advanced Micro Devices, Inc. in the United States and/or other jurisdictions. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit [www.lenovo.com/lenovo/us/en/safecom/](http://www.lenovo.com/lenovo/us/en/safecom/) periodically for the latest information on safe and effective computing. ©2016 Lenovo. All rights reserved.

Lenovo