

# XEROX® VERSALINK® COLOUR PRINTER AND COLOUR MULTIFUNCTION PRINTER

High-performance productivity—personalised.

**C500/C505**



ConnectKey®  
Technology

xerox 

# Xerox® VersaLink® C500 Colour Printer and Xerox® VersaLink® C505 Colour Multifunction Printer

Designed for fast-paced workteams, the VersaLink C500 Colour Printer and C505 Colour Multifunction Printer deliver a higher level of reliable performance. Cloud connected, mobile ready, app-enabled, and easy to customise, the C500 and C505 are your modern workplace assistants – helping you excel today and stay ready for the future.

## POWERFUL, RELIABLE, SECURE.

Right out of the box, you'll count on your VersaLink C500 or C505 to consistently and flawlessly perform the tasks that make your business work more efficiently. From IT-free installation wizards, to step-by-step configuration options, you're ready to go – hassle free.

Completely re-engineered for superior reliability, the VersaLink C500 and C505 feature a new hardware design with fewer moving parts, and a more advanced Hi-Q LED print head.

VersaLink devices are loaded with features and time-saving Xerox technologies designed to speed up information sharing and reduce inefficient workflows. Ensure information accuracy with Scan and Fax preview<sup>1</sup>, and do more with scanned documents with built-in optical character recognition (OCR)<sup>1</sup>.

When it comes to safeguarding critical information, VersaLink devices deliver a spectrum of stringent security features, including Secure Print and card authentication to control access.

Count on superior print quality to make your work look its best. A print resolution of up to 1200 x 2400 dpi delivers sharp text and fine line detail, plus exceptional colour vibrancy.

## EASY, EFFICIENT AND ENTIRELY NEW.

With the customisable, capacitive 7-inch colour touchscreen (5-inch on the C500), you can tap, swipe and pinch your way through tasks and functions with mobile-like ease.

Speed through tasks by saving common settings as presets for simple, single-touch job setup. With Simple ID, individual users and groups enter a user ID and password once, and then enjoy fast, secure, easy access to task-specific presets and commonly used apps on a personalised home screen.

## APP-BASED FLEXIBILITY AND MOBILE FREEDOM.

The VersaLink C500 Colour Printer and VersaLink C505 Colour Multifunction Printer give you the freedom to work where and how you want – with out-of-the-box connectivity to Google Drive™, Microsoft® OneDrive® and Dropbox™, and access to additional options through the Xerox App Gallery.

The ability to connect and print from multiple devices is key for today's worker, and VersaLink devices meet the challenge with Apple® AirPrint®, Google Cloud Print™, Xerox® Print Service Plug-in for Android™, Near Field Communication (NFC) Tap-to-Pair and Mopria®, plus optional Wi-Fi and Wi-Fi Direct.

Learn more about why Xerox is the only choice for today's mobile professionals by visiting [www.xerox.com/mobile](http://www.xerox.com/mobile).

<sup>1</sup> VersaLink C505 only (Fax Preview available for VersaLink Multifunction Printers with faxing capabilities)

To learn more about VersaLink device features, go to [www.xerox.com/VersaLinkEG](http://www.xerox.com/VersaLinkEG)

## XEROX® CONNECTKEY® TECHNOLOGY – THE NEXUS OF YOUR COMPLETE PRODUCTIVITY ECOSYSTEM

From Xerox – the company that created the modern workplace – we present the next revolution in workplace productivity. With a consistent user experience across a wide range of devices, mobile and cloud connectivity and a growing library of apps to expand functionality, you'll work faster, better and smarter.

### Intuitive User Experience

An entirely new – and yet entirely familiar way to interact that includes a tablet-like experience with gesture-based touchscreen controls and easy customisation.

### Mobile and Cloud Ready

Instant connectivity to cloud and mobile devices right from the user interface, with access to pre-loaded, cloud-hosted services that let you work where, when and how you want.

### Benchmark Security

Full multi-level protection for both documents and data, ready to guard against and eliminate emerging threats and meet or exceed regulatory compliance.

### Enables Next Generation Services

Work more efficiently and manage resources more effectively. Easy integration of Xerox® Managed Print Services enables remote monitoring of service delivery and consumables.

### Gateway to New Possibilities

Instantly extend your capabilities with access to the Xerox App Gallery, featuring real-world apps designed to optimise digital workflows. Commission our network of partners to design innovative, business-specific solutions.

Find out more about how you'll work smarter at [www.connectkey.com](http://www.connectkey.com).



**Xerox® VersaLink® C500 Colour Printer**  
Print.



**Xerox® VersaLink® C505 Colour Multifunction Printer**  
Print. Copy. Scan. Fax. Email.



**1 500-sheet output tray** with tray-full sensor (400-sheet capacity on C505).

**2 Card Reader Bay** for internal Card Reader (C500 includes an internal card reader compartment located behind the touch screen).

**3 Optional 250 GB Hard Drive** (standard with the C505/X) increases the capabilities of numerous app-based functions.

**4 A front-side USB port<sup>2</sup>** allows users to quickly print from or scan to<sup>3</sup> any standard USB memory device.

**5 150-sheet Bypass Tray** handles media sizes from 76.2 x 127 mm to 216 x 356 mm.

**6 Tray 1** handles up to 550 sheets with custom sizes of 76 x 190 mm to 216 x 356 mm.

**7 A 100-sheet Single-pass Duplex Automatic Document Feeder (DADF)** scans two-sided originals for copy, scan and fax jobs.

**8 The optional Stand (includes Caster Base)** provides storage for toner cartridges and other supplies.

**9 The High Capacity Feeder (includes Caster Base)** adds up to 2,000 sheets with standard sizes of 216 x 356 mm to 210 x 297 mm.

**10 Add up to 4 additional 550-sheet paper trays** that handle sizes from 76 x 190 mm to 216 x 356 mm (maximum of 2 additional trays with optional cabinet, maximum of 1 additional tray with High Capacity Feeder).

<sup>2</sup> USB ports can be disabled

<sup>3</sup> VersaLink C505 only.

## INTRODUCING TOUCHSCREEN SUPERIORITY.

Meet the industry's most advanced colour touchscreen interface. Whether 7-inch (C505) or 5-inch (C500), it's a user experience that sets a higher standard for customisation, personalisation and versatility.

By presenting a familiar "mobile" experience – with support for gestural input and task-focused apps that share a common look and feel – fewer steps are needed to complete even the most complex jobs.

A highly intuitive layout guides you through every task from start to finish, with a natural hierarchy placing critical functions near the top of the screen and commonly used options front and centre. Don't like where a function or app is located? Customise the layout to make it yours.

This unmatched balance of hardware technology and software capability helps everyone who interacts with the VersaLink C500 Colour Printer and VersaLink C505 Colour Multifunction Printer get more work done, faster.





# Xerox® VersaLink® C500/C505

ConnectKey®  
Technology

The VersaLink C500 Colour Printer and C505 Colour Multifunction Printer are built on Xerox® ConnectKey® Technology. For more information, visit [www.connectkey.com](http://www.connectkey.com).

DEVICE SPECIFICATIONS		VersaLink C500/N	VersaLink C500/DN	VersaLink C505/S	VersaLink C505/X
Speed		Up to 43 ppm			
Duty Cycle <sup>1</sup>		Up to 120,000 pages/month <sup>1</sup>			
Processor/Memory/Hard Drive		1.05 GHz/2 GB/optional 250 GB HDD		1.05 GHz/4 GB/optional 250 GB HDD	1.05 GHz/4 GB/ 250 GB HDD
Connectivity		Ethernet 10/100/1000 Base-T, High-speed USB 3.0, Wi-Fi 802.11n and Wi-Fi Direct with optional Wi-Fi Kit (concurrent wired and wireless connections supported), NFC Tap-to-Pair			
Controller Features		Unified Address Book (C505), Configuration Cloning, Xerox Extensible Interface Platform®, Xerox App Gallery, Xerox® Standard Accounting			
Paper Handling					
Paper Input	Standard	NA		<b>Single-Pass Duplex Automatic Document Feeder (DADF):</b> 100 sheets; Custom sizes: 140 x 140 mm to 216 x 356 mm	
	Optional	<b>Bypass Tray:</b> Up to 150 sheets; Custom sizes: 76 x 127 mm to 216 x 356 mm <b>Tray 1:</b> Up to 550 sheets; Custom sizes: 76 x 190 mm to 216 x 356 mm <b>Up to 4 Additional Trays:</b> Up to 550 sheets; Custom sizes: 76 x 190 mm to 216 x 356 mm <b>High Capacity Feeder:</b> Up to 2,000 sheets; 216 x 356 mm to 210 x 297 mm			
Paper Output	Standard	500 sheets		400 sheets	
Automatic Two-sided Output		N/A	Standard		
Copy and Print	Resolution	Print: Up to 1200 x 2400 dpi		Print: Up to 1200 x 2400 dpi; Copy: Up to 600 x 400 dpi	
First-page-out Time (as fast as)		Print: As fast as 10 seconds colour/8.5 seconds black and white		Print: As fast as 9 seconds colour/9 seconds black and white Copy: As fast as 7 seconds colour/5 seconds black and white	
Page Description Languages		PCL® 5e/PCL 6/PDF/XPS/TIFF/JPEG/HP-GL/Adobe® PostScript® 3™			
INTUITIVE USER EXPERIENCE					
Customise and Personalise		Walkup customisation, Personalise Home Screen by User, Multiple Home Screens with Simple ID, Customise by Site, Function or Workflow with Xerox App Gallery and Xerox® App Studio			
Print Drivers		Job Identification, Bidirectional Status, Job Monitoring, Xerox® Global Print Driver® and Mobile Express Driver®			
Xerox® Embedded Web Server		PC or mobile – Status Information, Responsive Design, Settings, Device Management, Cloning			
Preview		NA		Preview of Scan with Zoom, Rotate, Add Page	Preview of Scan/Fax with Zoom, Rotate, Add Page
Print Features		Print from USB, Secure Print, Sample Set, Personal Print, Saved Job, Xerox® Earth Smart Driver Settings, Job Identification, Booklet Creation, Store and Recall Driver Settings, Bidirectional Real-time Status, Scaling, Job Monitoring, Application Defaults, Skip Blank Pages			
Scan		NA		Optical Character Recognition (OCR), Scan to USB/Email/Network (FTP/SMB), Scan File Formats: PDF, PDF/A, XPS, JPEG, TIFF; Convenience Features: Scan to Home, Searchable PDF, Single/Multi-Page PDF/XPS/TIFF/Password Protected PDF	
Fax <sup>2</sup>		NA		Fax Features (C505/X only): Walk-up Fax (includes LAN Fax, Direct Fax, Fax Forward to Email)	
MOBILE AND CLOUD READY					
Mobile Printing		Apple® AirPrint® <sup>3</sup> , Google Cloud Print™ Ready, Xerox® Print Service and Mopria® Print Service Plug-ins for Android™			
Mobility Options		@PrintByXerox <sup>4</sup> , Xerox® Mobile Print Solution <sup>5</sup> and Xerox® Mobile Print Cloud <sup>5</sup> , Connect via NFC/Wi-Fi Direct Printing <sup>5</sup> , Xerox® Mobile Link App (C505) <sup>6</sup> . Visit <a href="http://www.xerox.com/officemobileapps">www.xerox.com/officemobileapps</a> for available apps.			
Cloud Connectors <sup>4</sup>		Print from/Scan to <sup>7</sup> Google Drive™, Microsoft® OneDrive®, Dropbox™, Microsoft Office 365®, Box®, Xerox® DocuShare® and more			
BENCHMARK SECURITY					
Network Security		IPsec, HTTPS, encrypted email, Network Authentication, SNMPv3, SSL/TLS, Security Certificates, Automatic Self-Signed Certificate			
Device Access		Firmware Verification, User access and internal firewall, Port/IP/Domain Filtering, Audit Log, Access Controls, User Permissions, Smart Card Enabled (CAC/PIV.NET), Integrated Card Reader Bay			
Data Protection		Setup/Security Wizards, Job Level Encryption via HTTPS/IPPS submission, Encrypted hard disk (AES 256-bit, FIPS 140-2) and image overwrite, Common Criteria Certification (ISO 15408) (undergoing evaluation)			
Document Security		Secure Print, Secure Fax (C505/X), Secure Scan (C505), Secure Email (C505), Password Protected PDF (C505)			
ENABLES NEXT GENERATION SERVICES					
Print Management		Xerox® Print Management and Mobility Suite <sup>5</sup> , Configuration Cloning, Xerox® Standard Accounting, Equitrac <sup>5</sup> , Y Soft <sup>5</sup> and more			
Managing Print		Xerox® Device Manager, Xerox® Support Assistance, Auto Meter Read, Managed Print Services tools			
Sustainability		Cisco EnergyWise®, Earth Smart Printing, Print User ID on margins			
GATEWAY TO NEW POSSIBILITIES					
Cloud Services		Xerox® Easy Translator (C505) <sup>5</sup> , CapturePoint™ (C505) <sup>5</sup> , many additional services available			
Xerox App Gallery		Many apps and cloud services available. Visit <a href="http://www.xerox.com/appgallery">www.xerox.com/appgallery</a> for a growing selection of Xerox® apps.			

<sup>1</sup> Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; <sup>2</sup> Analogue phone line required; <sup>3</sup> Visit [www.apple.com](http://www.apple.com) for AirPrint Certification list; <sup>4</sup> Free optional download from Xerox App Gallery to the Printer/MFP; <sup>5</sup> Purchased option; <sup>6</sup> Free download from Google Play or Apple Store <sup>7</sup> Scan to available for C505

## Certifications

To view the latest list of certifications, go to [www.xerox.com/OfficeCertifications](http://www.xerox.com/OfficeCertifications)

## Supplies

Standard Capacity Toner Cartridges:

Black: 5,000 pages <sup>1</sup>	106R03862
Cyan: 2,400 pages <sup>1</sup>	106R03859
Magenta: 2,400 pages <sup>1</sup>	106R03860
Yellow: 2,400 pages <sup>1</sup>	106R03861

High Capacity Toner Cartridges:

Black: 12,100 pages <sup>1</sup>	106R03876
Cyan: 5,200 pages <sup>1</sup>	106R03870
Magenta: 5,200 pages <sup>1</sup>	106R03871
Yellow: 5,200 pages <sup>1</sup>	106R03872

Extra High Capacity Toner Cartridges:

Cyan: 9,000 pages <sup>1</sup>	106R03873
Magenta: 9,000 pages <sup>1</sup>	106R03874
Yellow: 9,000 pages <sup>1</sup>	106R03875
Cyan Drum Cartridge: 40,000 pages <sup>2</sup>	108R01481
Magenta Drum Cartridge: 40,000 pages <sup>2</sup>	108R01482
Yellow Drum Cartridge: 40,000 pages <sup>2</sup>	108R01483
Black Drum Cartridge: 40,000 pages <sup>2</sup>	108R01484
Waste Cartridge: 30,000 pages <sup>2</sup>	108R01416

## Options

1x550-sheet Tray	097S04949
2,000-sheet High Capacity Feeder	097S04948
Stand	097S04955
Caster	097S04954
Wireless Connectivity Kit	497K16750
Productivity Kit	497K18360

## Warranty

One year on site warranty<sup>3</sup>

<sup>1</sup> Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

<sup>2</sup> Approximate pages. Declared yield based on an average job size of 3 A4-size pages. Yield will vary depending on job run length and media size and orientation. For more information, visit [www.office.xerox.com/latest/SUPGL-01.PDF](http://www.office.xerox.com/latest/SUPGL-01.PDF)

<sup>3</sup> Products purchased under a PagePack / eClick agreement do not carry a warranty. Please refer to your service agreement for full details of your enhanced service package.

Configurations vary by geography.

[www.xerox.com](http://www.xerox.com)

