

Model: DXOA 59C3			
Product No: 31008097			
EAN: 8016361947962			
Commodity Code: 84501190			
Replacement: New			
Introduction Date: August 2017			
Key Features			
9kg Load Capacity		Load Capacity	9kg
1500 rpm		Maximum Spin Speed (rpm)	1500
Hoover One Touch (NFC)		KG Mode	Yes
Intelligent Wash System		Colour	White
	Door Colour		Tinted
	Intelligent Wash System		Yes
	Time Manager Display		Yes
	3D Dynamic Wash System		Yes
	Pre-Wash		Yes
	Digital Display		Yes
	Programs		12
	Cottons		Yes
	Mixed		Yes
	Delicates		Yes
	Wool		Yes
	Hand & Silk		Yes
	Lingerie		Yes
	Drain & Spin		Yes
	Rinse		Yes
	Rapid 14 Minute Wash		Yes
	Rapid 30 Minute Wash		Yes
	Rapid 52 Minute Wash		Yes
	Dark Colours		Yes
	Auto Clean		Yes
	Shirts		Yes
	Rinse		Yes
	Drain and Spin		Yes
	Buttons		
	Start/Pause		Yes
	Pre Wash		Yes
	Easy Iron		Yes
Spin Selection		Yes	
Temperature Selection		Yes	
Rapid Length		Yes	
Delay Start		Yes - 24hrs	
Cold Wash Option		Yes	
Technical Specification			
Energy Consumption (kwh/cycle - wash) (full load @ 60 degree)		1.21	
Annual Energy Consumption		218	
Water Consumption (litres/cycle avg 220 washes)		48	
Water Consumption (litres/annum)		10600	
Moisture Content After Spin (% dry load)		44	
Noise dBA (Spin)		80	
Noise dBA (Wash)		61	
Wash Time - full load @ 60 degree		210 mins	
Cold Fill		Yes	
Motor		AC	
Dimensions			
Packed: 70kg			
Unpacked: 68kg			
Weight			
Packed: 890x650x560			
Unpacked: 850x600x520			
Packaging			
Paper, Carton			
PS (Polystyrene)	1.210		
LDPE (Low Density Polythelene)	0.331		
Other Plastic			
Wood	0.160		
Metal - Iron			
Metal - Aluminium			
Glass Shelves			
Performance			
Energy Efficiency	A+++		
Wash Performance	A		
Spin Drying Performance	A		