

Model: DXOC 58AC3			
Product No: 31008101			
EAN: 8016361948006			
Commodity Code: 84501190			
Replacement: New			
Introduction Date: August 2017			
Key Features			
8kg Load Capacity		Load Capacity	8kg
1500 rpm		Maximum Spin Speed (rpm)	1500
14 minuite quick wash		Colour	White
	Door Colour		Chrome
	Intelligent Wash System		Yes
	KG Mode		Yes
	Touch Display		Yes
	NFC		Yes
	WIFI		No
	Display lock		Yes
	Energy		A+++
	Programs - 15		
	Cottons		Yes
	Mixed		Yes
	Delicates		Yes
	Wool		Yes
	Hand & Silk		Yes
	Drain & Spin		Yes
	Rinse		Yes
	Rapid 14 Minute Wash		Yes
	Rapid 30 Minute Wash		Yes
	Rapid 44 Minute Wash		Yes
	Dark Colours		Yes
	All In One 20°		Yes
	All Baby 60°		Yes
	All In One 59 min		Yes
	One Touch		Yes
Buttons			
Temperature Selection		Yes	
Spin Selection		Yes	
Easy Iron		Yes	
Extra Rinse		Yes	
Time Delay		24hrs	
Time Remaining		Yes	
Start & Pause		Yes	
Dimensions			
Packed: 68.5kg			
Unpacked: 66.5kg			
Weight			
Packed: 890x650x560			
Unpacked: 850x600x520			
Packaging			
Paper, Carton		Technical Specification	
PS (Polystyrene)	1.210	Energy Consumption (kwh/cycle - wash) (full load@ 60 degree)	1.07
LDPE (Low Density Polythelene)	0.331	Annual Energy Consumption	196
Other Plastic		Water Consumption (litres/annum)	9850
Wood	0.160	Water Consumption (litres/cycle 220 washes)	45
Metal - Iron		Moisture Content After Spin (% dry load)	44
Metal - Aluminium		Noise dBA	80
Glass Shelves		Noise dBA	61
		Wash Time - full load @ 60 degree (short programme)	210
Performance			
Energy Efficiency	A+++	Cold Fill	Yes
Wash Performance	A	Electrical Supply (volts)	230
Spin Drying Performance	A	Rated Loads (watts)	2150
		Motor	Digital AC