# Lenovo™ ThinkCentre M715 TW SFF

# THE POWER TO DRIVE YOUR BUSINESS

Powerful, reliable, secure... ThinkCentre M715 TW SFF boosts efficiency and productivity—and grows in line with your business.

Designed to deliver outstanding performance and manageability—ThinkCentre M715 tower (TW) and Small Form Factor (SFF) meets the most demanding content creation and multi-media tasks. Featuring the latest 7<sup>th</sup> generation AMD processors and DDR4 memory, plus optional PCle SSD—you'll experience fast boot up times, open files faster than ever and avoid frustrating delays. Together with built-in security to protect your data, and cost-saving upgrade options—ThinkCentre M715 TW SFF empowers your workforce, and improves your organization's efficiency and productivity.

# WHY YOU SHOULD BUY THE LENOVO™ THINKCENTRE M715 TW SFF



# **Big on Power**

Enjoy huge power from your desktop with a ThinkCentre tower (TW) or small form factor (SFF)—with up to the latest 7th generation AMD processors and DDR4 memory. Plus, PCIe SSD with 3D NAND technology improves SSD endurance by 10 times—so you can rely on ThinkCentre to handle demanding tasks with ease. (\*SSD with 128 GB and above capacity are with 3D NAND technology)



# Management Made Easy

AMD DASH technology



# **Protect Critical Data**

TPM 2.0 bolsters security, protecting your ThinkCentre in case it falls into the wrong hands.



# **Expands With Your Business**

Easy to customize, you can choose components such as the CPU, memory, HDD and graphics card—and upgrade them as your needs change. What's more, with a wide array of ports, you can connect the devices and peripherals you need as your business grows.



# **Defence Against Dust**

Workshop or regular office—dust build-up affects computer performance. ThinkCentre TW SFF optional Dust Shield reduces dust intake by up to 42%, improving reliability and protecting your assets.



# THE LENOVO™ THINKCENTRE M715 TW SFF IS BEST SUITED FOR?



Progressive IT decision makers who recognise technological performance as integral to empowering their business



Busy professionals requiring desktop-standard performance with plenty of horsepower and upgrade options



IT managers who value the agility to extend and replace components as resource requirements evolve





# Lenovo™ ThinkCentre M715 TW SFF

# WHAT'S IN A THINKCENTRE®









# **SPECIFICATIONS**

# Lenovo™ ThinkCentre M715 TW SFF

# **PERFORMANCE**

### **Operating System**

Windows 10 Pro

Windows 10 Pro downgrade Windows 7 (only available with Carrizo DDR4 processor)

### Processor

AMD Summit Ridge Ryzen 7, Ryzen 5, Ryzen 3

AMD Bristol Ridge PRO A12, A10, A8, A6 AMD Carrizo DDR4 PRO A12, A10, A6

### Storage

1 x 2280 M.2 PCIe SSD

2 x 3.5" HDD on TWR; 1 x 3.5" + 1 x optional

1x Slim ODD

### Memory

Up to 64 GB 4 DDR4 UDIMM 2400MHz

### Power Adapter

210W 92% (for Spb)

210W 85%

180W 85%

# Graphics

Integrated Radeon

Geforce 730 2 GB

# **SECURITY**

HW TPM2.0

Kensington Lock

Padlock

KB/MS lock

# CONNECTIVITY

2 x USB 3.1 Gen2

2 x USB 3.1 Gen1

Optional 2 x USB 3.1 Gen2 Type-C

Optional card reader

2 x audio

### Rear I/O

2 x USB 3.1 Gen1

2 x USB 2.0

1 x VGA

2 x DP

1 x Serial, Optional 2nd serial

1 x LAN

3 x Audio

2 x PS2

Optional Parallel

# WiFi & Bluetooth®

# **DESIGN**

## **Dimensions**

292.7 mm x 145 mm x 366 mm

Small Form Factor:

290.5 mm x 92.5 mm x 343.5 mm

# Weight

Tower: 6.5 kg

SFF: 6 kg

# Ease of Use (Too-less Access)

Tower: No

Small Form Factor: Yes

# **SOFTWARE**

### Windows 10 Preloads

Cyberlink PowerDVD (optional)

Cyberlink PowerDVD Create, Power2Go and Power Producer (optional)

Lenovo Companion

Lenovo ID

Lenovo ThinkVantage Tools

Microsoft Office 2016 (Trial)

### Windows 7 Preloads

Adobe Reader

Create Recovery Media

Cyberlink PowerDVD (optional)

Cyberlink PowerDVD Create, Power2Go and

Power Producer (optional)

Lenovo Solution Center

Lenovo ThinkVantage Tools

Microsoft Office 2016

Internet Explorer

# **GREEN CERTIFICATION**

Energy Star 6.1

EPEAT Gold certified\*

(Note: Applicable in North America)

UL GreenGuard certified

Frp lot 3 verified

\*Note: Type-C port with USB data function <sup>1</sup> TBR Large Enterprise Repair Rate Study 2011. <sup>2</sup> CPU Socket is not included.

# RECOMMENDED SERVICES

Lenovo offers a comprehensive portfolio of services to support and protect your investment. Succeed with substance and let Lenovo Service support you all the way.

## PRIORITY TECHNICAL SUPPORT

Makes your priority, our priority. 24 x 7 priority call routing to advanced-level technicians, electronic incident tracking, and escalation management services

# WARRANTY UPGRADES-ON-SITE AND

MEXT BUSINESS DAY
Maximizes PC uptime and productivity by
providing convenient and fast repair service
at your place of business.

### WARRANTY EXTENSIONS (1-3 YEARS TOTAL DURATION)

TOTAL DURATION)
This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment, and lower the cost of ownership over time.

ACCIDENTAL DAMAGE PROTECTION
Avoid the hassles of unexpected repair
costs. Provides coverage for non-warranted
damage incurred under normal operating conditions, such as minor spills, drops, or damage to the integrated screen

# KEEP YOUR DRIVE

Retain your drive if it should happen to fail, giving you the peace of mind of knowing that your valuable data is secure.

# ASSET TAGGING

Systems come equipped with a professional, flexible asset tag based on your exact specifications. PCs are easily identifiable and trackable right out of the box.





# WWW.LENOVO.COM

