

Cisco UCS B200 M5 Blade Server



For remote sites or data centers, the enterprise-class Cisco UCS[®] B200 M5 Blade Server delivers market-leading performance, versatility, and density without compromise for workloads ranging from web infrastructure to distributed databases.

Product overview

The Cisco UCS B200 M5 Blade Server delivers performance, flexibility, and optimization for deployments in data centers, in the cloud, and at remote sites. This enterprise-class server offers market-leading performance, versatility, and density without compromise for workloads including Virtual Desktop Infrastructure (VDI), web infrastructure, distributed databases, converged infrastructure, and enterprise applications such as Oracle and SAP HANA. The B200 M5 server can quickly deploy stateless physical and virtual workloads through programmable, easy-to-use [Cisco UCS Manager](#) software and simplified server access through Cisco [SingleConnect](#) technology. It includes:

- Latest Intel[®] Xeon[®] Scalable processors with up to 28 cores per socket
- Up to 24 DDR4 DIMMs for improved performance
- Two GPUs
- Two Small-Form-Factor (SFF) drives
- Two Secure Digital (SD) cards or M.2 SATA drives
- Up to 80 Gbps of I/O throughput

Main features

The Cisco UCS B200 M5 server is a half-width blade. Up to eight servers can reside in the 6-Rack-Unit (6RU) Cisco UCS 5108 Blade Server Chassis, offering one of the highest densities of servers per rack unit of blade chassis in the industry. You can configure the B200 M5 to meet your local storage requirements without having to buy, power, and cool components that you do not need.

The B200 M5 provides these main features:

- Up to two Intel Xeon Scalable CPUs with up to 28 cores per CPU
- 24 DIMM slots for industry-standard DDR4 memory at speeds up to 2666 MHz, with up to 3 TB of total memory when using 128-GB DIMMs
- Modular LAN On Motherboard (mLOM) card with Cisco UCS Virtual Interface Card (VIC) 1340, a 2-port, 40 Gigabit Ethernet, Fibre Channel over Ethernet (FCoE)–capable mLOM mezzanine adapter
- Optional rear mezzanine VIC with two 40-Gbps unified I/O ports or two sets of 4 x 10-Gbps unified I/O ports, delivering 80 Gbps to the server; adapts to either 10- or 40-Gbps fabric connections
- Two optional, hot-pluggable, Hard-Disk Drives (HDDs), Solid-State Disks (SSDs), or NVMe 2.5-inch drives with a choice of enterprise-class RAID or passthrough controllers
- Cisco FlexStorage local drive storage subsystem, which provides flexible boot and local storage capabilities and allows you to boot from dual, mirrored SD cards
- Support for up to two optional GPUs
- Support for up to one rear storage mezzanine card

Product specifications

Table 1 lists the specifications for the Cisco UCS B200 M5 Blade Server.

Table 1. Specifications

Item	Specifications
Processors	Up to 2 Intel Xeon Scalable processors (1 or 2)
Memory	24 DDR4 DIMM slots: 16, 32, 64, and 128 GB at up to 2666 MHz
mLOM	mLOM slot for Cisco UCS VIC 1340
Mezzanine adapter (rear)	1 rear mezzanine adapter for: <ul style="list-style-type: none"> • Cisco UCS VIC 1380 mezzanine card • Cisco port expander mezzanine card • Cisco GPU rear mezzanine card • Cisco blade NVMe storage card
Mezzanine adapter (front)	1 front mezzanine adapter for: <ul style="list-style-type: none"> • Cisco FlexStorage 12-Gbps SAS RAID Controller • Cisco FlexStorage 12-Gbps SAS RAID Controller with 1-GB cache • Cisco FlexStorage NVMe or passthrough module • Cisco GPU front mezzanine card
Internal storage	2 hot-pluggable front-access 2.5-inch drives: <ul style="list-style-type: none"> • HDD: 10,000 or 15,000 rpm with up to 1.8 TB per drive • SSD: Enterprise Performance and Value SSDs with up to 7.6 TB per drive • NVMe: Up to 7.7 TB per drive <p>Note: Drives require a RAID or passthrough controller in the front mezzanine adapter slot.</p> <p>Choice of either:</p> <ul style="list-style-type: none"> • 2 internal SD cards (32, 64, or 128 GB) • 2 M.2 SATA drives (240 or 960 GB)
Management	Cisco Intersight™

Item	Specifications
	Cisco UCS Manager Release 3.2(1) Cisco UCS Central Software Cisco UCS Director Cisco UCS Performance Manager
Temperature: Operating	50 to 95° F (10 to 35° C)
Temperature: Nonoperating:	-40 to 149° F (-40 to 65° C)
Humidity: Operating	5 to 93% noncondensing
Humidity: Nonoperating	5 to 93% noncondensing
Altitude: Operating	0 to 10,000 ft (0 to 3000m); maximum ambient temperature decreases by 1° C per 300m
Altitude: Nonoperating	40,000 ft (12,000m)

System requirements

Table 2 lists system requirements for the server.

Table 2. System requirements

Item	Requirements
Blade chassis	Cisco UCS 5108 Blade Server Chassis
Fabric interconnect	Cisco UCS 6248UP 48-Port, 6296UP 96-Port, 6332-16UP, 6332, and 6324 Fabric Interconnects
Fabric extender	Cisco UCS 2204, 2208, and 2304 Fabric Extenders
Cisco UCS Manager software	Release 3.2(1) or later

Ordering information

Table 3 provides ordering information for the Cisco UCS B200 M5.

Table 3. Ordering information

Part number	Description
UCSB-B200-M5	UCS B200 M5 Blade w/o CPU, mem, HDD, mezz
UCSB-B200-M5-U	UCS B200 M5 Blade w/o CPU, mem, HDD, mezz (UPG)
UCSB-B200-M5-CH	DISTI:UCS B200 M5 w/o CPU, mem, Drive bays, HDD, mezz, HS

For information about installing or upgrading your server, see the [Cisco UCS B200 M5 hardware installation guide](#).

For ordering information, see the [Cisco UCS B200 M5 Blade Server specification sheet](#).

Warranty information

Cisco UCS B200 M5 Blade Servers have a 3-year Next-Business-Day (NBD) hardware warranty and 90-day software warranty.

Augmenting the Cisco Unified Computing System™ (Cisco UCS) warranty, Cisco Smart Net Total Care™ and Cisco Solution Support services are part of Cisco's technical services portfolio. Cisco Smart Net Total Care combines Cisco's industry-leading and award-winning foundational technical services with an extra level of actionable business intelligence that is delivered to you through the smart capabilities in the Cisco Smart Net Total Care portal. For more information, please refer to <https://www.cisco.com/c/en/us/support/services/smart-net-total-care/index.html>.



Solution Support includes both Cisco product support and solution-level support, resolving complex issues in multivendor environments on average 43 percent more quickly than with product support alone. Solution Support is a critical element in data center administration, helping rapidly resolve any issue encountered while maintaining performance, reliability, and return on investment.

This service centralizes support across your multivendor Cisco environment for both our products and solution partner products you've deployed in your ecosystem. Whether there is an issue with a Cisco or solution partner product, just call us. Our experts are the primary point of contact and own the case from first call to resolution. For more information, please refer to <https://www.cisco.com/c/en/us/services/technical/solution-support.html>.

Cisco and partner services

Cisco and our industry-leading partners deliver services that accelerate your transition to a Cisco UCS B-Series Blade Servers solution. Cisco Unified Computing Services can help you create an agile infrastructure, accelerate time to value, reduce costs and risks, and maintain availability during deployment and migration. After deployment, our services can help you improve performance, availability, and resiliency as your business needs evolve and help you further mitigate risk. For more information, visit <https://www.cisco.com/go/unifiedcomputingservices>.

Cisco Capital financing to help you achieve your objectives

Cisco Capital[®] financing can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce Capital Expenditures (CapEx), accelerate your growth, and optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital financing is available in more than 100 countries. [Learn more.](#)

For more information

For more information about Cisco UCS servers, refer to <https://www.cisco.com/go/ucs>.

Americas Headquarters

Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters

Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters

Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)