

SmartOnline SV Series 40kVA Large-Frame Modular Scalable 3-Phase On-Line Double-Conversion 208/120V 50/60 Hz UPS System

MODEL NUMBER: **SV40KL**



3-phase 40kVA UPS system offers network-grade power protection in a highly configurable, modular and scalable large-chassis rack-width frame. Pre-installed WEBCARDLX network interface allows full remote access 24/7.

Description

The SV40KL SmartOnline® SV Series 40kVA 3-Phase On-Line Double-Conversion UPS System delivers true scalability and offers the highest level of secure, uninterrupted power protection. Featuring a modular, scalable design with high-efficiency voltage and frequency independent (VFI) operation, this on-line UPS system is ideal for protecting a variety of critical IT systems.

The SV40KL includes preinstalled input, bypass and output breakers, as well as a static transfer switch (STS) and two included 20kVA SV20PM power modules. Space is included for up to six additional user-installable SV20PM power modules to accommodate increased capacity up to 140kVA with N+1 fault tolerance. Each power module is rated at 0.9 power factor for maximum power to the connected load.

The Java-free HTML5-based WEBCARDLX interface enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

With up to 92% efficiency in standard mode and up to 99% efficiency in optional economy mode, this 40kVA UPS system helps you reduce operating and cooling costs. Automatic and manual bypass options keep connected equipment operational during routine maintenance or critical power module failure. Batteries are not included. External ± 120 VDC battery cabinets, such as Tripp Lite's BP240V370, are sold separately.

Features

Highlights

- Scalable capacity up to 140kVA with N+1 redundancy
- Economy mode option helps reduce operating and cooling costs
- Pre-installed WEBCARDLX network interface for 24/7 remote access
- DSP/IGBT technology and 1% output voltage regulation
- Batteries not included; external battery cabinets sold separately

Package Includes

- SV40KL SmartOnline SV Series 40kVA 3-Phase On-Line Double-Conversion UPS System
- Pre-installed WEBCARDLX network interface
- (2) SV20PM 20kVA power modules (shipped separately)
- Owner's manual



40kVA 36kW 3-Phase Large-Chassis UPS System

- Supports 208/120V or 220/127V AC 50/60Hz Wye 4-wire plus Earth hardwire input and output wiring
- Dual hardwire input design enables operation from up to 2 power sources
- Network-grade sine-wave AC output with 1% output voltage regulation and less than 1.5% output total harmonic distortion
- Tested to UL 1778 (U.S.), CSA (Canada) and NOM (Mexico) standards
- High 0.9 power factor for maximum power to the connected load
- Batteries not included—external ± 120 VDC battery cabinets, such as Tripp Lite's BP240V370, sold separately

Pre-Installed WEBCARDLX Network Interface

- Allows full remote access for power monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH
- Supports 10/100 Mbps auto-sensing for communication with an Ethernet network
- Optional EnviroSense2 sensors (sold separately) enable site monitoring of temperature, humidity and contact-closure status
- No Java required

Modular, Scalable Design for Maximum Flexibility

- Modular configuration with hot-swappable power modules enables easy and fast maintenance with zero downtime
- Open slots for up to 6 additional 20kVA SV20PM power modules accommodate increased capacity up to 140kVA with N+1 fault tolerance

Optional Economy Mode

- Up to 99% efficient in optional economy mode to lower operating and cooling costs

Wide Input/Narrow Output Voltage Operating Range

- Enables full continuous online operation during brownouts as low as 156V and overvoltages up to 253V
- Regulates output voltage within 1% of the selected nominal output voltage in on-line double-conversion mode

Advanced IGBT Inverter with Digital Signal Processor (DSP) Technology

- Provides for less than 3% input total harmonic distortion (THDi) to support 1:1 generator sizing and prevent the need to oversize generator systems relative to UPS capacity

Automatic and Manual Bypass Options

- Keep connected equipment operational during routine maintenance or critical power module failure

Specifications

OVERVIEW	
UPC Code	037332210289
UPS Type	On-Line
INPUT	



Rated input current (Maximum Load)	SV40KL 40kVA Configuration: 120A; Maximum 140kVA Large Chassis Configuration: 420A; 330A maximum inrush current
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Nominal Input Voltage Description	Set of two hardwire input connections enables 3-Phase Wye, 4 wire (3P, N, G) inputs from two separate power sources
UPS Input Connection Type	Hardwire
Input Circuit Breakers	MAIN and ALTERNATE AC inputs are each protected by 630A 3 pole magnetic breakers
Input Phase	3-Phase
Input Frequency	40 to 70Hz (online mode); 50/60Hz Auto-selectable
Power Factor (Input)	Greater than 0.99 (full load)
THDi	Less than 3% (full linear load)
OUTPUT	
Output Volt Amp Capacity (VA)	40000
Output Capacity (kVA)	40
Output Watt Capacity (Watts)	36000
Output kW Capacity (kW)	36
Output Capacity Details	OVERLOAD CAPABILITY: Supports 105-110% load for 1 hour, 111-125% load for 10 minutes, 126-150% for 1 minute and Over 150% for 200ms before switching to Bypass; Online operation resumes when load is reduced to 100% or less
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	Output THD full resistive load: <1.5%; Output THD non-linear load: <4%; Max DC offset: $\pm 50\text{mV}$; Max Phase angle deviation: 2°; Max Voltage unbalance deviation: 1%; Output short-circuit protection included
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Auto-selectable, user adjustable
Output Receptacle Details	Output wiring: 3P, N, E
Output Circuit Breakers	630A 3 pole magnetic breaker
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Output Receptacles	Hardwire
Output Voltage Regulation	ONLINE, FREQUENCY CONVERSION, BATTERY MODE: 208/120, 220/127 $\pm 1\%$ typical (balanced load); $\pm 2\%$ typical (unbalanced load); ECONOMY MODE: 208/120, 220/127 $\pm 15\text{V}$; BYPASS MODE: +15% (default, adjustable to +10%, +15% or +20%), -20% (default, adjustable to -10%, -20%, -30%)



Tripp Lite
 1111 W. 35th Street
 Chicago, IL 60609 USA
 Telephone: 773.869.1234
www.tripplite.com

Output Frequency Regulation	ONLINE MODE: Output frequency is $\pm 0.05\text{Hz}$ of input frequency when input is within $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; Output frequency is $\pm 0.05\text{Hz}$ the configured 50/60Hz output setting when input is outside $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; BATTERY MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; FREQUENCY CONVERTER MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; ECONOMY MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (UPS switches to Online mode if frequency goes outside of this range); BYPASS MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (switches to STANDBY mode if frequency goes outside of this range). *The TRACKING RANGE is factory set to $\pm 4\text{Hz}$ and is user adjustable to $\pm 1\text{Hz}$, $\pm 2\text{Hz}$ or $\pm 4\text{Hz}$; The selected TRACKING RANGE setting controls frequency output tolerances as described above in Online, Economy and Bypass modes
Output Amp Capacity	Output Amp Capacity 111A (208/120V); 105A (220/127V)
Individually Controllable Load Banks	No
Modular Upgrade Options	Includes 2 SV20PM 20kVA power modules. Up to 6 additional SV20PM 20kVA power modules can be added for additional capacity or N+1 availability; Add 1 SV20PM for 60kVA capacity (or 40kVA with N+1 redundancy); Add 2 SV20PM for 80kVA capacity (or 60kVA with N+1 redundancy); Add 3 SV20PM for 100kVA capacity (or 80kVA with N+1 redundancy); Add 4 SV20PM for 120kVA capacity (or 100kVA with N+1 redundancy); Add 5 SV20PM for 140kVA capacity (or 120kVA with N+1 redundancy); Add 6 SV20PM for 140kVA total capacity with N+1 redundancy
BATTERY	
Full Load Runtime (min.)	Batteries sold separate; Runtime is dependent on battery pack quantity and load level
Expandable Battery Runtime	Supports extended runtime with optional external battery packs; 200A 3 pole 250VDC breaker recommended for external battery
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied
External Battery Pack Compatibility	<p> BP240V370 BP240V370NB EBP240V2501 EBP240V2501NB EBP240V2502 EBP240V2502NB EBP240V3501 EBP240V3501NB EBP240V3502 EBP240V3502NB EBP240V5001 EBP240V5001NB EBP240V5002 EBP240V5002NB EBP240V6002 EBP240V6002NB EBP240V6003 EBP240V6003NB </p>
DC System Voltage (VDC)	$\pm 120\text{VDC}$
Battery Recharge Rate (Included Batteries)	User selectable charging current of 1A to 16A (2A factory setting); Recharge rate is dependent on number of external battery packs connected and the selected charge current setting
Battery Replacement Description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning



Overvoltage Correction	Maintains continuous output in online mode, without using battery power, during overvoltages to 253V (Ph-Ph), reducing output to within 1% of selected 208/120V, 220/127V nominal output voltage
Undervoltage Correction	Maintains continuous output in online mode, without using battery power, during brownout/undervoltage conditions to 156V (Ph-Ph) at full load and to 121V (Ph-Ph) at 70% output load or less, increasing output to within 1% of selected 208/120V or 220/127V nominal output voltage
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	145mm front panel LCD display with directional scroll and select buttons offers complete operating status display, plus setting and selection options for all UPS functions
Switches	Front panel buttons include ESC (menu escape), UP/LEFT (menu up / left), DOWN/RIGHT (menu down / right), ENTER (confirm selection), HOME (return to home screen) and POWER (on/off power control); Also includes Manual Bypass switch
Alarm Cancel Operation	Audible alarms can be muted using on-screen prompts
Audible Alarm	Unique audible alarms for POWER ON / POWER OFF (alarm sounds for 2 seconds), BATTERY MODE (alarm sounds every 2 seconds), LOW BATTERY (alarm sounds every 0.5 seconds), UPS ALARM (alarm sounds every 1 second), UPS FAULT (continuous alarm)
LED Indicators	Front panel LED indicators represent INPUT (green), BYPASS (amber), INVERTER (green), BATTERY (red) and ALARM (red)
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	2496
AC Suppression Joule Rating Details	2496 joules (Ph-Ph), 2496 joules (Ph-N), 1872 joules (N-E)
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Tower
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary UPS Depth (mm)	1,100
Primary UPS Height (mm)	2,010
Primary UPS Width (mm)	600
Shipping Dimensions (hwd / cm)	138.43 x 72.39 x 107.95
Shipping Dimensions (hwd / in.)	54.50 x 28.50 x 42.50
Shipping Weight (kg)	479.90
Shipping Weight (lbs.)	1058.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	200.99 x 59.99 x 109.98
UPS Power Module Dimensions (hwd, in.)	79.13 x 23.62 x 43.3



UPS Power Module Weight (kg)	342.01
UPS Power Module Weight (lbs.)	754
ENVIRONMENTAL	
Operating Temperature Range	0° to +40°C (+32° to +104°F); De-rates to 90% capacity at 35°C / 95°F and 80% capacity at 40°C / 104°F
Storage Temperature Range	-15° to +60°C (+5° to +140°F)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	11075
AC Economy Mode BTU / Hr. (Full Load)	766
AC Economy Mode Efficiency Rating (100% Load)	99%
Audible Noise	Less than 73 DBA front-side, 1m
Operating Elevation (m)	Up to 1000m (At elevations over 1000m, output de-rates by 1% per 100m)
COMMUNICATIONS	
Network Management Cards	 WEBCARDLX ; MODBUSCARDSV ; RELAYCARDSV ;
Network Monitoring Port Description	Includes pre-installed Tripp Lite WEBCARDLX network interface
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	DB9 cabling included
SNMP Compatibility	Includes pre-installed WEBCARDLX ; network interface card
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode; Less than 20 ms. transfer time in economy mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to to 156V (Ph-Ph) Full load or 121V (Ph-Ph) 70% load or less; Below the low transfer voltage point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 253V (Ph-Ph), reducing output within 1% of nominal; Above this point, output is maintained utilizing reserve battery power
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Hot swappable UPS power module; Auto Probe Monitoring (included); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; High efficiency economy mode operation; Schedulable daily hours of economy mode operation



STANDARDS & COMPLIANCE	
UPS Certifications	ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
Certification Details	UL1778: 2014 5th Edition; CSA C22.2 No. 107.3.14; FCC Part 15 Class A
WARRANTY	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	Tripp Lite 3-Phase UPS Factory Warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>