

## MSA Uncoded Compatible 1m 40G QSFP+ to 4x SFP+ Direct Attach Breakout Cable Twinax - 40GbE QSFP+ to 4x SFP+ Copper DAC 40 Gbps Low Power Passive Transceiver Module DAC

**Product ID:** QSFP4SFPPC1M

The QSFP4SFPPC1M is an MSA Compliant QSFP+ direct-attach Twinax breakout cable. It is designed, programmed and tested to bridge 40G network equipment with 10G compatible servers or routers. This passive Twin axial cable connects a single QSFP+ port to four 10G SFP+ ports and is fully hot-pluggable making upgrades and replacements seamless by minimizing network disruptions.

At 1 meters long and designed for short-length, high-speed interconnects, this low-power, low-latency copper QSFP+ cable also uses a cost-effective cabling alternative to fiber-optic assemblies. It supports short-distance applications such as point-to-point in-rack and across-rack network switch or server connections, for up to four 10G SFP+ devices.

All StarTech.com QSFP & QSFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

### Certifications, Reports and Compatibility



### Applications

- Point-to-point in-rack server or network switch connections, for up to four devices
- Use in 40Gb/10Gb mixed Ethernet network applications

### Features

- **MSA UNCODED QSFP+ CABLE (DAC):** 40Gb direct attach cable works with MSA compliant switches the accept uncoded transceivers and modules
- **TECHNICAL SPECS:** 1m (3.3ft) 40 Gbps Passive Twinax (Copper) 1x QSFP+ to 4x SFP+ Pluggable Connector 100 Ohm Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant
- **DESIGNED FOR SERVER ROOMS:** This DAC is a cost-effective copper alternative to fiber cable inside & between racks; factory termination means high performance & reliability with less maintenance.
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM support and with access to our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 40GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers

---

<b>Hardware</b>	Warranty	90 Days
	Compatible Brand	MSA Compliant
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Type	Passive Copper Cable

---

<b>Performance</b>	Maximum Data Transfer Rate	40Gbps for QSFP+ / 10Gbps for SFP+
	Impedance	100 Ohm
	Compatible Networks	40 Gbps
	Power Consumption (In Watts)	< 0.1 W (per end)
<b>Connector(s)</b>	Connector A	QSFP+
	Connector B	SFP+
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 80C (-40F to 158F)
<b>Physical Characteristics</b>	Product Length	39.4 in [10.0 cm]
	Product Width	0.6 in [14.000 mm]
	Product Height	0.5 in [12.000 mm]
	Weight of Product	8.4 oz [238.000 g]
<b>Packaging Information</b>	Package Length	9.1 in [2.3 cm]
	Package Width	8.1 in [2.1 cm]
	Package Height	0.6 in [15.000 mm]
	Shipping (Package) Weight	2.8 oz [80.000 g]
<b>What's in the Box</b>	Included in Package	QSFP+ to 4x SFP+ cable

*\*Product appearance and specifications are subject to change without notice.*

