

# EB-X41

## DATASHEET



Create the big-screen experience with this high-quality, long-lasting and flexible projector for the home and office, with XGA resolution.

Here's a projector the whole family can enjoy; from watching box sets to delivering sharp presentations, this XGA projector has the tools for the job. There's no need to worry about ambient light; it produces a bright and clear display with 3,600 lumens and 3LCD technology. It's also easy to transport and set up. And its incredibly long lamp life means it's great value for money.

### Bigger is better

Whether you're watching your favourite blockbusters or delivering a presentation, this projector can achieve an impressive 300-inch display. It's great quality too, with 3LCD technology that makes the display up to three times brighter than competitor products<sup>2</sup>. In addition to its bright and vivid colours, the 15,000:1 contrast ratio produces defined shadows and deep blacks. From family and friends to business colleagues and clients, it's sure to get everyone's attention.

### High-quality, bright images

Even in bright rooms, this powerful yet affordable XGA projector delivers exceptionally bright yet colourful images with clear details. It's all thanks to 3LCD technology, which produces an equally high White and Colour Light Output of 3,600 lumens.

### Long-lasting solution

Looking for a long-term, hassle-free and affordable solution for your projection needs? With this model's long-lasting lamp light source, you could watch a film every day for 15 years<sup>1</sup>.

### Stress-free set up

Here's a projector that's designed with portability and quick set up in mind. The carry case makes it easy to move from room to room, and you can quickly position the image with keystone correction and access content simply with the HDMI inputs. With the optional ELPAP10 adapter, it offers Wi-Fi connectivity, allowing you to share content from a smart device using the iProjection app.

## KEY FEATURES

- **Create the big screen experience**  
From box sets to business presentations, capture everyone's attention
- **Bright even with ambient light**  
Equally high White and Colour Light Output of 3,600 lumens
- **Affordable, high-tech equipment**  
Enjoy this XGA projector
- **Long-lasting solution**  
Watch a film every day for 15 years<sup>1</sup>
- **Portable and quick to set up**  
Transport with a carry case and keystone slider for easy alignment



Source: Futuresource Consulting Ltd.

**EPSON®**  
EXCEED YOUR VISION

## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.55 inch with MLA (D10)

### IMAGE

Colour Light Output	3,600 lumen- 2,235 lumen (economy) In accordance with IDMS15.4
White Light Output	3,600 lumen - 2,235 lumen (economy) In accordance with ISO 21118:2012
Resolution	XGA, 1024 x 768, 4:3
Contrast Ratio	15,000 : 1
Lamp	UHE, 210 W, 6,000 h durability, 10,000 h durability (economy mode)
Keystone Correction	Auto vertical: ± 30 °, Manual horizontal ± 30 °
Colour Reproduction	Up to 1.07 billion colours
Aspect Ratio	4:3

### OPTICAL

Projection Ratio	1.48 - 1.77:1
Zoom	Manual, Factor: 1.2
Image Size	30 inches - 300 inches
Projection Distance Wide/Tele	1.8 m - 2.17 m ( 60 inch screen)
Projection Lens F Number	1.49 - 1.72
Focal Distance	16.9 mm - 20.28 mm
Focus	Manual
Offset	8 : 1

### CONNECTIVITY

USB Display Function	2 in 1: Image / Mouse
Interfaces	USB 2.0 Type A, USB 2.0 Type B, VGA in, HDMI in, Composite in, Cinch audio in, Wireless LAN IEEE 802.11b/g/n (optional)
Epson iProjection App	Ad-Hoc / Infrastructure

### ADVANCED FEATURES

Security	Kensington lock, Security cable hole, Wireless LAN unit lock, Password protection
3D	No
Features	AV mute slide, Automatic keystone correction, Built-in speaker, Horizontal and vertical keystone correction, Long lamp life, Quick Corner
Video Colour Modes	Blackboard, Cinema, Dynamic, Presentation, sRGB

### GENERAL

Energy Use	282 W, 203 W (economy), 0.2 W (standby), On mode power consumption as defined in JBMS-84 257 W
Product dimensions	302 x 237 x 82 mm (Width x Depth x Height)
Product weight	2.5 kg
Noise Level	Normal: 37 dB (A) - Economy: 28 dB (A)
Loudspeaker	2 W
Colour	White

### OTHER

Warranty	24 months Carry in, Lamp: 12 months or 1,000 h Optional warranty extension available
----------	---

## EB-X41

### WHAT'S IN THE BOX

- Main unit
- Power cable
- Quick Start Guide
- Remote control incl. batteries
- User manual (CD)
- Warranty card
- Carrying Case

**EPSON®**

## OPTIONAL ACCESSORIES

EB-X41

- Wireless LAN Adapter - ELPAP10  
V12H731P01
- ELPLP96  
V13H010L96
- Air Filter - ELPAF32  
V13H134A32
- Soft Carry Case - ELPKS69 - EB-x05/x41/x42, EH-TW6 series  
V12H001K69
- Screen (80" Pantograph 16:10) - ELPSC24  
V12H002S24
- Ceiling Pipe (700mm) - ELPFP14  
V12H003P14
- Ceiling Pipe (450mm) - ELPFP13  
V12H003P13
- Ceiling Mount (White) - ELPMB23  
V12H003B23

## LOGISTICS INFORMATION

SKU	V11H843041
EAN code	8715946639567
Dimensions Single Carton	335 x 380 x 160 mm
Carton Weight	3.74 Kg
Country of Origin	Philippines
Pallet Size Euro	78 Units (6 x 13)
Pallet Size Block	78 Units (6 x 13)



HDMI HDMI

For more information please contact:

Home users: 0343 90 37766

Web: [www.epson.co.uk](http://www.epson.co.uk)

Business users\*: 0871 42 37766

[www.epson.ie](http://www.epson.ie)

Republic of Ireland: 01 436 7742

Or visit us at <https://www.epson.co.uk/contactus>

\* 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.

1. Based on watching an average 1hr 45mins film every day and the lamp set in Eco mode.
2. Colour brightness (Colour Light Output) in brightest mode, measured by a third-party lab in accordance with IDMS 15.4. Colour brightness will vary depending on usage conditions. Top-selling Epson 3LCD projectors versus top selling 1-chip DLP projectors based on PMA research sales data for Dec 2015 through Nov 2016.

EPSON®