



HSM shredstar Document Shredders

Product Overview

Data protection? Important for everyone.



Your security system protects your valuable possessions.



Your fire alarm lets you know if something is getting too hot.



Your firewall stops intrusions into your pc.

So how do you protect your personal data?

Danger zone waste bin. You've thought about using a firewall and encrypting your data – but what about the confidential documents in your waste bin and the data they contain?

How do you dispose of invoices, tax documents, salary sheets or old credit cards? Crumpled up or cut with scissors in the waste bin? Then the door is wide open for spies and data misuse and you are risking a significant image or financial loss.

Are you sure that your tax documents can't get into your neighbour's hands?

**Put your trust in one thing:
an HSM shredstar document shredder!**



*Here you can see what used to be:
the tax returns,
2 confidential letters
1 DVD with private photos and
2 expired credit cards.*



HSM shredstar document shredders

Stylish – good value – secure: combine style and security with the trendy HSM shredstar document shredders for the home or small office.



Benefits:

- Quiet operation minimises noise development in the workplace.
- Light barrier for automatic start/stop.
- Effortless emptying of the waste container via the removal housing top.
- Level indicator through inspection window in the waste container (from HSM shredstar S10).
- Separate CD cutting unit with own waste container for sorted disposal (from HSM shredstar S10).



LED indicator shows the device's operating status (from HSM shredstar S10).



Simple destruction of CDs from HSM shredstar S10.



HSM shredstar S5



HSM shredstar S10








HSM shredstar X5

Technical Data


Model	HSM shredstar S5	HSM shredstar S10	HSM shredstar X5
Application area	Home use / small office (1 to 3 persons)	Home use / small office (1 to 3 persons)	Home use / small office (1 to 3 persons)
Cutting type	strip	strip	particle
Cutting size in mm / Product number	6 / 1041121	6 / 1042121	4,5 x 30 / 1043121
Security levels in accordance with DIN 66399	P-2	P-2 / O-1 / T-1 / E-2	P-4 / O-1 / T-2 / E-2 / F-1
Cutting capacity in DIN A4 sheets 80g/m ²	5	10	5
Noise level in idle operation in dB(A)	62	58	58
Intake width in mm	220	220	220
Power consumption of the motor in Watt	65	125	125
Voltage / Frequency	230 V / 50 Hz	230V / 50 Hz	230V / 50 Hz
Dimensions (W x D x H) in mm	310 x 210 x 350	345 x 245 x 385	345 x 245 x 385
Weight in kg	3	4	4
Container volume in l	12	18	18
Shredding material			


Data privacy concerns everyone! So shred sensitive data at the office or at home with a document shredder from the HSM shredstar line. These devices are characterised by their compact and modern design, by their high performance level and ease of use with an unbeatable price-performance ratio.


These media types can be destroyed:

 P Documents e.g. paper	 O e.g. CDs, DVDs, Blu-ray discs	 E e.g. USB sticks, chip cards, memory cards
 T e.g. floppy disks, ID cards with magnetic strips	 F e.g. films, foils	

That is what the HSM shredstar document shredders can do with your confidential documents (particles in original size):

P-2 
Strip cut 6 mm

P-4 
Particle cut 4 x 35 mm / 4 x 37 mm

P-5 
Particle cut 2 x 15 mm





HSM shredstar X6pro



HSM shredstar X8



HSM shredstar X10

Model	HSM shredstar X6pro	HSM shredstar X8	HSM shredstar X10
Application area	Home use/small office (1 to 3 persons)	Home use/small office (1 to 3 persons)	Home use/small office (1 to 3 persons)
Cutting type	particle	particle	particle
Cutting size in mm / Product number	2 x 15 / 1046111	4,5 x 30 / 1044121	4,5 x 30 / 1045111
Security levels in accordance with DIN 66399	P-5 / O-1 / T-2 / E-2 / F-2	P-4 / O-1 / T-2 / E-2 / F-1	P-4 / O-1 / T-2 / E-2 / F-1
Cutting capacity in DIN A4 sheets 80g/m ²	6	8	10
Noise level in idle operation in dB(A)	58	58	58
Intake width in mm	220	220	220
Power consumption of the motor in Watt	160	250	160
Voltage / Frequency	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz
Dimensions (W x D x H) in mm	345 x 245 x 445	345 x 245 x 385	345 x 245 x 445
Weight in kg	6	6	6
Container volume in l	20	18	20
Shredding material			

All statements without guarantee. Technical and design modifications reserved.

HSM shredstar document shredders

Stylish – good value – secure: keep big secrets secure for a small price with HSM shredstar document shredders for the office.



Benefits:

- Automatic return eliminates paper jams.
- Separate CD cutting unit with own waste container for sorted disposal.
- Quiet operation minimises noise development in the workplace.
- LED indicator shows the device's operating status: Power, Overload, Overheat, Bin full, Door open.
- Automatic detection and shutdown if the waste container is full.
- Light barrier for automatic start/stop.



LED indicator shows the device's operating status.



Can be moved on castors (from HSM shredstar X13 and X15).



HSM shredstar X13



HSM shredstar X15



Learn more.
Scan QR code.

Model	HSM shredstar X13	HSM shredstar X15
Application area	Workplace/office (up to 5 persons)	Workplace/office (up to 5 persons)
Cutting type	particle	particle
Cutting size in mm / Product number	4 x 37 / 1057121	4 x 37 / 1030121
Security levels in accordance with DIN 66399	P-4 / O-1 / T-2 / E-2 / F-1	P-4 / O-1 / T-2 / E-2 / F-1
Cutting capacity in DIN A4 sheets 80g/m ²	13	15
Noise level in idle operation in dB(A)	57	57
Intake width in mm	230	230
Power consumption of the motor in Watt	300	320
Voltage / Frequency	230 V / 50 Hz	230 V / 50 Hz
Dimensions (W x D x H) in mm	390 x 300 x 595	390 x 300 x 595
Weight in kg	13	13
Container volume in l	23	26
Shredding material		

HSM – the company

Shredding and Compressing.



Since 1971, HSM has been pursuing a clear strategy – a consistent commitment to quality “Made in Germany”. This product and service quality is the key to success in both the office technology and environmental technology business sectors. As a specialist for products and services for data protection as well as technologies for optimising logistics and recycling processes, HSM is one of the world’s leading providers.

Enquire now! We are always glad to help.

Head office in Germany:

HSM GmbH + Co. KG · Austraße 1-9 · 88699 Frickingen / Germany
Tel. +49 7554 2100-0 · Fax +49 7554 2100-160
info@hsm.eu · www.hsm.eu

E-mail / hotline:

Gratis Hotline
DE, AT, IT, ES, BE, NL, LU
Tel. 00800 44 77 77 66
Fax 00800 44 77 77 67

HSM Vertrieb Deutschland
Deutschland@hsm.eu

HSM Vertrieb Österreich
Austria@hsm.eu

HSM Vertrieb Schweiz
Schweiz@hsm.eu

HSM Verkoop België, Nederland,
Luxemburg
Benelux@hsm.eu

HSM Commerciale Italia
Italia@hsm.eu

HSM subsidiaries:

HSM Técnica de Oficina
y Medioambiente, España, S.L.U.
C/Tona
Nave nº 15 “El Lago”
Pol. Ind. Monguit
08480 L’Ametlla del Vallès
Barcelona
Spain
Tel. +34 93 8617168
Fax +34 93 8463417
Spain@hsm.eu
www.hsm.eu

HSM France SAS
Parc de Genève
240, Rue Ferdinand Perrier
69800 Saint-Priest
France
Tél. +33 472 210580
Fax +33 472 517481
France@hsm.eu
www.hsm.eu

HSM (UK) Ltd.
14 Attwood Road / Zone 1
Burntwood Business Park
Burntwood · Staffordshire
WS7 3GJ
United Kingdom
Tel. +44 1543 272-480
Fax +44 1543 272-080
info@hsmuk.co.uk
www.hsm.eu

HSM Polska Sp. z o.o.
ul. Emaliowa 28
02-295 Warsaw
Polska (Poland)
Tel. +48 22 862-2369
Fax +48 22 862-2368
handlowy@hsm.eu
www.hsm.eu

HSM of America LLC
419 Boot Road
Downingtown
PA 19335
USA
Tel. +1 484 237-2308
+1 800 613-2110
Fax +1 484 237-2309
customerservice@hsm.us
info@hsm.us
www.hsm.us

HSM®

Great Products, Great People.