

### Dual-Bay 2.5" SATA SSD / HDD Rack for 3.5" Bay - Trayless - RAID

#### Product ID: HSB225S3R



This HDD rack lets you install two 2.5" SATA hard drives or solid-state drives into a single 3.5" front bay. With configurable RAID support, the SATA drive rack provides an ideal data storage solution.

Configure and arrange your drives for increased drive capacity, or add data redundancy, with built-in hardware RAID functionality. The HDD rack offers software and operating system independent operations and with multiple RAID options, such as RAID 0, RAID 1, spanning, or JBOD, you can build the data storage solution that works best for you.

This SATA backplane is trayless and hot-swappable, which makes it easy to install and remove your drives from your computer system when required, without having to open the case every time. It also provides a more convenient way to create backups for data recovery and archiving.

The removable hard-drive bay/backplane features durable aluminum construction for long-lasting performance. The SATA backplane also has LED indicators for power and hard drive activity, and drive status, which makes it easy to monitor the status of your hard drives and RAID array.

The HSB225S3R is backed by a StarTech.com 2-year warranty and free lifetime technical support.

# **Certifications, Reports and Compatibility**

# **Applications**

- Ideal for IT professionals, such as systems integrators and administrators, looking for flexible storage management
- Build your incremental or off-site storage backup plan by connecting hot-swappable drives to your server or desktop computer
- Save time in fast-paced work environments where drives need to be replaced often



### **Features**

- SATA III (6Gbps) drive interface, compatible with SATA I, II and III
- Increase drive capacity, performance, or data redundancy, with multiple RAID modes: RAID 0, RAID 1, spanning
- Supports up to two 2.5" SATA SSD/HDDs
- Front-mount bay design for installation into any standard 3.5" front bay
- Trayless design, with hot-swappable bays, makes it easy to swap drives in and out of the mobile rack
- Well-built, durable aluminum construction
- LED indicators for power and activity, to easily monitor your hard drives
- 50,000 insertion rating
- Single SATA data and power connection

Hardware		
	Warranty	2 Years
	Front Door Key Lock	No
	Fan(s)	No
	Interface	SATA
	Number of Drives	2
	Drive Size	2.5in
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Number of 2.5 inch bays	2
	Supported Drive Height(s)	5mm
		7mm
		9.5mm
	Chipset ID	ASMedia - ASM1092R

**Performance** 



TRIM Support Yes

S.M.A.R.T. Support Yes

Type and Rate SATA III (6 Gbps)

Port Multiplier Yes

Hardware Raid

Supported

Yes

Supported RAID Modes RAID 0 (Striped Disks)

RAID 1 (Mirrored Disks)

BIG (Spanning or Concatenation)

JBOD - (Just a Bunch of Disks)

Hot Swap Capability Yes

Insertion Rating 50,000

Connector(s)

Drive Connectors 22 pin SATA Data + Power (7 + 15 pin) Receptacle

Host Connectors LP4 (4 pin, PWM)

7 pin SATA Data Receptacle

Special Notes / Requirements

Note TRIM and SMART have limited support while in a RAID configuration.

A SATA controller with Port Multiplier support is required, in addition to the product configured in JBOD mode, to provide full TRIM and

SMART support.

**Indicators** 

LED Indicators Link/Activity/Error

**Environmental** 

Operating Temperature 0C to 55C (32F to 131F)

Storage Temperature -20C to 55C (-4F to 131F)

Humidity 5% ~ 65%

Physical Characteristics



0-1	DII-
Color	Black

Material Aluminum and Plastic

Max Drive Height 0.4 in [9.5 mm]

Product Length 5.5 in [14.0 cm]

Product Width 4.0 in [10.1 cm]

Product Height 1.0 in [25.0 mm]

Weight of Product 7.8 oz [220.0 g]

Packaging Information

Package Length 7.8 in [19.8 cm]

Package Width 5.9 in [15.0 cm]

Package Height 1.8 in [45.0 mm]

Shipping (Package)

Weight

12.2 oz [345.0 g]

What's in the Box

Included in Package mobile rack

SATA data cable

SATA to LP4 adapter

installation screw kit

quick-start guide

<sup>\*</sup>Product appearance and specifications are subject to change without notice.