



STYLEVIEW™

by ergotron®

Non-powered StyleView 43 Cart with HD Pivot

- Heavy-duty pivot supports larger monitors and all-in-one computers
- Requires less user force to lift the head-unit assembly when loaded to capacity
- Accommodates the largest range of nurses and caregivers when sitting or standing
- Maneuvers effortlessly to the point of need with ultra-smooth gliding casters that travel easily across crowded carpet or hard surface floors
- Small footprint makes it ideal for space constrained areas
- Open-architecture design accommodates multiple configurations and future hardware upgrades
- Passes Ergotron's 25,000-cycle motion test, which ensures years of trouble-free sit-to-stand height adjustment
- Extra rows of drawers may be added (up to a maximum of five rows)



DOCUMENTATION MEDICAL CART WITH HEAVY-DUTY PIVOT
SUPPORTS LARGER MONITORS AND ALL-IN-ONE COMPUTERS



Our market-leading, point-of-care StyleView Carts are designed to include all of the features that caregivers have asked for, with all of the open architecture and quality construction that IT departments require.

The SV43 Heavy-Duty (HD) Pivot cart handles larger monitors and all-in-one computers, requiring less user effort to lift the head-unit assembly when loaded to capacity.

For user, facility and patient safety, the cart is tested to UL/EN/IEC and FCC Part 15 Class A specifications.

Non-powered StyleView 43 Cart with HD Pivot

DIMENSIONS AND WEIGHTS

Storage compartment for closed notebook, thin client or CPU:
17.75"W x 14.75"D x 4"H (45 x 37,5 x 10,1 cm); larger computers can mount to rear of cart with Universal CPU Holder accessory (#80-105-064 ordered separately)

Compact wheel-to-wheel base dimensions: 17 x 21" (43 x 53,3 cm)

Cart weight: 92 lbs (41,8 kg)

Shipping dimensions: 56"D x 24.5"W x 34"H (142 x 62 x 86 cm)

Shipping weight: 120 lbs (54,5 kg)

CART INCLUDES

HD pivot, worksurface, CPU lock, secure CPU compartment, four-port USB hub, scanner holder bracket, mouse holder, wrist rest, back-tilt keyboard tray, left/right mouse tray, rear handle, storage basket, cable storage, four casters (two locking), plus:

SV43-2530-0: Includes 3 locking drawers

SV43-2550-0: Includes 5 locking drawers

SV43-2570-0: Includes 7 locking drawers

SV43-2590-0: Includes 9 locking drawers

- 1 HD Pivot supports larger monitors up to 24" and all-in-one computers; provides 25 degrees of tilt and 90 degree rotation
LCD and worksurface adjust 16" (41 cm) in tandem
LCD Pivot adjusts 5" (13 cm) independently
Maximum LCD height adjustment = 21" (53 cm)
- 2 Scanner holder bracket
- 3 Spacious worksurface: 22.4"W x 19.75"D (56,7 x 50,2 cm)
- 4 Back-tilt keyboard tray, wrist rest and mouse holder; keyboard pans fully side-to-side
- 5 Rear basket keeps task-related items where they can be quickly accessed
- 6 Locking drawer system comes standard with cart; features an auto-locking system; also supports "Pharmacy Mode" which unlocks all drawers simultaneously
- 7 T-slot channel interface on the column allows you to integrate additional drawers and accessories
- 8 Four 4" (10,2 cm) casters; two front casters are lockable
- 9 Wheel-to-wheel base dimensions: 17"x 21" (43 x 53,3 cm)



STANDARD DRAWER CONFIGURATIONS:



SV43-2530-0: Includes primary single drawer, two supplemental single drawers and drawer dividers (for a total of 3 individual drawers)



SV43-2550-0: Includes primary single drawer, one supplemental single drawer, one supplemental triple drawer and drawer dividers (for a total of 5 individual drawers)



SV43-2570-0: Includes primary single drawer, two supplemental triple drawers and drawer dividers (for a total of 7 individual drawers)



SV43-2590-0: Includes primary triple drawer, two supplemental triple drawers and drawer dividers (for a total of 9 individual drawers)

| | |
|------------------|--|
| Typical LCD size | ≤ 24" |
| Weight Capacity* | 20–37 lbs (9,1–16,8 kg) |
| Lift* | 25" (63,5 cm) |
| Tilt | 25° |
| Pan | 24° |
| Rotation* | 90° |
| VESA | MIS-D |
| Warranty | 5-year warranty for mechanical components; 1-year warranty for electrical components |

*See website

Download additional resources at ergotron.com.

For more information:

NORTH AMERICA: 800.888.8458 / +1.651.681.7600 / sales@ergotron.com

EMEA: +31.33.45.45.600 / info.eu@ergotron.com

APAC: apaccustomerservice@ergotron.com

OEM: info@oem.ergotron.com

© Ergotron, Inc. 01.07.2019

Literature made in the U.S.A.

Content subject to change.

Ergotron devices are not intended to cure, treat, mitigate or prevent any disease.

Patent information available at www.ergotron.com/patents.

