

# ThinkVision T22v 61BBMAR6US

Region  
US  
Color  
Black  
Panel  
In-Plane Switching

Display Size  
21.5"

View Area  
476.1x267.8 mm

Resolution  
1920x1080

Aspect Ratio  
16:9

Pixel Pitch  
0.248x0.248 mm

Dot / Pixel Per Inch  
102 dpi

Brightness  
250 nits

Contrast Ratio  
1000:1

Pixel Response Time  
6 ms

Color Gamut  
72%

View Angle (H / V)  
178 / 178

Stand  
Tilt, Swivel, Pivot, Height Adjust Stand

Side Bezel Width  
2 mm

Dimensions with Stand (HxWxD)  
485.8x489.7x251.9 mm

Power Consumption (Typical / Maximum)  
18W / 43W

Power Adapter  
Integrated

Weight (Including Stand)  
10.16lb / 4.61kg

Warranty  
3-year

ENERGY STAR  
ENERGY STAR 7.0

TCO  
TCO 7.0

EPEAT  
Gold

Presets / User Settings  
24 / 20

On Screen Display  
OSD, 8 Languages

USB Port  
USB 3.0x3

Speaker  
Stereo speakers

Camera  
FHD Camera

Multiple Input  
HDMI, DP, VGA

Monitor Cable  
HDMI (ROW), DP, VGA

CPU / Platform  
None / None

Display Ram / Storage / Card Slot  
None / None / None

Wireless / Ethernet / Bluetooth  
None / None / None

Touch Screen / Digitizer Pen / Battery  
None / None / None

Operating System  
Support Windows 7, Windows 10

Ann Date (mm/yy)  
10/17

## Note:

Country Code "US" is for United States, "++" is for EMEA countries (e.g. AD - Saudi, Arabia, AT - Austria, BM - Bulgaria, etc.), "xx" is for EAST countries (e.g. BM - Bulgaria, CX - Hungary, CY - Cyprus, etc.), and "\*\*\*" is for MEA countries (e.g. AD - Saudi, Arabia, ED - Egypt, EQ - Sweden, etc.). Please be aware that the EMEA/ EAST/MEA models listed above might not be available in all countries



This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2017. All rights reserved.



Name	<b>T22v Wide Flat Panel Monitor</b>	
Bezel color	<b>Black</b>	
Type-model	<b>61BBMAR6US / 61BBMAT6EU</b>	
Panel	TFT-LCD, In-Plane Switching (IPS), White LED backlight	
Viewable image size	<b>21.5" (546mm) diagonal</b>	
Max view area (W x H)	18.74" x 10.54" (476.1mm x 267.8mm)	
Native resolution	<b>1920x1080</b>	
Aspect ratio	16:9	
Pixel pitch (mm)	0.248 x 0.248 mm	
Dot/Pixel per Inch	102 dpi	
Brightness	250 nits or cd/m <sup>2</sup> (typical)	
Contrast ratio	1000:1 (typical)	
Pixel response time	6ms (typical); 4ms (extreme mode)	
Color gamut	72%	
Viewing angle at 10:1 CR	178° (+/- 89°) horizontal, 178° (+/- 89°) vertical	
Stand	Tilt, swivel, pivot, and height adjustable stand	
Bezel width	<i>Sides:</i> 0.08" (2.0mm)	
Dimensions (HxWxD)	19.14" H x 19.28" W x 9.92" D; 485.8mm H x 489.7mm W x 251.9mm D	
Power supply	18 watts typical, 43 watts maximum (with USB 3.0 hub), <0.5 watts standby/suspend, universal, integrated (no external brick-like power supply)	
Weight	10.16 lb; 4.61 kg	
Limited warranty	<b>3 year</b> (includes backlight)	
Available date	October 2017	
VESA-compliant	VESA DDC2B/CI	
Power management	ENERGY STAR® qualified	
Ergonomics	ISO 9241-307	
Emission standards	FCC Class B	
Environmental	TCO Displays 7.0, TCO Certified Edge 2.0, WEEE, RoHS, <b>EPEAT™ Gold rating</b>	
Preset resolutions	VGA: 640x480, 720x400 SVGA: 800x600, 832x624 XGA: 1024x768, 1152x864 SXGA: 1280x1024 WXGA+: 1440x900, 1600x900 WSXGA+: 1680x1050 Full HD: 1920x1080	
Presets display modes	Presets: 24; user modes: 20	
Viewing adjustments	<i>Tilt:</i> 30° back, -5° forward; <i>lift:</i> 4.3" (110mm); <i>swivel:</i> +/-45°; detachable stand	
Rotating screen	Screen pivots 90 degrees from landscape to portrait	
On screen display	On screen display with digital user controls (8 languages)	
Control features	Direct access for power, menu, input source select, volume up / down, speaker mute and microphone mute	
USB hub	USB 3.0 Hub: 1 port into PC (USB 3.0); 2 ports for accessories (2 USB 3.0)	
Multimedia	Integrated speakers, dual-array microphone, audio-in and Audio-out, optional sound bar supported	
Camera	Integrated FHD camera with IR	
Multiple input	Support HDMI, DisplayPort, VGA	
Monitor connectors	(1) VGA 15-pin D-shell, analog, blue (2) HDMI (1.4), digital, <b>HDCP-compliant</b> (3) DisplayPort, digital, black, <b>HDCP-compliant</b>	
Signal cables	(1) detachable, VGA 15-pin D-shell at each end, analog, 1.8 meter (2) detachable, DisplayPort at each end, digital, 1.8 meter	
Mounting features	Wall or desk mounting using the Extend Arm or third-party accessories, 100mm x 100mm mount	
Security	Security keyhole for attachment of optional cable lock (Kensington® lock-compatible)	
Ship group	Monitor with stand, Safety and Warranty Information, 1.8 meter analog signal cable, 1.8 meter DP signal cable, 1.8 meter USB signal cable, 1.8 meter black power cord, 1.8 meter HDMI signal cable (Row)	

<b>Features</b>	
<ul style="list-style-type: none"> <li>Widescreen 21.5-inch monitor</li> <li>Supports 1920x1080 resolution</li> <li>Supports optional soundbar</li> <li>Supports ThinkCentre Tiny via VESA back mount</li> <li>EPEAT Gold certified</li> <li>Microsoft® Windows® 7 certified</li> <li>Microsoft Windows 10 certified</li> </ul>	
 <p><b>ThinkVision T22v Wide Monitor</b></p>	

<b>Limited Warranty</b>	<b>Accessories</b>
See details at <a href="http://support.lenovo.com/en_US/guides-and-manuals/detail.page?DocID=UM008281">http://support.lenovo.com/en_US/guides-and-manuals/detail.page?DocID=UM008281</a>	Kensington MicroSaver Cable Lock Kensington Twin Head Cable Lock
	See details at <a href="http://www.lenovo.com/support/monitoraccessories">www.lenovo.com/support/monitoraccessories</a> See all monitors at <a href="http://www.lenovo.com/thinkvision">www.lenovo.com/thinkvision</a>

# ThinkVision T22v

Lenovo

