

# Cisco ESR6300 Embedded Series Router

---

# Contents

Product highlights	3
Product overview	4
Product specifications	5
Software licensing	9
Ordering information	10
Warranty coverage and technical service options	12
Cisco environmental sustainability	12
Cisco Capital	13

---

## Product highlights

The Cisco® ESR6300 Embedded Series Router is a high-performance, ruggedized router designed for use in harsh environments, offering reliable operation in extreme temperatures and under shock and vibration conditions typical for mobile applications in rugged terrain. With onboard hardware encryption, the Cisco ESR6300 offloads encryption processing from the routing engine to provide highly secure yet scalable video, voice, and data services for mobile and embedded outdoor networks. The router offers high performance, six Gigabit Ethernet interfaces (two routed and four switched), and a rich Cisco IOS® XE Software feature set, providing investment protection for customers deploying bandwidth-intensive applications in mobile or embedded networks in heavy industrial, public safety, transportation, defense, and energy markets.

The Cisco ESR6300 is an embedded router module with a compact form factor of 3.0 by 3.775 in. (76.2 by 95.885 mm). This module may fit in an enclosure that was originally designed for PC/104 modules with some additional adaptation. The more compact design simplifies integration and enables the module to be used in a wide variety of embedded applications. The ESR6300 card is available with a custom-designed cooling plate, as well as without the cooling plate for systems integrators who want to design their own thermal solution. The card is designed as a replacement for the Cisco 5915 and 5940 Embedded Services Routers.


Cisco has an ecosystem of partners and systems integrators that embed Cisco ESR6300s into industry-standard, commercially available enclosures as well as custom enclosures tailored to the unique environments in which these routers are deployed. Figures 1 and 2 show the Cisco ESR6300 NCP (no cooling plate) and ESR6300 CON (conduction-cooled) models, respectively.



**Figure 1.**  
Cisco ESR6300 NCP model (no cooling plate)



**Figure 2.**  
Cisco ESR6300 CON model (with cooling plate)



**Figure 3.**  
ESR6300: The next-generation Gigabit Ethernet embedded router

## Product overview

**Table 1.** Key features and benefits

Feature	Benefits
<b>Gigabit Ethernet interface support</b>	The Cisco ESR6300 provides 2 routed and 4 switched high-speed Gigabit Ethernet interfaces, enabling the router to serve as an aggregation point for on-demand network connectivity in mobile or fixed deployments.
<b>Onboard hardware acceleration</b>	The onboard hardware encryption module offloads packet encryption and decryption from the routing engine to increase router performance.
<b>Cisco trustworthy technologies</b>	The onboard Trust Anchor module (TAM), along with image signing, Secure Boot, and runtime defenses, helps ensure that the code running on the ESR6300 hardware platform is authentic, unmodified, and operating as intended.
<b>Storage capabilities</b>	The third-party systems integrator has the option to add an mSATA that Cisco has specified to enhance Cisco IOx edge compute capabilities.
<b>Power over Ethernet-ready architecture</b>	To enable PoE or PoE+, the third-party systems integrator has the option to add a PoE/PoE+ controller based on Cisco's specifications.

Feature	Benefits
<b>Flexible integration into solutions</b>	<p>The inclusive and compact design of the ESR6300 simplifies integration.</p> <ul style="list-style-type: none"> <li>• Non-conduction-cooled and conduction-cooled models are available to satisfy diverse operational environments.</li> <li>• Designed as a transitional replacement for the Cisco 5915 and 5940 Embedded Services Routers, the ESR6300 allows for accelerated time to market.</li> </ul> <p>The router enables development of solutions that address size, weight, power, price, performance, and cooling requirements.</p>
<b>Security</b>	Enterprise-grade Cisco IOS XE routing and switching security features help ensure highly secure voice, video, and data communication.
<b>Cisco Unified Communications Manager Express support</b>	This application supports up to 48 phones for remote IP telephony on vehicles or in outdoor locations. It provides primary or backup telephony services for command-and-control communications.
<b>Throughput performance tiers</b>	<p>Various throughput performance licenses are available:</p> <ul style="list-style-type: none"> <li>• 50-Mbps encrypted (Default license)</li> <li>• 250-Mbps encrypted (Performance license)</li> <li>• 350-Mbps encrypted (Boost license)</li> </ul>
<b>Ease of management</b>	On-premises and cloud-based network management solutions cater to businesses across multiple industries. Tools such as Cisco DNA Center, Cisco IOx, and Cisco vManage* simplify deployment and offer broad cross-network management and the depth of multilayer visibility.

\*vManage support will be available in future releases.

## Product specifications

**Table 2.** Hardware specifications

Feature	Specification
<b>Memory</b>	
<b>Default and maximum DRAM</b>	4-GB DDR4 memory capacity (32-bit plus 4-bit ECC)
<b>Default and maximum flash memory</b>	4-GB usable (pSLC mode) eMMC flash
<b>Physical characteristics</b>	
<b>Physical dimensions (H x W)</b>	3.0 x 3.775 in. (76.2 x 95.885 mm)
<b>Power specifications</b>	3.3V and 5V power inputs
<b>Power consumption</b>	<p>At idle: 5W</p> <p>Typical: 7.5W</p> <p>Maximum: 12W</p>

Feature	Specification
<b>Interface support</b>	
<b>Console</b>	<ul style="list-style-type: none"> <li>• 1 universal asynchronous receiver-transmitter (UART) port, defaults to 9600 baud</li> </ul> Options for external interface: <ul style="list-style-type: none"> <li>• 1 USB 2.0 port (requires USB/UART bridge)</li> <li>• 1 EIA-232 serial console port (requires EIA-232/UART transceiver)</li> </ul>
<b>USB host</b>	1 USB 3.0 host port Type A (requires USB connector and 5V VBUS power switch)
<b>WAN Gigabit Ethernet</b>	2 Layer 3 GE WAN ports (requires magnetics and connector)
<b>LAN Gigabit Ethernet</b>	4 Layer 2 GE LAN ports (the module has an integrated Layer 2 switch that can be PoE/PoE+ enabled - requires magnetics, connector, and PoE controller)
<b>Serial interface</b>	<ul style="list-style-type: none"> <li>• EIA-232 DTE serial port</li> <li>• Support for asynchronous mode and flow control with data rate up to 921,600 baud</li> </ul>
<b>Storage module interface</b>	<ul style="list-style-type: none"> <li>• 1 mSATA module interface (storage for Cisco IOx edge compute applications)</li> </ul>
<b>Input and output</b>	ALARM input port (requires isolated dry contact open/closed detection circuit)
<b>LED signals</b>	SYS: System (green/yellow) ALM: Alarm (red) VPN: Virtual private network (green) USB CONS: USB console (green) SSD: Solid state drive, mSATA (green) GE WAN: Link and activity (green) SFP WAN: Link and activity (yellow) GE LAN: Link and activity (green)
<b>Environmental characteristics</b>	
<b>Industrial-grade board component temperature</b>	-40° to 85° C (-40° to 185° F) component local ambient temperature specification
<b>Operating temperature</b>	-40° to 85° C (-40° to 185° F) for conduction-cooled SKUs as measured at the center top surface of the heat spreader plate Temperature range of a completed solution depends on the enclosure thermal design characteristics used by the systems integrator
<b>Storage temperature</b>	-40° to 85° C (-40° to 185° F)
<b>Operating altitude</b>	12,192 m (40,000 ft)
<b>Nonoperating altitude</b>	12,192 m (40,000 ft)

Feature	Specification
<b>Nonoperating shock and vibration</b>	MIL-STD-810, Method 514.4 IEC 68000-2-32 MIL-STD-810 F, Method 516.5, Procedure V Crash Hazard (All shock and vibration is dependent on the packaging.)
<b>Standard safety certifications</b>	Information Technology Equipment: UL/CSA 60950-1 UL Recognized Component UL/CSA 62368-1 UL Recognized Component CB report and certificate to IEC 60950-1 with all country deviations CB report and certificate to IEC 62368-1 with all country deviations
<b>Industry standards</b>	<ul style="list-style-type: none"> <li>• IEC 61850-3</li> <li>• IEEE 1613</li> </ul>
<b>EMC emissions CLASS A</b>	<ul style="list-style-type: none"> <li>• 47 CFR, Part 15:2016</li> <li>• CISPR32:2012:Ed:1</li> <li>• CISPR32:2015:Ed:2</li> <li>• CNS13438:2006</li> <li>• EN300 386:2012:V1.6.1</li> <li>• EN55032:2012</li> <li>• EN55032:2015</li> <li>• EN61850-3:2014</li> <li>• ICES-300:2016:6</li> <li>• IEC61850-3:2013</li> <li>• KN32:2015</li> <li>• QCVN 118:2018/BTTTT</li> <li>• VCCI-CISPR 32:2016</li> </ul>
<b>EMC immunity</b>	<ul style="list-style-type: none"> <li>• CISPR24:2010+A1:2015</li> <li>• CISPR35:2016:Ed:1</li> <li>• EN300 386:2012:V1.6.1</li> <li>• EN55024:2010</li> <li>• EN55024:2010:A1</li> <li>• EN55035:2017</li> <li>• EN61850-3:2014</li> <li>• IEC61850-3:2013</li> <li>• IEEE 1613.1:2013</li> <li>• IEEE 1613:2009</li> <li>• IEEE 1613a:2011</li> <li>• KN35:2015</li> <li>• TCVN 7317:2003</li> </ul>

**Table 3.** Software specifications

Feature	Description
<b>Cisco IOS Software requirements</b>	<ul style="list-style-type: none"> <li>• Cisco IOS XE Software: Universal Cisco IOS Software image</li> <li>• Cisco IOS XE Software Release 17.1.1 or later</li> </ul>
<b>IPv4 and IPv6 services features</b>	<ul style="list-style-type: none"> <li>• Routing Information Protocol (RIP) v1 and v2</li> <li>• Generic Routing Encapsulation (GRE) and Multipoint GRE (MGRE)</li> <li>• Standard 802.1d Spanning Tree Protocol (STP)</li> <li>• Network Address Translation (NAT)</li> <li>• Dynamic Host Configuration Protocol (DHCP) server, relay, and client</li> <li>• Dynamic DNS (DDNS)</li> <li>• DNS proxy</li> <li>• DNS spoofing</li> <li>• Access Control Lists (ACLs)</li> <li>• IPv4 and IPv6 multicast</li> <li>• IP Service-Level Agreement (IP SLA)</li> <li>• Open Shortest Path First (OSPF) v2 and v3</li> <li>• Border Gateway Protocol (BGP)</li> <li>• Enhanced Interior Gateway Routing Protocol (EIGRP)</li> <li>• Virtual Route Forwarding (VRF) Lite</li> <li>• Next-Hop Resolution Protocol (NHRP)</li> <li>• Serial data encapsulation and relay</li> <li>• Layer 2 Tunneling Protocol (L2TP) v3 over sub-interfaces and VLAN</li> </ul>
<b>Security features</b>	<p><b>Secure connectivity</b></p> <ul style="list-style-type: none"> <li>• Secure Sockets Layer (SSL) VPN for secure remote access</li> <li>• Hardware-accelerated encryption with minimal impact to system performance</li> <li>• Next-Generation Encryption (NGE) and Quantum Computing Resistant (QCR) algorithms such as AES-256, SHA-384, and SHA-512</li> <li>• Public-Key Infrastructure (PKI) support</li> <li>• 20 IPsec tunnels</li> <li>• Cisco Easy VPN Solution client and server</li> <li>• NAT transparency</li> <li>• Dynamic Multipoint VPN (DMVPN)</li> <li>• Tunnel-less Group Encrypted Transport VPN</li> <li>• FlexVPN</li> <li>• IPsec stateful failover</li> <li>• VRF-aware IPsec</li> <li>• IPsec over IPv6</li> </ul> <p><b>Cisco IOS Firewall</b></p> <ul style="list-style-type: none"> <li>• Zone-based policy firewall</li> <li>• VRF-aware stateful inspection routing firewall</li> <li>• Stateful inspection transparent firewall</li> <li>• Advanced application inspection and control</li> <li>• Secure HTTP (HTTPS), FTP, and Telnet Authentication Proxy</li> <li>• Dynamic and static port security</li> <li>• Firewall stateful failover</li> <li>• VRF-aware firewall</li> </ul>



Feature	Description
	<p><b>Integrated threat control</b></p> <ul style="list-style-type: none"> <li>• Control-Plane Policing (CoPP)</li> <li>• Flexible packet matching</li> <li>• Network foundation protection</li> </ul>
<p><b>QoS features</b></p>	<ul style="list-style-type: none"> <li>• Provides traffic precedence to delay-sensitive and mission-critical services</li> <li>• Facilitates low-latency routing of delay-sensitive industrial applications</li> <li>• Supported on all LAN and WAN interfaces</li> <li>• Low Latency Queuing (LLQ)</li> <li>• Weighted Fair Queuing (WFQ)</li> <li>• Class-Based WFQ (CBWFQ)</li> <li>• Class-Based Traffic Shaping (CBTS)</li> <li>• Class-Based Traffic Policing (CBTP)</li> <li>• Policy-Based Routing (PBR)</li> <li>• Class-Based QoS MIB</li> <li>• Class of Service (CoS) to Differentiated Services Code Point (DSCP) mapping</li> <li>• Class-Based Weighted Random Early Detection (CBWRED)</li> <li>• Resource Reservation Protocol (RSVP)</li> <li>• Real-Time Transport Protocol (RTP) header compression (cRTP)</li> <li>• Differentiated Services (DiffServ)</li> <li>• QoS pre-classify and pre-fragmentation</li> <li>• Hierarchical QoS (HQoS)</li> </ul>
<p><b>IPv6 features</b></p>	<ul style="list-style-type: none"> <li>• IPv6 addressing architecture</li> <li>• IPv6 unicast and multicast forwarding</li> <li>• IPv6 ACLs</li> <li>• IPv6 routing</li> <li>• IPv6 domain name resolution</li> </ul>

## Software licensing

The Cisco ESR6300 offers two technology packages – Network Essentials and Network Advantage. The Network Essentials license offers the essential elements of routing and security necessary for typical IoT deployments. The Network Advantage license enables advanced features, including Multiprotocol Label Switching (MPLS) for a highly scalable and cost-effective solution, mobile IP for seamless migration between networks, and application-aware QoS policies for built-in intelligence.

A single Cisco IOS XE universal image encompassing all functions is delivered with the product. Software feature licenses are preinstalled in the factory, depending on the selection made at the time of purchase, simplifying software delivery and decreasing the operational costs of the deployment. Licenses can be upgraded after deployment by going through the Cisco [Smart License activation process](#).

**Table 4.** Software licensing

License type	Description
<b>Network Essentials</b>	<ul style="list-style-type: none"> <li>• Authentication, Authorization, and Accounting (AAA), Address Resolution Protocol (ARP), ACLs, Cisco Configuration Professional, Cisco Discovery Protocol, Connectionless Network Service (CLNS), Cisco Networking Services, EIGRP, SNMP, MIB, raw sockets, Call Home, First-Hop Redundancy Protocol (FHRP), Hierarchical Queuing Framework (HQF), iEDGE, basic routing and multicast, NAT, Network Time Protocol (NTP), DHCP, Internet Control Message Protocol (ICMP), Internet Group Management Protocol (IGMP), basic OSPF and OSPFv3, QoS, RIP, HTTP, Hot Standby Router Protocol (HSRP), STP, VLAN, VRF, 802.1X</li> <li>• IPsec, crypto tunnels, FlexVPN, Internet Key Exchange (IKE) v2</li> <li>• Cisco Unified Communications Manager Express</li> </ul>
<b>Network Advantage</b>	<ul style="list-style-type: none"> <li>• AAA, ARP, ACL, Cisco Configuration Professional, Cisco Discovery Protocol, CLNS, Cisco Networking Services, EIGRP, SNMP, MIB, raw sockets, Call Home, FHRP, HQF, iEDGE, basic routing and multicast, NAT, NTP, DHCP, ICMP, IGMP, basic OSPF and OSPFv3, QoS, RIP, HTTP, HSRP, STP, VLAN, VRF, 802.1X</li> <li>• IPsec, crypto tunnels, FlexVPN, IKE v2</li> <li>• MPLS, BFD, RSVP, IP SLA, TCP optimization, App-aware QoS policies and troubleshooting</li> <li>• Cisco Unified Communications Manager Express</li> <li>• Cisco DNA Center add-on license*</li> </ul>


Only key features are highlighted above.

\*Cisco DNA Center license will be added in the future.

## Ordering information

The ESR6300 is a Smart License-enabled product. Cisco Smart Accounts and Virtual Accounts are required to order the product. For more information on how to order the ESR6300 and Cisco Smart Accounts, visit the Cisco [Smart Account user guide](#).

1. ESR6300 board selection: Choose ESR6300 CON (conduction-cooled models) or ESR6300 NCP (no cooling plate).
2. Mandatory purchase of one software package/throughput license.



**Figure 4.**  
ESR6300 licensing and ordering

- HSEC license is mandatory if the Boost license is selected, and is automatically included.
- Cisco Unified Communications Manager Express per-seat license is optional and is required if a customer wants to use Cisco Unified Communications Manager Express.
- Only key features under Network Essentials and Network Advantage are highlighted in Figure 4.

**Table 5.** ESR6300 router

Product name	Part number
<b>Cisco ESR6300 Embedded Series Router Cards</b>	
<b>Cisco ESR6300 no cooling plate card with 2x Gigabit Ethernet routed ports and 4x Gigabit Ethernet switched ports</b>	ESR-6300-NCP-K9
<b>Cisco ESR6300 conduction cooled card with 2x Gigabit Ethernet routed ports and 4x Gigabit Ethernet switched ports</b>	ESR-6300-CON-K9

**Table 6.** Performance tiers and software packages

Throughput	Software package	
	Network Essentials	Network Advantage
Default (50 Mbps)	SL-6300-NE/DEF-K9	SL-6300-NA/DEF-K9
Performance (250 Mbps)	SL-6300-NE/PERF-K9	SL-6300-NA/PERF-K9
Boost (350 Mbps)	SL-6300-NE/BOOS-K9	SL-6300-NA/BOOS-K9

**Table 7.** Software option

Options	Part number
Cisco Unified Communications Manager Express - 1 seat	CME-UL

**Table 8.** Boost license requirement

HSEC license	Part number
High-security license, required with Boost license	L-63-HSEC-K9

## Warranty coverage and technical service options

### For more information

For more information about the Cisco ESR6300 Embedded Services Router, visit <https://www.cisco.com/go/esr6300> or contact your local Cisco account representative.

## Cisco environmental sustainability

Information about Cisco’s environmental sustainability policies and initiatives for our products, solutions, operations, and extended operations or supply chain is provided in the “Environment Sustainability” section of Cisco’s [Corporate Social Responsibility](#) (CSR) Report.

Reference links to information about key environmental sustainability topics (mentioned in the “Environment Sustainability” section of the CSR Report) are provided in the following table:

Sustainability topic	Reference
Information on product material content laws and regulations	<a href="#">Materials</a>
Information on electronic waste laws and regulations, including products, batteries, and packaging	<a href="#">WEEE compliance</a>

Cisco makes the packaging data available for informational purposes only. It may not reflect the most current legal developments, and Cisco does not represent, warrant, or guarantee that it is complete, accurate, or up to date. This information is subject to change without notice.

---

## Cisco Capital

### Flexible payment solutions to help you achieve your objectives

Cisco Capital makes it easier to get the right technology to achieve your objectives, enable business transformation and help you stay competitive. We can help you reduce the total cost of ownership, conserve capital, and accelerate growth. In more than 100 countries, our flexible payment solutions can help you acquire hardware, software, services and complementary third-party equipment in easy, predictable payments. [Learn more.](#)

#### Americas Headquarters

Cisco Systems, Inc.  
San Jose, CA

#### Asia Pacific Headquarters

Cisco Systems (USA) Pte. Ltd.  
Singapore

#### Europe Headquarters

Cisco Systems International BV Amsterdam,  
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)