

## GV-VS2820 8CH H.264 AHD 1080p Video Server



- H.264
- 8-channel HD-AHD 1080p / 720p and analog 960H / D1 real-time video
- 12V DC
- Tampering Alarm
- USB HDD Storage
- UMTS / 3G / 3.5G / 4G
- Automatic switch between WiFi and 3G / 4G
- Supports over 50 PTZ models
- 29 languages on web interface
- ONVIF (Profile S) conformant

GV-VS2820 is a powerful H.264 Video Server with compact size and supports multiple applications. It supports 8-channel HD-AHD 1080p / 720p, and is fully integrated with GV-DVR / NVR / VMS to form the most powerful IP solution. GV-VS2820 converts analog signals into high-resolution digitized images up to 2 megapixels. It also supports over 50 PTZ models to fulfill various project demands. It can record video to a local USB storage, forming the smallest video recorder. It can also activate Tampering Alarm alerts when cameras are tampered with, which can prevent criminal activities successfully.

### Specifications

Video			
Video Standard			NTSC, PAL
Video Input			8 channels
Compression			H.264
Frame Rate	NTSC		30 fps per channel; 240 fps in total for 8 channels
	PAL		25 fps per channel; 200 fps in total for 8 channels
Resolution	NTSC HD	Main Stream	1920 x 1080 (Default), 1280 x 720, 640 x 360, 448 x 252 for AHD Signal
		Sub Stream	640 x 360, 448 x 252 (Default) for AHD Signal
	NTSC SD	Main Stream	960 x 480, 720 x 480 (Default), 480 x 240, 360 x 240 for Analog Signal
		Sub Stream	480 x 240, 360 x 240 (Default) for Analog Signal
	PAL HD	Main Stream	1920 x 1080 (Default) , 1280 x 720, 640 x 360, 448 x 252 for AHD Signal
		Sub Stream	640 x 360, 448 x 252 (Default) for AHD Signal
	PAL SD	Main Stream	960 x 576, 720 x 576 (Default), 480 x 288, 360 x 288 for Analog Signal
		Sub Stream	480 x 288, 360 x 288 (Default) for Analog Signal
Video Streaming			Configurable frame rate and bandwidth, Constant and variable bitrate
Video Adjustment			Brightness, Contrast, Saturation, Hue, Sharpness
Dual Streams			Yes
Coaxial Cable	Recommended Type		5C-FB or above
	Maximum Length		300 m (984 ft)
Audio			
Audio Input			4 ports, 8 channels
Compression			G.711
Audio Support			Two-way

Management		
Event Management	Trigger	Schedule, Sensor Input, Motion Detection
	Action	<ul style="list-style-type: none"> <li>● Store Video (AVI format)</li> <li>● Send e-mails with captured images</li> <li>● Upload captured images to FTP Server</li> <li>● Monitor through Center V2 and Vital Sign Monitor</li> <li>● Activate relay outputs to control external devices</li> </ul>
Firmware Upgrade		Remote upgrade by HTTP, Firmware upgrade utility
Storage		USB HDD Storage
Client PC Requirements		Microsoft Internet Explorer 8.x or later
Security		IP address filtering
Language		Bulgarian / Czech / Danish / Dutch / English / French / German / Greek / Hebrew / Hindi / Hungarian / Italian / Indonesian / Japanese / Norwegian / Lithuanian / Persian / Polish / Portuguese / Romanian / Russian / Serbian / Simplified Chinese / Slovakian / Slovenian / Spanish / Thai / Traditional Chinese / Turkish
Network		
Interface		10/100/1000 Base-T Ethernet, 802.11b/g/n Wireless LAN (optional), Mobile broadband: UMTS, EDGE, etc. (optional)
Protocol		DHCP, DynDNS, FTP, HTTP, HTTPS, 3GPP/ISMA, NTP, ONVIF (Profile S), RTSP, SMTP, SNMP, TCP, UDP, UPnP, QoS (DSCP)
External Interface		
Video Input		8 BNC ports
Audio Input		4 ports (stereo phone jack, 3.5mm/0.14")
Audio Output		1 port (stereo phone jack, 3.5 mm/0.14")
Sensor Input		8 inputs
Alarm Output		8 outputs
PTZ		RS-485 +/-
Ethernet		RJ-45, 10/100/1000 Mbps
USB		2 ports (USB 2.0)
Power	Input	12V, 3.0A
Environment		
Operation Temp.		-20 ~ 50 °C / -4 ~ 122 °F
Humidity		0 ~ 90% RH (non-condensing)
Weather Resistance		Indoor use
Physical		
Dimensions (L x W x H)		200 x 175 x 40 mm / 7.87 x 6.88 x 1.57 in
Weight		0.95 kg / 2.09 lb
Regulatory		CE, FCC, RCM, RoHS compliant
Applications		
Software Supported		GV-VMS (V16.10.3.0), GV-DVR / NVR (V8.7.1.0), GV-Control Center (V3.4.0.0), GV-Edge Recording Manager (V1.2.0.0), GV-Center V2 (V16.10.0.0), GV-Recording Server (V1.3.0.0), GV-Redundant / Failover Server (V1.1.0.0)
Network Storage		GV-System (GV-DVR/NVR) / GV-VMS, GV-Backup Center, GV-Recording Server
Mobile Phone Support		GV-Eye for iOS and Android
Live Viewing		IE, Firefox, Chrome, Safari, Edge, GV-Edge Recording Manager
CMS Server support		GV-Control Center, GV-Center V2, GV-Vital Sign Monitor

**Note:**

1. It is required to apply patch files to all the supported software mentioned above except GV-VMS and GV-Center V2.
2. The GV-Video Server cannot work with the microphones that acquire power from the unit. Use microphones that have external power supply.
3. GV-VS2820 supports 1 external hard disk (2.5" or 3.5") with up to 6 TB capacities.




4. It is not recommended to use the flash USB drive with GV-VS2820 because of its slow read and write speed.
5. GV-VS2820 does not support coaxial cable connection with PTZ cameras.
6. Product design and specifications are subject to change without notice.

### Packing List

1. GV-VS2820
2. AC Power Cord x 1
3. Power Adaptor x 1
4. Download Guide
5. Warranty Card

### Options

Optional devices can expand your GV-Video Server's capabilities and versatility. Contact your dealer for more information.

GV-Relay V2	Working with the GV-Relay V2, the GV-Video Server is capable of driving the loads of relay outputs over 5 volts.
GV-WiFi Adaptor V2	The WiFi Adaptor V2 is designed to connect the GV IP devices, such as GV-Video Server, to the wireless network.
3.5 mm Stereo to RCA Cable	3.5 mm Stereo to RCA Cable is served as an audio adapter for microphones with RCA connectors.
Wall Hook	<p>Wall Hook is used to mount GV-VS2820 to the wall.</p> 
DIN-rail Hook	<p>DIN-rail Hook is used to mount GV-VS2820 to a 35-mm (1.38-in) DIN rail.</p> 
Rack Mount	<p>Rack Mount is used to mount up to 2 video servers to a 19-in (482.6-mm) rack.</p> 

### Supported Wireless LAN USB Adaptor

Vendors	Model
D-Link	DWA-140 (H/W version B1), DWL-G122 (version C1)
EDIMAX	EW-7318Ug, EW-7718Un, EW-7711UAn
Linksys	WUSB54GC, WUSB600 (version 1)
Pegatron	WL-166N11
<b>Note:</b> Linksys WUSB54GC ver. 3 is not supported.	

## Supported Mobile Broadband Device

Vendors	Model
Bandlux	C320, C501
HUAWEI	E156, E156B, E169, E220, E1692, E1750, E1752, E1756, E1756C, EC169C, EC189 USB Modem (HSDPA/UMTS/EDGE/GPRS/GSM)
Novatel	MC950D, MC996D, MC998D (HSDPA/UMTS/EDGE/GPRS/GSM)
Onda	MSA523HS
Sierra	250U
Verizon	USB727, USB728, USB760 Modem (EVDO)
Vodafone	K3565 (Rev 2)
ZTE	MF100