

N 30
BUILT-IN/BUILT-UNDER COOKER/OVEN
U1DCC1BN0B STAINLESS STEEL



B



Included accessories

3 x combination grid, 1 x universal pan

Built-in oven with CircoTherm® - The award-winning hot air system from Neff

Double built-in oven - perfect for grilling, baking and roasting of multiple dishes at the same time.

- ✓ CircoTherm® - the unique hot air-system for simultaneous baking and roasting on up to 3 levels
- ✓ Telescopic rail pull-out for 1 level

Features

Technical Data

Color / Material Front : Stainless steel
Built-in / Free-standing : Built-in
Integrated Cleaning system : No
Dimensions of the product (mm) : 888 x 594 x 550
Dimensions of the packed product (HxWxD) (mm) : 960 x 690 x 660
Control Panel Material : Stainless steel
Door Material : Glass
Net weight (kg) : 51.3
Usable volume (of cavity) - cavity 1 (l) : 71
Cooking method : Conventional heat, Full width grill, Heißluft sanft, Hot Air, Hot air grilling
Temperature control : No control of the temperature
Number of interior lights : 1
Approval certificates : CE, VDE
EAN code : 4242004222064
Energy efficiency class (2010/30/EC) : A
Energy consumption per cycle conventional (2010/30/EC) : 1.02
Energy consumption per cycle forced air convection (2010/30/EC) : 0.81
Energy efficiency class (2010/30/EC) - cavity 2 : B
Energy consumption per cycle conventional - cavity 2 (2010/30/EC) : 0.83
Energy efficiency index (2010/30/EC) : 95.3
Energy efficiency index cavity 2 (2010/30/EC) : 120.3
Electrical connection rating (W) : 5900
Current (A) : 32
Voltage (V) : 220-240
Frequency (Hz) : 50
Plug type : fixed connection, no plug



4 242004 222064

N 30

BUILT-IN/BUILT-UNDER COOKER/OVEN

U1DCC1BN0B STAINLESS STEEL

Features

Design

- Fixed control dials
- Bar handle

Main Lower oven

- Oven capacity: 71 litre
- 1 level telescopic shelf, Stop function
- Control panel lock
- Smooth cavity interior, Shelf support rails
- Cavity (inner surface) bottom: Enamel grey
- Interior halogen light

Programmes/functions

- 5 heating methods: CircoTherm®, Top/bottom heat, Hot air grilling, Full surface grill, CircoTherm® gentle
- Manual rapid heating up

Cleaning

- EcoCleanDirect : back panel
- Full glass inner door

Secondary top oven

- Cavity volume: 34 Litre
- Interior halogen light
- Cavity (inner surface) top: Enamel grey

Programmes/functions

- Oven with 3 heating methods: Top/bottom heat, Full surface grill, Small area grill

Cleaning

- EcoClean Direct: back panel, ceiling, side liners

Standard accessories

- 3 x combination grid, 1 x universal pan
- 1 level telescopic shelf, Stop function

Performance/technical information

- Energy efficiency rating (acc. EU Nr. 65/2014): A
Energy consumption per cycle in conventional mode: 1.02 kWh
Energy consumption per cycle in fan-forced convection mode: 0.81 kWh

Number of cavities: 1

Heat source: electrical

Cavity volume: 71 litre

- Energy efficiency rating (acc. EU Nr. 65/2014): B
Energy consumption per cycle conventional mode: 0.83 kWh
Number of cavities: 2
Heat source: electrical
Cavity volume: 34 Litre
- Nominal voltage: 220 - 240 V
- Appliance dimension (hxwxd): 888 mm x 594 mm x 550 mm
- Please refer to the dimensions provided in the installation manual

N 30

BUILT-IN/BUILT-UNDER COOKER/OVEN

U1DCC1BN0B STAINLESS STEEL

Dimensioned drawings

