

EB-S39



DATASHEET / BROCHURE



With the versatility to mount just about anywhere, bright, sharp images and low maintenance, the EB-S39 is a great all-rounder for business.

The EB-S39 offers a very versatile proposition that can be mounted just about anywhere. Meanwhile long lamp life and trusted Epson durability offer peace of mind and minimal maintenance.

Bright, vivid content on a large scalable screen

Enjoy large scale presentations with crisp, clear text, as well as compelling imagery and video content, on screen sizes up to 350 inches. 3,300-lumen performance combines with a high contrast ratio of 15,000:1 to offer outstanding visual performance, even in well-lit rooms.

Years of uninterrupted meetings

With a lamp life and air filter maintenance cycle of 10,000 hours in eco mode, users won't need to worry about maintenance for up to 5 years¹.

Installation and placement flexibility

Automatic vertical and manual horizontal keystone correction provide greater flexibility as to where the projector can be placed in the room for distortion-free images and the wide optical zoom adds to the flexibility.

Wi-Fi capability

Wi-Fi compatibility means the EB-S39 can be upgraded for wireless device access at a later stage (optional accessory required).

High quality sound

This projector has a built-in 5W speaker to allow audio content to be heard clearly without the need for separate external speakers.

KEY FEATURES

- **High-quality bright images**
3LCD technology and equally high white and colour light output
- **Portable**
Small and light enough to be moved easily and used in multiple rooms
- **High quality sound**
Built-in 5W speaker for crisp, clear sound
- **Low TCO**
Lamp and filter life of 10,000 hours in eco mode
- **Versatile and flexible control**
Project from many sources with HDMI and optional Wi-Fi connectivity



EPSON
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.55 inch with MLA (D7)

IMAGE

Colour Light Output	3,300 lumen- 2,050 lumen (economy)
White Light Output	3,300 lumen - 2,050 lumen (economy) in accordance with ISO 21118:2012
Resolution	SVGA, 800 x 600, 4:3
Aspect Ratio	4:3
Contrast Ratio	15,000 : 1
Light source	Lamp
Lamp	UHE, 210 W, 6,000 h durability, 10,000 h durability (economy mode)
Keystone Correction	Auto vertical: $\pm 30^\circ$, Manual horizontal $\pm 30^\circ$
Colour Processing	10 Bits
2D Vertical Refresh Rate	50 Hz - 85 Hz
Colour Reproduction	upto 1.07 billion colours

OPTICAL

Projection Ratio	1.45 - 1.96:1
Zoom	Digital, Factor: 1.35
Lens	Optical
Image Size	30 inches - 350 inches
Projection Distance Wide/Tele	1.77 m - 2.4 m (60 inch screen)
Projection Lens F Number	1.44
Focal Distance	16.7 mm
Focus	Manual
Offset	8 : 1

CONNECTIVITY

USB Display Function	3 in 1: Image / Mouse / Sound
Interfaces	USB 2.0 Type A, USB 2.0 Type B, RS-232C, Wireless LAN IEEE 802.11b/g/n (optional), VGA in (2x), VGA out, HDMI in, Composite in, Component in (2x), RGB in (2x), Stereo mini jack audio out, Stereo mini jack audio in (2x)
Epson iProjection App	Ad-Hoc / Infrastructure

ADVANCED FEATURES

Security	Kensington lock, Security cable hole, Wireless LAN unit lock, Wireless LAN security, Password protection
2D Colour Modes	Dynamic, Cinema, Presentation, sRGB, Blackboard
Features	AV mute slide, Automatic keystone correction, Built-in speaker, Digital zoom, Direct Power on/off, Document Camera Compatible, Easy OSD pre-setting, Horizontal and vertical keystone correction, Network projection, OSD copy function, PC Free, Quick Corner, Split-Screen-Function, Wireless LAN capable, iProjection set-up by QR code
Video Colour Modes	Blackboard, Dynamic, Presentation, sRGB, Theatre
Projector control	via: AMX, Crestron, Control4, Extron

EB-S39

WHAT'S IN THE BOX

- VGA cable
- Main unit
- Power cable
- Remote control incl. batteries



EPSON
WORLD LEADER
IN PROJECTORS

Source: Futuresource Consulting Ltd.

EPSON®
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

GENERAL	
Energy Use	309 W, 227 W (economy), 0.2 W (standby)
Supply Voltage	AC 100 V - 240 V, 50 Hz - 60 Hz
Product dimensions	302 x 249 x 92 mm (Width x Depth x Height)
Product weight	2.7 kg
Noise Level	Normal: 37 dB (A) - Economy: 28 dB (A)
Temperature	Operation 5° C - 35° C, Storage -10° C - 60° C
Humidity	Operation 20% - 80%, Storage 10% - 90%
Included Software	Epson Projector Management Software, EasyMP Multi PC Projection, EasyMP Network Projection
Options	Document camera, Soft carry case, Wireless LAN unit
Loudspeaker	5 W
Room Type / Application	Boardroom, Portable / Huddle space, Collaboration space / Classroom
Positioning	Ceiling Mounted, Desktop
Colour	White / Grey
TCO Certified	Yes
OTHER	
Warranty	36 months Carry in, Lamp: 36 months or 1,000 h Optional warranty extension available

EB-S39

WHAT'S IN THE BOX

- VGA cable
- Main unit
- Power cable
- Remote control incl. batteries

OPTIONAL ACCESSORIES

- Soft Carry Case - ELPKS70
V12H001K70
- Wireless LAN Adapter - ELPAP10
V12H731P01
- Air Filter - ELPAF32
V13H134A32
- ELPLP96
V13H010L96
- Active Speakers (2 x 15W) - ELPSP02
V12H467040DA
- Ceiling Pipe (450mm) - ELPFP13
V12H003P13
- Ceiling Mount (White) - ELPMB23
V12H003B23
- Ceiling Pipe (700mm) - ELPFP14
V12H003P14

EB-S39

LOGISTICS INFORMATION

SKU	V11H854041
EAN code	8715946642550
Country of Origin	Philippines
Layer	6 Units
Layer Block	6 Units



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

1. Based on eight hours of use per day, five days a week.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®