

## USB-C to DVI Adapter, USB 3.1, Thunderbolt 3, 1080p - M/F, Black

MODEL NUMBER: U444-06N-DVIBAM



### Features

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

### Applications

- Play 1080p video from your laptop or PC on a DVI display
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input

### Package Includes



- U444-06N-DVIBAM USB-C to DVI Adapter, USB 3.1, Thunderbolt 3, 1080p - M/F, Black
- Quick Start Guide

## Specifications

MODEL TEXT	
What Does This Product Do?	
OVERVIEW	
Over Current Protection	
INPUT	
Cable Length (ft.)	
Cable Length (m)	
Cable Length (in.)	
Built-In Cable Length (ft.)	
Built-In Cable Length (m)	
Built-In Cable Length (in.)	
Built-In Cable Length (cm)	
External Power Supply Input Specs (V / Hz / A)	
External Power Supply Output Specs (V / A)	
External Power Supply Cord Length (ft.)	
External Power Supply Cord Length (m.)	
Bus Powered	Yes
Cable Length (cm)	
Product Length (in.)	6.00
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	



<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	0.800 x 3.800 x 4.800
Shipping Weight (lbs.)	0.2000
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.57 x 1.8 x 1.7
Unit Weight (lbs.)	0.05
Unit Weight (kg)	0.02
Material of Construction	PVC & ABS
Color	Black
Transmitter Unit Dimensions (hwd / in.)	
Transmitter Unit Dimensions (hwd / cm.)	
Receiver Unit Dimensions (hwd / in.)	
Receiver Unit Dimensions (hwd / cm.)	
Transmitter Unit Weight (lbs.)	
Transmitter Unit Weight (kg)	
Receiver Unit Weight (lbs.)	
Receiver Unit Weight (kg)	
Cable Jacket Rating	VW-1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.7 BTU/Hr
Power Consumption (Watts)	0.8
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	USB C (MALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side B - Connector 1	DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Connector Plating	Nickel
<b>PORT EXPANSION</b>	
Max Distance (Between any 2 Units)	
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	1920 x 1080 (1080p) @60Hz
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	
Driver Required	No
Recommended Category Cable	
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>