

FSS52610Z Dishwasher



Customised Cycles, Complete Cleaning

Advanced sensors in AEG dishwashers automatically adjust the time, temperature and water usage according to the soil level of each load. So you can have customised cycles for each clean with the very best results every time.

Dedicated protection for your delicate glasses

Glasses are often the most delicate items in your dishwasher, which means they need special care. The upper basket in this dishwasher has soft rubber spikes to support and protect glasses. The SoftSpikes stabilise your glasses and mugs efficiently, preventing them from falling over and possibly breaking.



Ready when you are

Make the most of the time you have available with the delay start function in our dishwashers. Preset a programme time that suits and enjoy the convenience of having clean dishes when you want them.

More Benefits :

- Beam-on-floor technology to give you an at-a-glance status check
- The dish washer door opens up during the last part of the drying phase.
- PerfectFit Sliding Hinge makes installing the dishwasher seamless and stylish.

Features :

- Capacity: 13 place settings
- Sensorlogic
- 4 temperature settings
- 5 programmes including:
 - 30 min 60° quickwash
 - Glass 45° C wash
 - Auto half load
 - Multi-tab
- Delay start of up to 24 hours
- Time remaining indicator
- Height adjustable upper basket
- Floor beam to update you on wash status
- End of programme audible alarm
- Rinse aid and salt indicators
- Noise level: dB
- A class energy efficiency
- A class cleaning performance
- A class drying performance

Technical Specs :

- Installation : Fully integrated
- Dimensions (mm) (HxWxD) : 818x596x550
- Dimensions_Dishwasher_FSBU_DK : 820-880x600x550
- Double Hinges : Sliding
- Water Supply : Cold or hot
- Cord Length : 1.5
- Inlet hose length (mm) : 150
- Outlet hose length (mm) : 150
- Connected Load : 1950
- Wheels/feet : 2 adj feet + 1 front adj rear foot, Adj 0 to 8 cm
- Voltage : 220-240
- Required Fuse : 10
- Frequency : 50
- Noise level, dB(A) : 44
- Settings : 13
- Number of programmes : 5
- Number of Temperatures : 4
- Second Generation Energy Class : A++
- Cleaning efficiency (2010/30/EC) : A
- Drying efficiency (2010/30/EC) : A
- Energy consumption (annual) : 262
- Annual water consumption, l : 2775
- Water consumption, l : 9.9
- Program : Eco 50
- Door Colour : None
- Anti-flood Device : Floating switch
- Inlet Pipe Type : Aqua control
- Spray arm : Standard
- Top spraying level : None
- Options : Time Saver, XtraDry
- Drying System : AirDry Technology
- Dishwasher programs : 30 MIN 60°, AutoSense 45°-70°, Eco, Glass 45°, Intensive 70°

Product Description :

FSS52610Z Dishwasher

PSGBDW150D002001

