



BE EVERYWHERE

When the competition is relentless, greatness is achieved by those heroes who rise to the occasion. Equipped with powerful hardware and an aggressive design, the OMEN Laptop takes mobile performance seriously, letting you conquer any challenge in-game from just about anywhere.



Go on, turn up the settings

With this kind of power, they'll be running scared. Includes an Intel® Core™ processor[1] and NVIDIA® or AMD graphics. And with high performance cooling in your arsenal, you're ready to conquer even the most intensive AAA titles.

Every last detail. In your sights.

A Dragon Red backlit keyboard with highlighted WASD, customizable macros, and 26-key rollover anti-ghosting, ensures every keystroke is detected. With a 1080p with 120 Hz refresh rate[2] display, combat without frustrating lag and image ghosting.

Upgrade. Expand. Evolve.

Level up to the latest hardware and make upgrading a breeze with single panel access to internals. An optional Thunderbolt 3-certified USB-C™ port[4], 3 USB Type A ports, and an HDMI port lets you easily adapt to all the action.



Featuring

Oculus ready

We've collaborated with Oculus to tune and test our machines for a smooth, seamless VR experience right out of the box.

HTC optimized

Tuned and tested with the engineers at HTC, we've stressed the hardware and drivers with the most intensive games to ensure an optimal VR experience right out of the box.

Single access panel

Quickly access your PC's internals with the large, single panel on the bottom of the laptop. Held on by only a few screws, it's easily removable for upgrading or maintenance.

OMEN Command Center

Set up devastating one-click key combinations with included software that gives control over the customizable macro keys. This easy-to-use interface also helps prioritize gaming traffic, minimizing network latency

HP Jumpstart

When you boot up your PC for the first time, get a personal walkthrough during the setup and get an informative overview of your PC's features.

Specifications

Chipset	Intel® HM370
Display size (diagonal)	43.9 cm (17.3")
Display size (diagonal)	17.3"
Audio features	Bang & Olufsen, dual speakers, HP Audio Boost
Minimum dimensions (W x D x H)	42.3 x 30.4 x 3.3 cm <i>(Dimensions vary by configuration)</i>
Minimum dimensions (W x D x H)	16.65 x 11.97 x 1.3 in
Weight	3.73 kg <i>(Weight varies by configuration)</i>
Weight	8.23 lb
Ports	1 Thunderbolt™ 3 (Data Transfer up to 40 Gb/s, DP1.2, HP Sleep and Charge); 3 USB 3.1 Gen 1 (1 HP Sleep and Charge); 1 Mini DisplayPort™; 1 HDMI; 1 RJ-45; 1 headphone/microphone combo; 1 microphone-in
Expansion slots	1 multi-format SD media card reader
Package weight	4.56 kg
Network interface	Integrated 10/100/1000 GbE LAN
Security management	Kensington NanoSaver™ security lock support

Accessories and services

No Recommended Accessories and Services

Messaging Footnotes

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

[4] USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2018 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com>.

Microsoft, Windows, and the Windows Logo are U.S. registered trademarks of Microsoft Corporation. Bluetooth is a trademark of its proprietor and used by Hewlett-Packard Company under license. Intel and Core are trademarks of Intel Corporation in the U.S. and other countries. ENERGY STAR is a registered mark owned by the U.S. government. All other trademarks are the property of their respective owners.

