

Thunderbolt 3 to FireWire Adapter - Card & Chassis

Product ID: BNDTB1394B3



The Thunderbolt 3 to 1394 FireWire adapter connects your FireWire peripherals to your Thunderbolt 3 computer. This adapter combines StarTech.com's Thunderbolt 3 PCIe Expansion Chassis (TB31PCIEX16) and 1394 FireWire adapter card (PEX1394B3). The chassis uses Thunderbolt 3 technology, the fastest connection available, supporting your FireWire devices, plus one DisplayPort output and one additional Thunderbolt 3 port.

Use your legacy FireWire devices with your next-generation Thunderbolt 3 computer, without having to pay for upgraded peripherals.

Thunderbolt 3 is the fastest connection available. By avoiding performance bottlenecks, you can accomplish more in the same amount of time. With 40Gbps of throughput and support for other high-performance PCIe cards, you can swap the card in and out, to add the peripherals you need connected to a Thunderbolt 3 desktop or laptop computer.

Both hot-swap and backward compatible, you can assemble and connect this adapter in minutes. Install the PCIe card using only a Phillips type screwdriver, then plug and play with automatic driver installation.

The TB31PCIEX16 is backed by StarTech.com's 2-year warranty.

The PEX1394B3 is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Ideal for anyone who wants to upgrade their laptop without having to upgrade their legacy FireWire peripherals
- Daisy chain up to six Thunderbolt 3 devices and expand your workstation to suit your specific requirements
- Great for connecting DV camcorders, external hard drives, digital cameras, and other high-powered FireWire

peripherals to your Thunderbolt 3 laptop

- Ideal for those who may need to swap the included FireWire card with other types of PCI Express devices such as USB-A and USB-C cards, SSDs, network adapters, eSATA cards, and video capture cards

Features

- Save on peripheral upgrade costs by adapting legacy FireWire peripherals to Thunderbolt 3 devices
- Create an efficient workstation with extra displays, using the DisplayPort output and additional Thunderbolt 3 port
- Upgrade your peripheral connections without having to upgrade your chassis by just switching out your PCIe card
- Install the PCIe card easily with just a screwdriver and automatic driver installation

Hardware

Warranty	2 Years
Fan(s)	Yes
Fans	92 mm
Ports	6
Air Flow Rate	14.06 CFM
Noise Level	24.55 dB
Interface	Thunderbolt FireWire 800 (1394b) FireWire 400 (1394a)
Bus Type	Thunderbolt 3 PCI Express
Card Type	Standard Profile
Industry Standards	Thunderbolt 3 IEEE-1394/1394A/1394B OHCI PCI Express 1.1
Fan Bearing Type	Sleeve Bearing

Chipset ID	Intel - Alpine Ridge DSL6540 (Thunderbolt Chassis) Texas Instruments - XIO2213B (Firewire card)
------------	--

Performance

Maximum Data Transfer Rate	40Gbps (Thunderbolt 3)
	800Mbps (Firewire)
	400Mbps (Firewire)
Bandwidth	3.94 GB/s (x4 PCIe 3.0)
Type and Rate	Thunderbolt 3 - 40 Gbit/s

Connector(s)

Connector Type(s)	PCI Express x1
Internal Ports	LP4 (4 pin; Large Drive Power)
	PCI Express x16
External Ports	FireWire 400 (6 pin, IEEE 1394a)
	FireWire 800 (9 pin, IEEE 1394b)
	Thunderbolt 3 USB-C (24-pin) (40Gbps)
	DisplayPort (20 pin)

Special Notes / Requirements

System and Cable Requirements	Thunderbolt 3 equipped computer with a Thunderbolt 3 port.
-------------------------------	--

Note The expansion chassis does not support video cards.

This expansion chassis does not provide full power delivery but will provide 15W of power, resulting in a slow charge to some laptops, such as the MacBook Pro. When the dock is connected to your host laptop, a charging icon may appear on your laptop's screen. This is only sufficient enough to charge your laptop in sleep state, and charging will require an extended time period.

5K support can only be achieved using a Thunderbolt 3 5K monitor. DisplayPort 5K monitors will not work with this expansion chassis.

A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).

Certain monitors may be limited to 4K at 30Hz when connecting through DisplayPort. These monitors include the following models: Dell



P2715Q, Viewsonic VX2475Smhl-4K, Philips 288P6LJEB, LG 31MU97C-B, Asus PB287Q (these models will need to be set to 4K at 30Hz).

When connecting a display to one of the Thunderbolt 3 USB-C ports, a USB-C video adapter might be required depending on the input of your display.

Secondary Thunderbolt 3 port can also be used to connect USB 3.1 (10Gbps) USB-Type C devices, such as USB 3.1 Hubs. Backwards compatible with USB 3.0 (USB 3.1 Gen 1), and USB 2.0.

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	2A
Output Voltage	12V DC
Output Current	5.417A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	65

Environmental

Operating Temperature	Chassis: 5C to 35C (41F to 95F)
	PCIe Card: 0C to 70C (32F to 158F)
Storage Temperature	Chassis: -20C to 50C (-4F to 122F)
	PCIe Card: -54C to 150C (-65F to 302F)
Humidity	Chassis: 20 ~ 80%RH

Physical Characteristics

Color	Black
Material	Aluminum and Steel
Cable Length	19.7 in [50 cm]
Product Length	11.0 in [28 cm]



Product Width	5.6 in [14.2 cm]
Product Height	3.2 in [82 mm]
Weight of Product	3.7 lb [1.7 kg]

**Packaging
Information**

Package Length	14.2 in [36 cm]
Package Width	11.4 in [29 cm]
Package Height	5.7 in [14.5 cm]
Shipping (Package) Weight	7.4 lb [3.3 kg]

****Product appearance and specifications are subject to change without notice.***

