

TeraStation™ 5010 Series

TS5210DN, TS5410DN, TS5410RN, TS5810DN, TS51210RH



HIGH PERFORMANCE BUSINESS CLASS SCALABLE STORAGE SOLUTION

TeraStation 5010 is a business-class network attached storage (NAS) including hard drives* featuring high performance processing power, and native 10GbE support. Accelerate speed and overall performance with business class processing power supporting 100 concurrent sessions with sustained performance even during heavy-load operations.

TeraStation 5810DN is an eight bay desktop system featuring a native 10GbE port. Base models ship with NAS-grade hard drives allowing future scalability. Users with defined storage needs can order fully populated models with eight NAS-grade hard drives up to 64TB of storage capacity.

TeraStation 51210RH is a 2U rackmount system offering scalability. Base models ship with four enterprise-grade hard drives allowing users to meet future storage demands by simply adding additional hard drives. Users with defined storage needs have the ability to select fully populated systems with twelve enterprise-grade hard drives included up to 96TB total storage capacity. TeraStation 51210RH includes dual 10GbE ports and a rail kit for easy deployment.

Strong Performance

- Premium grade components (NAS & Enterprise-grade hard drives)
- Up to 2 native 10GbE ports*
- Quad-core Annapurna processor
- VMware certified (iSCSI & NFS certifications)*

Enhanced Security and Reliability

- 256-bit AES encryption
- Premium metal chassis with Kensington security slot and front panel lock*
- Boot Authentication - locks device until authenticated on network in case of theft
- Duplex Firmware for reduced system downtime

Simple Experience

- Hard drives included*
- Industrial-grade internal power supply
- Pre-configured RAID enabled systems
- 24/7 North American based support

Business Class Solutions

- Private & 3rd party integrated cloud support
- Novastor Business Essentials server and workstation licensing
- Use cases include: Virtualized storage target, Offsite disaster recovery, and File sharing & local backup



AT BUFFALO, WE'RE ALWAYS ON

At Buffalo, we work hard to make sure peace of mind is included with all Buffalo products. This starts with products are reliable, easy to deploy and supported after the sale. Our 24/7 North American-based team is on hand to help identify solutions that are the right fit for your business.

Once your product is deployed our team is available to resolve any questions or issues.

*TS5210DN, TS5410DN, TS5810DN and TS5410RN ship with NAS-grade hard drives. TS51210RH ship with enterprise-grade hard drives and two native 10GbE ports.

*TS5210DN, TS5410DN, TS5810DN include Kensington security slot and front panel lock

High Performance Scalable Solution

MODELS	TS5210DN (2-BAY)	TS5410DN (4-BAY)	TS5410RN (4-BAY)	TS5810DN (8-BAY)	TS51210RH (12-BAY)				
Part Numbers	TS5210DN0402 TS5210DN0802	TS5410DN0804 TS5410DN1604 TS5410DN2404 TS5410DN3204	TS5410RN0804 TS5410RN1604 TS5410RN2404 TS5410RN3204	TS5810DN1604 4 X 4TB TS5810DN3204 4 X 8TB TS5810DN3208 8 X 4TB TS5810DN6408 8 X 8TB	TS51210RH1604 4 X 4TB TS51210RH3204 4 X 8TB TS51210RH4004 4 X 10TB TS51210RH4812 12 X 4TB TS51210RH9612 12 X 8TB TS51210RH12010 12 X 10TB				
Configuration	Desktop	Desktop	Rackmount	Desktop	Rackmount				
INTERNAL HARD DRIVES									
Number of included Drives	2	4	4	4 or 8	4 or 12				
Total Capacity	4 or 8 TB	8, 16, 24 or 32 TB	8, 16, 24 or 32 TB	16, 32 or 64 TB	16, 32, 40, 48, 96 or 120 TB				
Drive Interface	SATA III (6 Gbps)	SATA III (6 Gbps)	SATA III (6 Gbps)	SATA III (6 Gbps)	SATA III (6 Gbps)				
Supported RAID	0/1/ JBOD (Individual Disks)	0/1/5/6/10/ JBOD (Individual Disks)	0/1/5/6/10/ JBOD (Individual Disks)	0/1/5/6/10/ JBOD (Individual Disks)	0/1/5/6/10/JBOD (Individual Disks)				
USB INTERFACE									
Number of Ports	2x USB 3.0	2x USB 3.0	3x USB 3.0	3x USB 3.0	2x USB 3.0, 2x USB 2.0				
PERFORMANCE									
CPU	Annapurna Labs® Alpine Processor AL314 (1.7 GHz Quad-Core)	Annapurna Labs® Alpine Processor AL314 (1.7 GHz Quad-Core)	Annapurna Labs® Alpine Processor AL314 (1.7 GHz Quad-Core)	Annapurna Labs® Alpine Processor AL314 (1.7 GHz Quad-Core)	Annapurna Labs® Alpine Processor AL314 (1.7 GHz Quad-Core)				
Memory	4 GB DDR3 with ECC	4 GB DDR3 with ECC	4 GB DDR3 with ECC	4 GB DDR3 with ECC	8 GB DDR3 with ECC				
ENVIRONMENTAL & POWER									
Power Consumption	Max 85W Data Transfer 45W Idling 32W	Max 85W Data Transfer 56W Idling 45W	Max 100W Data Transfer 60W Idling 46W	Max 150W Data Transfer 108W Idling 87W	Max 500W Data Transfer 122W Idling 100W				
Power Supply	Internal AC 100-240V Universal 50/60Hz	Internal AC 100-240V Universal 50/60Hz	Internal AC 100-240V Universal 50/60Hz	Internal AC 100-240V Universal 50/60Hz	**Internal AC 100-240V Universal 50/60Hz				
Operating Temperature	32° - 104°F (0° - 40°C)	32° - 104°F (0° - 40°C)	32° - 104°F (0° - 40°C)	32° - 104°F (0° - 40°C)	32° - 104°F (0° - 40°C)				
Operating Humidity	10 - 85% non-condensing	10 - 85% non-condensing	10 - 85% non-condensing	10 - 85% non-condensing	10 - 85% non-condensing				
SHIPPING									
Unit Dimensions (LxWxH)	9.06 x 6.69 x 6.69 in	9.06 x 6.69 x 8.46 in	16.93 x 16.93 x 1.74 in	11.81 x 8.46 x 9.06 in	29.01 x 18.94 x 3.46 in				
Unit Weight	10.58 lbs	15.43 lbs	18.52 lbs	20.72 - 27.55 lbs	41.67 - 53.13 lbs				
LAN INTERFACE									
Standards Compliance	IEEE802.3an (10GBASE-T), IEEE802.3bz (5GBASE-T/2.5GBASE-T), IEEE802.3ab (1000BASE-T), IEEE802.3u (100BASE-TX), IEEE802.3 (10BASE-T)								
Number of Ports	1 (10GBASE-T)*, 2 (1000BASE-T)	*TS51210RH includes second 10GBASE-T port							
File Share Protocol	CIFS/SMB, AFP, FTP, SFTP, NFS, SNMP								
Connector Type	RJ-45								
CLIENT OS SUPPORT	Windows® 10, Windows® 8.1 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Server® 2016, Windows Server® 2012, Windows Server® 2012R2, Windows Server® 2008, Windows Server® 2008R2, Mac® OS® X 10.9 or later								
WARRANTY	Comes with standard 3-year warranty. TS51210RH features standard 5-year warranty when registered within 90 days of purchase								
ACCESSORIES	Enhanced Warranty, Keep Your Drive Warranty Service, Next Business Day Warranty Service								
Warranties									
**Optional Redundant Power Supply	OP-PU-10R2UWR (TS51210RH only)								

TeraStation™ 5010 Series

©2017 BUFFALO INC. All rights reserved. BUFFALO and BUFFALO logo are either trademarks or registered trademarks of MELCO HOLDINGS INC. TeraStation is a trademark of BUFFALO INC. Microsoft Windows and Windows logo are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Mac OS is a trademark of Apple Inc., registered in the U.S. and other countries. The names and logos of other companies mentioned herein belong to their respective owners.