

AMR2P32V

Dual Monitor Pole Vertical Mount Max 32" Monitors

The AMR2P32V is a vertical pole style adjustable monitor mount for LCD / LED TVs. Made with industrial grade steel and aluminum alloy to ensure reliability and ease of use. This mount has the ability to hold two monitors with a maximum length of 32" and weight of 26.5lb each vesa plate.

AMR2P32V features :

1. Easy Cable Management cover & column to make the cables tidy & well arranged.
2. The gap of each display monitor can be adjusted while height can be adjusted too.
3. The Smart Torque Adjust is always available at every Hinge Module to cater towards different weight specifications
4. Quick Release [™] on each ARM to ensure ease of removal or installation.



Specifications

General

Mounting Pattern:	• 200x200 / 100x100 / 75x75mm	Screw Type:	• M4, M5, M6, M8
Material:	• Steel/Aluminum Alloy/Plastic	Dimensions (W*H*D):	• 226 x 965 x 128 mm 8.90" x 37.99" x 5.03"
Weight:	• 3.25kg (7.17lbs)	Swivel(Hinge):	• Adjustable
User Torque Adjust:	• Available	Display Type:	• Dual Monitor
Tilt(Hinge):	• Max. + / -15°	Rotate(Pivot):	• 360°
Support Max Weight:	• 12kg (26.5lbs)(Per plate)	Support Flat Panel Size:	• 24" - 32"
Height Adjustment Range:	• 890mm (35.04)	Cable Management:	• Yes

Warranty and Support

Warranty: 3 Years
Support: Free technical support (phone/email)

www.amer.com / www.amermounts.com

sales@amer.com
1-800-262-9703

Specifications subject to change without notice. Errors and omissions excepted. All trademarks are properties of their respective owners.

Revision 1.00