

# DynamiQ™ mMount

## Motorized, height adjustable wall mount

The DynamiQ mMount provides height adjustable capabilities with a motorized wall mounting system. The double-column design provides the stability needed to work with large interactive touchscreens up to 86".

The wired remote controller may be placed at a convenient and easy-to-reach location, allowing the user to adjust the height of the screen safely and quietly. The motorized mount has an anti-collision feature to prevent accidental pinching, when the system is moving and senses an obstruction it will stop and retreat. In its lowest position, the monitor allows easy access for users in wheelchairs.

A lockbox is located on the back of the VESA mounting box, which safely stores the electric controls. The lockbox also may be used for a mini PC or other small equipment.


With the optional accessories, the product may be equipped for use with a laptop or keyboard tray, teleconferencing equipment, camera, or sound bar.

### FEATURES

- Supports a single display up to 265 lbs.
- Motorized double columns provide height adjustable control
- VESA mounting box
- Wired remote control with 5' cable
- Rear lock box for storage or technology

### SPECIFICATIONS

DIMENSIONS	VERTICAL ADJUST	LOAD CAPACITY	DISPLAY SIZE	PART NUMBER
45.75"H x 30.4"W x 42"L	34.25"	265 lbs	up to 86"	AVT-487A02
45.75"H x 48"W x 42"L			55" Cisco Spark Board	AVT-487A02-CSB55
45.75"H x 62"W x 42"L			70" Cisco Spark Board	AVT-487A02-CSB70



Call 800.285.8315 or visit AVTEQ.net

[facebook.com/avteq](https://www.facebook.com/avteq) [twitter.com/avteqinc](https://twitter.com/avteqinc) [youtube.com/avteq](https://www.youtube.com/avteq)



Need a custom solution?  
Give us call.