

## USB-C to USB-C Cable w/ 5A PD - M/M - 2 m (6 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2C5C2M



With up to 5A (100W) of power output, you can use this USB-C™ to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel™, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

### Fast-charge your mobile devices

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready, whenever you need them while you're on the road.

### Provide superior connections with USB-IF certified cables

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C2M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop

### Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Thunderbolt™ 3 port compatible
- Guaranteed reliability with our 2-year warranty

|                                 |                           |  |
|---------------------------------|---------------------------|--|
| <b>Hardware</b>                 | Warranty                  | 2 Years  |
|                                 | Cable Jacket Type         | PVC - Polyvinyl Chloride                       |
|                                 | Cable Shield Type         | Aluminum-Mylar Foil with Braid                 |
|                                 | Connector Plating         | Nickel   |
| <b>Performance</b>              | Type and Rate             | USB 2.0 - 480 Mbit/s                           |
| <b>Connector(s)</b>             | Connector A               | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) Male |
|                                 | Connector B               | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) Male |
| <b>Power</b>                    | Power Delivery            | 100W   |
| <b>Physical Characteristics</b> | Cable Length              | 6.6 ft [2 m]                                   |
|                                 | Color                     | Black  |
|                                 | Connector Style           | Straight                                       |
|                                 | Product Height            | 0.2 in [0.6 cm]                                |
|                                 | Product Length            | 6.6 ft [2 m]                                   |
|                                 | Product Width             | 0.5 in [12 mm]                                 |
|                                 | Weight of Product         | 3.9 oz [111 g]                                 |
|                                 | Wire Gauge                | 24/26 AWG                                      |
| <b>Packaging Information</b>    | Package Height            | 0.4 in [10 mm]                                 |
|                                 | Package Length            | 8.9 in [22.5 cm]                               |
|                                 | Package Width             | 4.9 in [12.5 cm]                               |
|                                 | Shipping (Package) Weight | 4.1 oz [116 g]                                 |
| <b>What's in the Box</b>        | Included in Package       | 1 - USB-C cable                                |

Product appearance and specifications are subject to change without notice.