

GDPSP2

## 2-Port DisplayPort 1.2 Graphics Splitter / Multi- Monitor MST Video Hub



- Connect 2 independent displays to a single DisplayPort 1.2 video output
- Mirror or extend a desktop across 2 displays from a computer with 1 DisplayPort output
- Enjoy Ultra 4K video resolutions up to 4096 x 2160 @ 60HZ

### 2-Port DisplayPort Splitter and MST Hub


Connect two displays from a single DisplayPort 1.2-enabled computer with the IOGEAR 2-Port DisplayPort Splitter/MST Hub. Increase productivity and workflow by expanding the amount of usable screen space on two independent screens for multi-document viewing, media streaming, and content/web browsing, or mirror your computer's display across two monitors to allow remote viewing applications such as monitoring equipment diagnostics or the status of a remote server.

### 4K Ultra High Definition (DCI) Video Support

IOGEAR's 2-Port DisplayPort 1.2 Splitter and MST Hub supports high-resolutions up to 4096 x 2160 @ 60Hz and is ideal for use with applications such as medical imaging, graphic design, gaming, and more.

- Connect 2 independent displays from a single DisplayPort 1.2 video output
- Mirror or extend a desktop across 2 displays from a computer with 1 DisplayPort output
- Enjoy Ultra 4K video resolutions up to 4096 x 2160 @ 60HZ
- With DisplayPort 1.2 Graphic Cards:
  - 2 Monitors: Up to 4K 4096 x 2160 (DisplayPort/HDMI)
- Supports 7.1 digital audio surround sound
- Push-button toggle between Single Stream Transport (SST) and Multi-Stream Transport (MST)
- DPCP and HDCP compliant
- No driver or software installation needed
- Supports DisplayPort 1.2a; HDCP 1.3





### Requirements

- **Hardware:**
- Computer with DisplayPort 1.2 compatible graphics card
- 2 Monitors with DisplayPort ports
- 
- **Optional:**
- G2LDPDP02 DisplayPort to DisplayPort Cable

### Package Contents

- 1 x GDPSP2 2-Port DisplayPort Splitter / MST Hub
- 1 x Power Adapter
- 1 x Quick Start Guide
- 1 x Warranty Card

## Specifications

Function	GDPSP2
<b>Cable Connections</b>	
Input	DisplayPort 1.2
Output	DisplayPort
<b>Connectors</b>	
Video Input	1 x DisplayPort Female
Video Output	2 x DisplayPort Female
Data Rate	Up to 5.4Gbps
<b>Environment</b>	
Humidity	20~90% RH (Non Condensing)
Operation Temperature	32°F~104°F (0°C~40°C)
Storage Temperature	-4°F~140°F (-20°C~60°C)
<b>Housing</b>	
Case	Metal
<b>LEDs</b>	
Input	1
Output	2
<b>Power</b>	
Amps	2A
Voltage	DC 5V
Video Resolution	Up to 4K@60Hz
<b>Audio</b>	
Codec	2-Ch LPCM / AC3 / DTS
Sample Rate	32-192kHz

Dimensions	GDPSP2
<b>Unit Dimensions</b>	
Height	1" (2.5 cm)
Depth	4.4" (11.1 cm)
Length	3" (7.6 cm)
<b>Unit Package Dimensions</b>	
Width	9.4" (23.8 cm)
Height	2.32" (5.9 cm)
Depth	6.3" (16 cm)
<b>Master Carton</b>	
Width	14.89" (37.8 cm)
Height	10.04" (25.5 cm)
Depth	7.17" (18.2 cm)
Master Carton Qty.	6
<b>Weight</b>	
Master Carton Wt.	8.95 lb
Unit Pack Wt.	1.3 lb (0.6 kg)
Unit Wt.	0.45 lb (0.2 kg)