## **CyberPower**

# OL10KRT SMART APP ONLINE UPS SYSTEM

Providing mission-critical enterprise applications maximum power protection.



The CyberPower Smart App Online OL10KRT is a 6U rack/tower double-conversion UPS. It provides sine wave output to multiple types of critical IT infrastructure requiring seamless power protection. The OL10KRT is generator compatible and delivers consistent 200-240 V power with zero-transfer time. Automatic-bypass ensures connected equipment continues to operate seamlessly when an overload or internal fault is detected.

The OL10KRT features a removable LCD control panel to reposition it in a more convenient location (with optional DB-26 cable), and it has a RMCARD205 pre-installed network card. Smart-battery management charging technology increases battery life by up to 50%. Fast-charge technology helps replenish battery charge from 0-90% in five hours, regardless of the number of Extended Battery Modules (EBM) connected. The energy-saving GreenPower UPS™ ECO Mode allows the UPS to reach up to 97% efficiency to reduce power consumption and thermal dissipation.

This UPS can use the BP240VL3U01 extended battery module for more runtime. The OL10KRT comes with a three-year warranty (including batteries) and a \$300,000 connected equipment guarantee.

#### **TYPICAL APPLICATIONS**

- Server Rooms
- Server Virtualization Infrastructures (VMware, Hyper-V, Citrix)
- Hyperconverged Infrastructure (HCI)
- Core Network Equipment
- Storage Systems
- · VoIP Infrastructure

#### **FEATURES**

- 10,000 V/10,000 W
- Double Conversion Topology
- Sine Wave Output, Zero Transfer Time
- Output: 200-240 V
- GreenPower UPS™ ECO Mode
- Removable LCD Control Panel
- Generator Compatibility Mode

#### **SPECIFICATIONS**

GENERAL	
UPS Topology	Double Conversion
Energy Saving	Yes - ECO Mode Efficiency up to 97%
INPUT	
Nominal Voltage	200 V to 240 V
Voltage Range	120 V to 139 V, 0% to 25% load 140 V to 159 V, 0% to 50% load 160 V to 179 V, 0% to 75% load 180 V to 280 V, 0% to 100% load
Frequency Range	40 Hz to 70 Hz (auto-sensing)
Power Factor	0.99

INPUT CONT.		
Cold Start	Yes	
Backfeed Protection	Yes	
Plug Type	Hardwire	
OUTPUT		
VA	10,000 (10 kVA)	
Watts	10,000 (10 kW)	
Power Factor	1	
Waveform (Battery Mode)	Sine wave	

# OL10KRT SMART APP ONLINE UPS SYSTEM



### **SPECIFICATIONS CONT.**

OUTPUT CONT.	OUTPUT CONT.	
Frequency	50/60 Hz ±0.25 Hz (auto-sensing/configurable)	
ECO Mode Bypass Voltage Range	±10%, ±15% (configurable)	
Harmonic Distortion	<3% at linear load, <5% at non-linear load	
Crest Factor	3:1	
Outlets - Total	4	
Outlet Type	(3) NEMA L6-30R, (1) Hardwire Terminal Block	
Overload Protection	Line Mode: 105% to 125% load for 1 min 126% to 150% load for 10 s Battery Mode: 105% to 130% load for 10 s 131% to 150% load for 2 s	
Short Circuit Protection	UPS Output Cut off Immediately or Input Fuse/ Circuit Breaker Protection	
Bypass	Internal Bypass (Automatic and Manual)	
Transfer Time	0 ms	
BATTERY		
Runtime at Half Load	10 min	
Runtime at Full Load	3.6 min	
Battery Type	Sealed lead acid	
Battery Size	12 V/9 Ah	
Battery Quantity	20	
Replaceable	Yes	
Replacement Battery	(2) RB1290X10	
Hot Swappable	Yes	
Typical Recharge Time	5 h (0% to 90%)	
Smart Battery Management (SMB) Mode	Yes	
Extended Battery Module (EBM)	Optional BP240VL3U01	

SURGE PROTECTION AND FILTERING		
Surge Protection	2430 Joules, per IEC 61000-4-5 Level 3	
Phone RJ-11 / Ethernet Surge Protection RJ-45	1-In / 1-Out (Combo)	
EMI/RFI Filtration	Yes	
MANAGEMENT AND CO	MMUNICATION	
LCD Control Panel	Access 50 information status and configuration settings via the Information and Configuration Menus, in addition to an Event Log Menu.	
Rotatable LCD Control Panel Option	Yes	
Removable LCD Control Panel Option	Yes - Requires DB26 cable (not included)	
HID Compliant USB Port	Yes	
Serial Port	Yes	
Emergency Power Off (EPO) Port	Yes	
Dry Contact Port	Yes	
Cables Included	USB cable, serial cable, phone cable	
LED Indicators	Power On (White) Line Mode (Green) Battery Mode (Yellow) Bypass Mode (Yellow) Fault (Red) Replace Battery (Red)	
Audible Alarms	Battery Mode, Battery Low, Overload, UPS Fault	
Software	PowerPanel® Business Edition	
Upgradeable Firmware	Yes	
Expansion Slot	Yes - RMCARD205 pre-installed	
PHYSICAL		
Form Factor	Rack / Tower convertible (rotatable LCD)	
Enclosure Contruction	Steel	
Rack Mounting Hardware	Included	

# OL10KRT SMART APP ONLINE UPS SYSTEM



### **SPECIFICATIONS CONT.**

PHYSICAL CONT.	
Dimensions (WxHxD, in)	17 x 10.5 x 26
Dimensions (WxHxD, mm)	433 x 266 x 660
Weight (lb)	226.6
Weight (kg)	103
Rack Units	6U
Max. Mounting Rail Depth (in)	36.02
Max. Mounting Rail Depth (mm)	915
Min. Mounting Rail Depth (in)	20.47
Min. Mounting Rail Depth (mm)	520
PHYSICAL - POWER MODULE	
Dimensions (WxHxD, in)	17 x 5.25 x 26
Dimensions (WxHxD, mm)	433 x 132 x 660
Weight (lb)	55
Weight (kg)	25
Rack Units	3U
PHYSICAL - BATTERY MODULE	
Dimensions (WxHxD, in)	17 x 5.25 x 26
Dimensions (WxHxD, mm)	433 x 132 x 660
Weight (lb)	171.6
Weight (kg)	78
Rack Units	3U

SHIPPING DIMENSIONS		
Dimensions (WxHxD, in)	23.62 x 25.12 x 35.43	
Dimensions (WxHxD, mm)	600 x 638 x 900	
Weight (lb)	279.4	
Weight (kg)	126.75	
ENVIRONMENTAL		
Operating Temperature	32°F to 104°F (0°C to 40°C)	
Operating Relative Humidity	0% to 90% (non-condensing)	
Operating Elevation	0 ft to 10,000 ft (0 to 3,000 m)	
Storage Temperature	-4°F to 113°F (-20°C to 45°C)	
Storage Relative Humidity	0% to 95% (non-condensing)	
Storage Elevation	0 ft to 50,000 ft (0 m to 15,000 m)	
UPS Online Thermal Dissipation (100% load)	3211 BTU/h	
ECO Mode Thermal Dissipation (100% load)	1019 BTU/h	
Audible noise at 1 m from surface of unit	38 dBA to 65 dBA (0% to 100% load)	
CERTIFICATIONS		
Safety	UL 1778 5th Ed. CSA C22.2 NO.107.3-05 FCC Part 15 Class A	
Environmental	ROHS Compliant	
WARRANTY		
Product Warranty	Three-Years Limited	
Extended 2-Year Warranty	Optional WEXT5YR-U20C	
Connected Equipment Guarantee	Lifetime	
CEG Amount	\$300,000	