

Cisco UCS C220 M5 Rack Server



The Cisco UCS[®] C220 M5 Rack Server delivers record-breaking performance for space-constrained environments.

Product overview

The Cisco UCS C220 M5 Rack Server is among the most versatile general-purpose enterprise infrastructure and application servers in the industry. It is a high-density 2-socket rack server that delivers industry-leading performance and efficiency for a wide range of workloads, including virtualization, collaboration, and bare-metal applications. The Cisco UCS C-Series Rack Servers can be deployed as standalone servers or as part of the Cisco Unified Computing System[™] (Cisco UCS) to take advantage of Cisco's standards-based unified computing innovations that help reduce customers' Total Cost of Ownership (TCO) and increase their business agility.

The Cisco UCS C220 M5 server extends the capabilities of the Cisco UCS portfolio in a 1-Rack-Unit (1RU) form factor. It incorporates the Intel[®] Xeon[®] Scalable processors, supporting up to 20 percent more cores per socket, twice the memory capacity, 20 percent greater storage density, and five times more PCIe NVMe Solid-State Disks (SSDs) compared to the previous generation of servers. These improvements deliver significant performance and efficiency gains that will improve your application performance. The C220 M5 delivers outstanding levels of expandability and performance in a compact package, with:

- Latest Intel Xeon Scalable CPUs with up to 28 cores per socket
- Up to 24 DDR4 DIMMs for improved performance
- Up to 10 Small-Form-Factor (SFF) 2.5-inch drives or 4 Large-Form-Factor (LFF) 3.5-inch drives (77 TB storage capacity with all NVMe PCIe SSDs)
- Support for 12-Gbps SAS modular RAID controller in a dedicated slot, leaving the remaining PCIe Generation 3.0 slots available for other expansion cards
- Modular LAN-On-Motherboard (mLOM) slot that can be used to install a Cisco UCS Virtual Interface Card (VIC) without consuming a PCIe slot
- Dual embedded Intel x550 10GBASE-T LAN-On-Motherboard (LOM) ports

Powering next-generation applications

The Cisco UCS C220 M5 Rack Server is well-suited for a wide range of workloads, including:

- IT and web infrastructure
- High-performance virtual desktops
- Medium-sized and distributed databases
- Middleware
- Collaboration
- Public cloud

C220 M5 servers can be deployed as standalone servers or in a Cisco UCS managed environment. When used in combination with Cisco UCS Manager, the C220 M5 brings the power and automation of unified computing to enterprise applications, including Cisco® SingleConnect technology, drastically reducing switching and cabling requirements.

Cisco UCS Manager uses service profiles, templates, and policy-based management to enable rapid deployment and help ensure deployment consistency. It also enables end-to-end server visibility, management, and control in both virtualized and bare-metal environments.

The Cisco Integrated Management Controller (IMC) delivers comprehensive out-of-band server management with support for many industry standards, including:

- Redfish Version 1.01 (v1.01)
- Intelligent Platform Management Interface (IPMI) v2.0
- Simple Network Management Protocol (SNMP) v2 and v3
- Syslog
- Simple Mail Transfer Protocol (SMTP)
- Key Management Interoperability Protocol (KMIP)
- HTML5 GUI
- HTML5 virtual Keyboard, Video, and Mouse (vKVM)
- Command-Line Interface (CLI)
- XML API

Management Software Development Kits (SDKs) and DevOps integrations exist for Python, Microsoft PowerShell, Ansible, Puppet, Chef, and more. For more information about integrations, see [Cisco DevNet](#).

The C220 M5 is Cisco Intersight™ ready. Cisco Intersight is a new cloud-based management platform that uses analytics to deliver proactive automation and support. By combining intelligence with automated actions, you can reduce costs dramatically and resolve issues more quickly.

Product specifications

Table 1 lists the specifications for the Cisco UCS C220 M5 Rack Server.

Table 1. Specifications

Item	Specifications
Form factor	1RU rack server
Processors	Intel Xeon Scalable processors (1 or 2)
Memory	24 DDR4 DIMM slots: 8, 16, 32, 64, and 128 GB and up to 2666 MHz
PCIe expansion	2 PCIe 3.0 slots plus 1 dedicated 12-Gbps RAID controller slot and 1 dedicated mLOM slot
RAID controllers	<ul style="list-style-type: none"> Internal controllers: Cisco 12-Gbps Modular RAID Controller (PCIe 3.0) with 1- or 2-GB Flash-Backed Write Cache (FBWC), providing enterprise-class data protection for up to 10 SAS and SATA Hard-Disk Drives (HDDs), SSDs, or NVMe PCIe SSDs; or Cisco 12-Gbps Modular SAS Host Bus Adapter (HBA) External controller: Cisco 12-Gbps 9400-8e SAS HBA
Internal storage	<p>Backplane options:</p> <ul style="list-style-type: none"> Up to 10 x 2.5-inch SAS and SATA HDDs and SSDs and up to 2 NVMe PCIe drives Up to 10 x 2.5-inch NVMe PCIe drives Up to 4 x 3.5-inch SAS and SATA HDDs and SSDs and up to 2 NVMe PCIe drives
Embedded Network Interface Cards (NICs)	Dual 10GBASE-T Intel x550 Ethernet ports
mLOM	Dedicated mLOM slot that can flexibly accommodate 1-, 10-, 25-, 40-, and 100-Gbps adapters
Power supplies	Hot-pluggable, redundant 770W AC, 1050W AC, 1050W DC, and 1600W AC
Other storage	<ul style="list-style-type: none"> Dual internal Cisco FlexFlash Secure Digital (SD) cards (32, 64, and 128 GB) for installing an operating system or hypervisor Support for RAID 0 mirroring between SD cards Dedicated Baseboard Management Controller (BMC) MicroSD card (32 GB) for server utilities Dual M.2 SATA SSD or NVMe
Management	<ul style="list-style-type: none"> Cisco Intersight™ Cisco IMC Cisco IMC Supervisor Cisco UCS Manager Cisco UCS Central Software Cisco UCS Director Cisco UCS Performance Manager
Rack options	Cisco ball-bearing rail kit or friction rail kit with optional reversible cable management arm
Hardware and software interoperability	See the Cisco Hardware and Software Interoperability List for a complete listing of supported operating systems and peripheral options.

System requirements

Table 2 lists system requirements for the server.

Table 2. System requirements

Item	Requirements
Cisco UCS Manager (optional)	Release 3.2(1) or later
Cisco IMC	Release 3.1(1) or later

Ordering information

For information about installing or upgrading your server, see the [Cisco UCS C220 M5 hardware installation guide](#).

For ordering information, see:

- [Cisco UCS C220 M5 SFF rack server specification sheet](#)
- Cisco UCS C220 M5 LFF rack server specification sheet

Warranty information

Cisco UCS C220 M5 Rack Servers have a 3-year Next-Business-Day (NBD) hardware warranty and 90-day software warranty.

Augmenting the Cisco UCS warranty, Cisco Smart Net Total Care™ and Cisco Solution Support services are part of Cisco's technical services portfolio. Cisco Smart Net Total Care combines Cisco's industry-leading and award-winning foundational technical services with an extra level of actionable business intelligence that is delivered to you through the smart capabilities in the Cisco Smart Net Total Care portal. For more information, please refer to <https://www.cisco.com/c/en/us/support/services/smart-net-total-care/index.html>.

Solution Support includes both Cisco product support and solution-level support, resolving complex issues in multivendor environments on average 43 percent more quickly than with product support alone. Solution Support is a critical element in data center administration, helping rapidly resolve any issue encountered while maintaining performance, reliability, and return on investment.

This service centralizes support across your multivendor Cisco environment for both our products and solution partner products you've deployed in your ecosystem. Whether there is an issue with a Cisco or solution partner product, just call us. Our experts are the primary point of contact and own the case from first call to resolution. For more information, please refer to <https://www.cisco.com/c/en/us/services/technical/solution-support.html>.

Cisco and partner services

Cisco and our industry-leading partners deliver services that accelerate your transition to a Cisco UCS C-Series Rack Servers solution. Cisco Unified Computing Services can help you create an agile infrastructure, accelerate time to value, reduce costs and risks, and maintain availability during deployment and migration. After deployment, our services can help you improve performance, availability, and resiliency as your business needs evolve and help you further mitigate risk. For more information, visit <https://www.cisco.com/go/unifiedcomputingservices>.

Cisco Capital

Financing to help you achieve your objectives

Cisco Capital can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce CapEx. Accelerate your growth. Optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital is available in more than 100 countries. [Learn more](#).

For more information

For more information about Cisco UCS servers, refer to <https://www.cisco.com/go/ucs>.



Americas Headquarters
Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters
Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters
Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)