



C2425dw

Reliability. Security. Productivity.



C2425dw



Google Cloud Print 2.0 Ready



Lexmark C2425dw

Start your colour journey with the Lexmark C2425dw, the printer that helps you control the cost of colour output at up to 25 ppm*. Built for reliability, performance and security, the Lexmark C2425dw comes equipped with both built-in Wi-Fi and tools to minimize toner consumption.



Ready when you are

- ▶ 1-GHz dual-core processor and 512 MB memory drives printing at up to 25 ppm.*
- ▶ Steel frame and durable design stands up to heavy use and harsh environments.
- ▶ Long-life fuser and imaging components extend uptime.
- ▶ Unison™ Toner replacement cartridges deliver up to 3500 colour and 6000 monochrome pages**.
- ▶ Keep printing in black even when colour toner is empty.

Colour that keeps saving

- ▶ PANTONE® calibration, embedded colour sample pages and Lexmark Colour Replacement produce accurate, professional colour output in house.
- ▶ Save toner with suite of tools that let you choose when and how much colour to print.

Input that works

- ▶ Reliable, flexible media handling supports cardstock, small media, and envelopes from the main tray or a convenient single-sheet feeder.
- ▶ 251 pages of standard input can grow to 901.

Interact with ease

- ▶ 2.4-inch/6-cm colour LCD lets you configure, interact and monitor vital system information.
- ▶ Front USB port allows walk-up printing from popular file formats without a computer.
- ▶ Compact footprint allows flexible placement in more locations.
- ▶ Connect easily via Ethernet, USB, Wi-Fi or simple mobile printing options.

Full-spectrum security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—in the document, on the device and over the network.
- ▶ Keypoint Intelligence - Buyers Lab honored Lexmark with a prestigious BLI PaceSetter award for Document Imaging Security***.



Built for planet earth

- ▶ Energy management features reduce power consumption in active use or sleep mode.
- ▶ Standard two-sided printing saves paper.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).

*Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds. **Average continuous black or continuous composite colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information.

***Award based on North America and/or Western Europe data

Lexmark C2425dw



1 Printer with 2.4-inch/6-cm LCD

12.1 x 17.4 x 16.6 inches

308 x 442 x 421 mm

2 650-sheet duo tray

5.2 x 16.7 x 16.4 inches

133 x 424 x 416 mm

Adjustable printer stand (not shown)

20.5 x 25.7 x 24.6 inches

521 x 653 x 625 mm

Swivel cabinet (not shown)

10.4 x 18.7 x 23.6 inches

263 x 476 x 600 mm

 Standard

 Optional

Note 1: Supports one optional tray.

Note 2: All measurements are shown as height x width x depth. For more information about supported configurations, refer to the Printer, Option and Stand Compatibility Guide at http://www.lexmark.com/publications/furniture_safety/

© 2018 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Google Cloud Print is a trademark of Google, Inc. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are trademarks, service marks, and certification marks of Mopria Alliance, Inc. in the United States and other countries. PANTONE®, PANTONE® Goe™ and other Pantone, Inc. trademarks are property of Pantone, Inc. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>).

Product specifications		Lexmark C2425dw
Printing		
Display	2.4-inch (60 mm) Colour LCD display	
Print Speed: Up to ⁵	Black: 25 ppm / Colour: 25 ppm	
Time to First Page: As fast as / Time to First Page: as fast as	Black: < 10.1 seconds / Colour: < 10.1 seconds	
Print Resolution	Black: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi) / Colour: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi)	
Memory / Processor	Standard: 512 MB / Maximum: 512 MB / Dual Core, 1000 MHz	
Hard Disk	Not Available	
Recommended Monthly Page Volume ¹	800 - 6500 pages	
Maximum Monthly Duty Cycle: Up to ²	75000 pages per month	
Supplies⁶		
Laser Cartridge Yields (up to)	1,000-page Black and Colour (CMYK) Cartridges, 6,000-page Black Extra High Yield Cartridge, Average continuous cartridge yield is stated number of standard pages as listed. Declared yield value in accordance with ISO/IEC 19798, 2,300-page Colour (CMY) High Yield Cartridges, 3,000-page Black High Yield Cartridge, 3,500-page Colour (CMY) Extra High Yield Cartridges	
Photoconductor Estimated Yield: Up to ⁴	40,000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage	
Cartridge(s) Shipping with Product	1,400-page Black Starter Return Program Toner Cartridge, 750-page Color (CMY) Starter Return Program Toner Cartridge	
Paper Handling		
Included Paper Handling	250-Sheet Input, 125-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed	
Optional Paper Handling	650-Sheet Duo Tray	
Paper Input Capacity: Up to	Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 900+1 pages 20 lb or 75 gsm bond	
Paper Output Capacity: Up to	Standard: 125 pages 20 lb or 75 gsm bond / Maximum: 125 pages 20 lb or 75 gsm bond	
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper, Vinyl Labels, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Hagaki Card, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6	
General Information³		
Standard Ports	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), 802.11b/g/n Wireless, Front USB 2.0 Specification Hi-Speed Certified port (Type A)	
Optional Network Ports	Marknet N8372 WiFi Option	
Noise Level: Operating	Print: 48 dBA	
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity, Altitude: 0 - 3048 meters, Temperature: 10 to 32°C (50 to 90°F)	
Limited Warranty - See Statement of Limited Warranty	1-Year Advanced Exchange, Next Business Day	
Size (mm - H x W x D) / Weight	308 x 442 x 421 mm / 21 kg	

All information in this brochure is subject to change without notice. Lexmark is not liable for any errors or omissions.

¹"Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ²"Maximum Monthly Duty Cycle" is defined as the maximum number of pages device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ³Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details. ⁴Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. ⁵Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds. ⁶Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details.