

Lenovo™ ThinkCentre M715q Thin Client

DO MORE WITH LESS


Combining power with energy efficiency, the sleek M715q Thin Client punches way above its weight. Built with productivity in mind, it's powered by the latest AMD processors and is virtualization- and cloud-ready. Easy to set up and use, it also comes with an intelligent thin-client management tool to help simplify things.

WHY YOU SHOULD BUY THE LENOVO™ THINKCENTRE M715q Thin Client




Powerful and future-proof

With the latest generation of AMD PRO 3.0 processors drawing on 35W of power and backed by 4G DDR4 memory, the ThinkCentre M715q Thin Client delivers the power to meet your business needs now—and in the future.



More Than a PC

The Windows 10 IoT-powered ThinkCentre M715q Thin Client can do everything a full-fledged PC can do—from data analytics to video conferencing. And by enabling you to access files, apps, and services through the cloud, it gives your business more freedom and flexibility.



Intuitive and Intelligent

Included as standard with every ThinkCentre M715q Thin Client is Lenovo Thin Client Manager. This intelligent software is an invaluable tool for managing thin clients. Whether it's upgrading desktop or assigning users roles, you can do so quickly and easily—all from one place.



Go Green, Save Green

The ThinkCentre M715q Thin Client is certified to run industry-leading desktop and app virtualization software, including Citrix, Citrix HDX, and VMware Horizon. By running multiple virtual machines on a single physical machine, your business can reap many benefits, including a smaller energy footprint and cost savings.



Here to Help

Machine Type Model, or MTM. Custom to Order, or CTO. Just some of the ways that we can help to ensure that you purchase the right thin clients for your business. We can also help you with roll-out, maintenance, and further down the line, refresh.



THE LENOVO™ THINKCENTRE M715q Thin Client IS BEST SUITED FOR?

- 1** Progressive IT decision makers who recognise technological performance as integral to empowering their business
- 2** Busy professionals requiring desktop-standard performance with plenty of horsepower and upgrade options
- 3** IT managers who value the agility to extend and replace components as resource requirements evolve



Lenovo™ ThinkCentre M715q Thin Client

WHAT'S IN A THINKCENTRE®



Lowest failure rates in the industry¹



The highest % of recycled materials



Intelligent Cooling Engine (ICE)



Gold plated pins² for signal quality

SPECIFICATIONS

Lenovo™ ThinkCentre M715q Thin Client

PERFORMANCE

Operating System

Windows 10 IoT

Windows Embedded Standard Version 7 (WE S 7)

Lenovo™ Terminal Operating System

(LeTOS™)

Processor

AMD PRO A6-8570E 3.0GHz/2C/1M 35W AM4;

AMD PRO A10-8770E 2.8GHz/4C/2M 35W AM4;

Storage

32G SSD for Windows 10 IoT/WES7/LeTOS

128G SSD for Windows 10 IoT/WES7/LeTOS

Memory

4G DDR4 SODIMM 2400MHz

8G DDR4 SODIMM 2400MHz

Power Adapter

65W 88% Adapter

Graphics

AMD Radeon™ R7 Graphics

AMD Radeon™ R5 Graphics

SECURITY

TPM 2.0

Kensington Lock

Padlock

Chassis Intrusion Switch

CONNECTIVITY

Front I/O

2x USB 3.0

1x Headphone/ microphone combo jack (stereo, 3.5 mm)

Rear I/O

1x USB 3.0

3x USB 2.0

Ethernet

2x Display Port

1x Optional Port (VGA, 3rd DP, HDMI or serial)

1x Headphone

SLOTS

32G and 128G SSD

Security Slot

WiFi & Bluetooth*

Optional

DESIGN

Dimensions

179 mm x 34,5 mm x 182.9 mm

Weight

1,32 KG

Ease of Use (Too-less)

Yes

GREEN CERTIFICATION

Energy Star 6.1

EPEAT Gold certified

GreenGuard

RECOMMENDED SERVICES

Lenovo offers a comprehensive portfolio of services to support and protect your investment. Succeed with substance and let Lenovo Service support you all the way.

PRIORITY TECHNICAL SUPPORT

Makes your priority, our priority. 24 x 7 priority call routing to advanced-level technicians, electronic incident tracking, and escalation management services.

WARRANTY UPGRADES—ON-SITE AND NEXT BUSINESS DAY

Maximizes PC uptime and productivity by providing convenient and fast repair service at your place of business.

WARRANTY EXTENSIONS (1-3 YEARS TOTAL DURATION)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment, and lower the cost of ownership over time.

ACCIDENTAL DAMAGE PROTECTION

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops, or damage to the integrated screen.

KEEP YOUR DRIVE

Retain your drive if it should happen to fail, giving you the peace of mind of knowing that your valuable data is secure.

ASSET TAGGING

Systems come equipped with a professional, flexible asset tag based on your exact specifications. PCs are easily identifiable and trackable right out of the box.



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. AMD, the AMD Arrow logo and combinations thereof are trademarks of Advanced Micro Devices, Inc. in the United States and/or other jurisdictions. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2017 Lenovo. All rights reserved.

Lenovo™