




SOCKETSCAN® S860



2D/1D Imager

Passport Reader

OCR-A / OCR-B / MICR E13B

Thin, Small & Light 2D/1D Scanner & Passport Reader - Great for one-handed solutions


The Socket Mobile S860 is a fast-scanning 2D/1D imager barcode scanner and passport reader with Bluetooth® wireless technology. The scanner virtually captures any 1D/2D barcodes in milliseconds. Small, thin and easy to use, the scanner is optimized for attaching to mobile devices, enabling one-handed operation. Merchants can scan barcodes of products and the passports of consumers with one scanner. Scanning barcodes printed on labels or displayed on device screens, it reads all the most popular 2D barcodes and MRZ/passports, perfect for the travel industry retail point of sale, inventory management, sales order entry, field service, and other mobile business applications. Approximately the same size as a credit card, measuring less than ½ inch (1.27cm) thick and weighing less than two ounces, the S860 is one of the smallest and lightest barcode scanners and passport readers available in the market today. The S860 slips neatly into your pocket and fits comfortably in the palm of your hand when attached to a smartphone or other mobile device.



Certified by Apple® for iOS devices (iPad®, iPhone®, iPod Touch® devices) and compatible with Android and Windows®

Features


- **Bluetooth Wireless Technology** - Connects easily to a wide range of Bluetooth enabled smartphones, tablets, notebook and desktop computers
- **Certified by Apple® for iOS devices - Guaranteed Compatibility** - With our SDK integrated in over 700+ applications, Socket Mobile scanners are one of the most natively integrated scanners available today. Socket Mobile Scanners are also 100% compatible with any application out-of-the-box in HID (keyboard emulation) mode.
- **Compatible with all Android and Windows devices and applications**
- **Scanning** - Fast 2D & 1D barcode scanning with highly visible and safe LED aimer and omni-directional ability, allowing intuitive rapid scanning. Scans OCR A&B fonts, OCR USC, OCR passport and OCR MICR (E13B) fonts.
- **Decoding Ability** - Reads damaged and poorly printed barcodes.
- **LED Aimer** - Bright, rectangular illumination field with LED dot for precise aiming.
- **Size & Weight** - Measuring less than ½ inch (1.27cm) thick and weighing less than two ounces (48g)
- **User Feedback** - With audible tones, vibrations and Bluetooth indicators
- **Long-Lasting Battery** - Power to last a full work day, up to 10 hours
- **One-Handed Operation** - Attachable clip included
- **Protective Material** - Made with antimicrobial material for protection against potentially harmful bacteria
- **Application Integration** - Socket Mobile's Capture SDK enables easy integration in your applications to improve business productivity with fast, efficient and reliable data transfer over Bluetooth wireless technology
- **Accessories** - DuraCase, lanyard and wrist strap available (sold separately)
- **Designed and Assembled in the USA**
- **Developer Support Available** - The Capture SDK is available with subscription
- **1-Year Warranty**



Weight Mass:
1.7 oz
47.5 g



- (1) S860, 2D/1D Imager Barcode Scanner and Passport Reader
- (1) Micro USB Charging Cable
- (1) Universal Klip Case
- (1) Get Started Insert



Socket Mobile Companion
Download for Free!

OPTIONAL ACCESSORIES


DuraCase - Only
Apple® iPod touch® for 5th/6th gen
Samsung J3/J5
Samsung Galaxy S7



DuraCase Charging Adapter



DuraCase & Charging Dock
Apple® iPod touch® for 5th/6th generation
Samsung J3/J5
Samsung Galaxy S7



DuraCase Charging Dock




Holster



DuraCase 6 Multi-Bay Charger



DuraCase 6 Multi-Bay Charger
AC Power Cord



Klip Cases
iPhone SE/5/5s
iPhone 5c
iPod touch(5th generation)
Samsung Galaxy S4



Wrist Strap or Lanyard



Technology: 2D/1D Barcode Imager & OCR character reader
 Light Source Aimer: Hyper red 660 NM (nanometer) LED 6/0 NM LED

SCANNING PERFORMANCE


Default Barcode Symbologies: 1D Symbologies: Codabar, Code 39, Code 93, Code 128, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, UPC A, UPC EO
 2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, PDF417
 Postal Codes: Australia Post
 OCR Type Face: OCR Passport - 2 lines

Supported Barcode Symbologies: 1D Symbologies: Bookland EAN, Chinese 2 of 5, Codabar, Code 11, Code 39, Code 93, Code 128, Composite CC-A/B, Composite CC-C, Composite TLC, Discrete 2 of 5, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, ISSN EAN, Matrix 2 of 5, MSI, UPC/EAN/JAN, UPC A, UPC EO
 2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, MicroQR, PDF417, QR Code
 Postal Codes: Australia Post, Han Xin, Japan Postal, KIX Code, Maxicode, Netherlands, UPU FICS Posta, US Planet, US Postnet, USPS 4CB/One Code/Intelligent Mail
 OCR Type Face: OCR-A, OCR-B, MICR-BBB, US currency serial number

Scan Angle: Horizontal: 42° Vertical: 28°

Sensor Resolution: 1280 x 800 pixels

Print Contrast: Down to 25%



4.6 to 76.2 cm (1.8 to 30.0 in.) Depends on barcode size, symbology, label media, ratio, scan angle

Decode Ranges:

	Near	Far
4 mil Code 39	3.3 in/8.4 cm	8.8 in/22.4 cm
5 mil Code 128	2.8 in/7.1 cm	8.2 in/20.8 cm
5 mil Code 39	2.0 in/5.08 cm	13.5 in/34.3 cm
5 mil PDF	3.1 in/7.9cm	8.4 in/21.3 cm
10 mil Data Matrix	2.9 in/7.4 cm	10.1 in/25.7 cm
100% UPC A	1.8 in/4.6 cm*	26.0 in/66.0 cm
20 mil Code 39	2.0 in/5.08 cm*	30.0 in/76.2 cm

Battery:	Lithium ion rechargeable battery
Charge Time:	4 Hours
Battery Life: Per Full Charge:	Standby time: 25 hours Active Scan Time: 34,000 scans within 3 hours (based on 2 scans every 1 second) or 9,000 scans within 10 hours (based on 1 scan every 4 seconds)
Note:	Battery life varies depending on ambient temperature, ambient light, age of battery, etc.

WARRANTY

Scanner:	Standard one year limited warranty
Accessories:	90 days
Extended Warranty: (sold separately)	www.socketmobile.com/socketcare



COMMON USES

Retail	Hospitality	Point of Sale
Logistics	Life Sciences	Automotive
Healthcare	Travel	

BLUETOOTH (WIRELESS CONNECTION)

Bluetooth Radio:	Class 2 Bluetooth, version 2.1 + EDR (Enhanced Data Rates) with 56-bit data encryption
Bluetooth Range:	Up to 10 m (33 ft.) depending on environment, range limit is usually due to the Host Device (phone, tablet or notebook)
Bluetooth Profiles:	Basic Mode - Human Interface Device (HID)*, Application Mode - Serial Port Profile (SPP) and Application Mode - MFi-SPP. Some Operating Systems or smartphone/tablet models may support only one profile. <i>*By default, the scanner is set to Basic Mode (HID).</i>

USER ENVIRONMENT

Ambient Light:	From 0 to 100,000 lux From pitch black to direct sun light
Operating Temperature:	+32 to +122 °F (0 to +50 °C)
Storage Temperature:	-22 to +158 °F (-30 to +70 °C)
Relative Humidity:	5% to 95% (non condensing)
Sealing:	IP40
Drop Specifications:	Multiple drops to vinyl covered concrete at 3 feet or 1 meter

OPERATING SYSTEM COMPATIBILITY

Android OS: Basic Mode (HID)* & Application Mode (SPP)	Mac OS: Basic Mode (HID)* only
Apple iOS: Basic Mode (HID)* & Application Mode (MFi-SPP)	Windows: 10, 8, and 7: Basic Mode (HID)* & Application Mode (SPP)
Compatible with devices supporting Basic Mode (HID)* protocol	
<i>*By default the scanner is in Basic Mode (HID).</i>	

Certified by Apple® for iOS devices (iPad®, iPhone®, iPod Touch®) and compatible with Android and Windows®.



Electrical Safety:	Certified to IEC 60950-1, UL 60950-1, CAN/CSA C22.2
Environmental:	RoHS compliant
EMI / RFI:	FCC Part 15 Class C, RSS 210, iCES 003, C-Tick, CISPR 22, CE EN55022, EN55024, TELEC
LED Safety:	IEC 60825-1, EN 60825-1 FCC: T9J-RN42 IC: 6514A -RN42 Telec ID: 201-125709



socketmobile.com

Toll-Free: +1 800 552 3300 (USA/Canada)
France: +33 970 462 241
Latin America: +1 510 933 3153

sales@socketmobile.com

Asia Pacific: +1 510 933 3122
Germany: +49 9401 5299 052
Switzerland: +41 62 834 07 80

EMEA & Russia: +41 62 834 0780
Japan: +8190 9808 0518
UK/Ireland/South Africa: +44 (0) 1252 761403
+44 7787 112109