



MS622de with optional trays



MS620 Series

Reliability. Security. Productivity.



The MS622de is a Class A device according to the FCC Rules and international electromagnetic emissions standards. This device is not intended for use in residential or domestic environments due to potential interference to radio communications. The MS621dn is a Class B device.

Lexmark MS620 Series

The MS620 series prints up to 50 pages per minute* and features superior print quality, enhanced security and built-in durability. Maximize printing performance with a 1-GHz dual-core processor and up to 1 GB of memory (MS622de), while monitoring and interacting via a 2.4-inch color LCD (MS621dn) or tablet-like 4.3-inch touch screen with e-Task (MS622de).



Get more done


- ▶ Get up to 50-page-per-minute printing.
- ▶ Tackle your printing workload with the power of a 1-GHz dual-core processor with up to 1 GB of memory and optional hard drive (for MS622de).
- ▶ Easily configure and monitor vital system information via a 2.4-inch color LCD (MS621dn).
- ▶ Intuitive 4.3-inch color touch screen (MS622de) offers smooth, tablet-like interaction.

Ready when you are

- ▶ Long-life fuser and imaging components extend uptime.
- ▶ Unison™ Toner replacement cartridges deliver up to 25,000 pages** of high-quality printing.
- ▶ Maximum input capacity of 2300 pages means fewer interruptions.
- ▶ Durable metal frame is designed for longevity.

Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—on the document, the device, over the network, and everywhere in between.
- ▶ A range of embedded features harden device against attacks.
- ▶ Go beyond standard Confidential Print with optional security solutions like Print Release and Lexmark Secure Document Monitor.
- ▶ Keypoint Intelligence - Buyers Lab honored Lexmark with a prestigious BLI PaceSetter award for Document Imaging Security***.



Built for planet earth


- ▶ Energy management features reduce power consumption in active use or sleep mode.
- ▶ Standard two-sided printing saves paper.
- ▶ Use of post-consumer recycled content in manufacturing saves natural resources.
- ▶ Device is rated EPEAT® Silver and ENERGY STAR® certified.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).

*Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

**Average standard page yield value declared in accordance with ISO/IEC 19752.

***Award based on North America data.

Lexmark MS620 Series



- 1 Printer with 2.4-inch (6 cm) color display
11.9 x 15.7 x 14.7 inches
303 x 399 x 374 mm
- 3 550-sheet tray
5 x 15.7 x 14.7 inches
126 x 389 x 374 mm

- 2 Printer with 4.3-inch (10.9 cm) color touch screen
11.9 x 15.7 x 14.7 inches
303 x 399 x 374 mm
- 4 250-sheet tray
3.7 x 15.7 x 14.7 inches
95 x 389 x 374 mm

Standard
 Optional
 Supports up to three optional trays.

© 2018 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. ENERGY STAR® is a U.S. registered mark. EPEAT® is a trademark of EPEAT, Inc. in the United States and other countries. Google Cloud Print is a trademark of Google, Inc. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are trademarks, service marks, and certification marks of Mopria Alliance, Inc. in the United States and other countries. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

Product specifications	Lexmark MS621dn	Lexmark MS622de
Printing		
Display	2.4-inch (60 mm) Color LCD display	Lexmark e-Task 4.3-inch (10.9 cm) color touch screen
Print Speed: Up to ⁴	Black: 50 ppm	
Time to First Page: As fast as	Black: 6 seconds	
Print Resolution	Black: 600 x 600 dpi, 2400 Image Quality, 1200 x 1200 dpi, 1200 Image Quality	
Memory / Processor	Standard: 512 MB / Maximum: 512 MB / Dual Core, 1000 MHz	Standard: 1024 MB / Maximum: 1024 MB / Dual Core, 1000 MHz
Hard Disk	Not Available	Option available
Recommended Monthly Page Volume ²	2000 - 20000 pages	
Maximum Monthly Duty Cycle: Up to ³	175000 pages per month	
Supplies⁶		
Laser Cartridge Yields (up to) ¹	25,000-page Ultra High Yield Cartridge, 6,000-page Cartridge, 20,000-page Extra High Yield Cartridge, 15,000-page High Yield Cartridge	6,000-page Cartridge, 25,000-page Ultra High Yield Cartridge, 20,000-page Extra High Yield Cartridge, 15,000-page Black High Yield Cartridge
Imaging Unit Estimated Yield: Up to ⁷	60000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage	
Cartridge(s) Shipping with Product ¹	6,000-page Starter Return Program Toner Cartridge	
Paper Handling		
Included Paper Handling	250-Sheet Output Bin, Integrated Duplex, 100-Sheet Multipurpose Feeder, 550-Sheet Input	
Optional Paper Handling	550-Sheet Lockable Tray, 550-Sheet Tray, 250-Sheet Tray	
Paper Input Capacity: Up to	Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 2300 pages 20 lb or 75 gsm bond	
Paper Output Capacity: Up to	Standard: 250 pages 20 lb or 75 gsm bond / Maximum: 250 pages 20 lb or 75 gsm bond	
Media Types Supported	Refer to the Card Stock & Label Guide., Transparencies, Plain Paper, Paper Labels, Envelopes, Card Stock	
Media Sizes Supported	A6, Oficio, Universal, Statement, Letter, Legal, JIS-B5, Folio, Executive, DL Envelope, A5, A4, 9 Envelope, 7 3/4 Envelope, 10 Envelope	
General Information⁵		
Standard Ports	Front USB 2.0 Specification Hi-Speed Certified port (Type A), Gigabit Ethernet (10/100/1000), USB 2.0 Specification Hi-Speed Certified (Type B)	Rear USB 2.0 Specification Hi-Speed Certified Port (Type A), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Gigabit Ethernet (10/100/1000), USB 2.0 Specification Hi-Speed Certified (Type B), One Internal Card Slot
Optional Network Ports / Optional Local Ports	Marknet N8372 WiFi Option, Marknet N8370 WiFi Option	Marknet N8372 WiFi Option, Marknet N8370 WiFi Option, MarkNet N8230 Fiber Ethernet Print Server / Internal 1284-B Bidirectional Parallel, Internal RS-232C serial
Noise Level: Operating	Print: 56 dBA	
Specified Operating Environment	Altitude: 0 - 5000 Meters (16,404 Feet), Temperature: 10 to 32°C (50 to 90°F), Humidity: 8 to 80% Relative Humidity	
Limited Warranty - See Statement of Limited Warranty	1-Year Exchange, Return-to-Base Service	
Size (in. - H x W x D) / Weight (lb.)	11.9 x 15.7 x 14.7 in. / 34.8 lb.	11.9 x 15.7 x 14.7 in. / 35.5 lb.

All information in this brochure is subject to change without notice. Lexmark is not liable for any errors or omissions.

The MS622de is a Class A device according to the FCC Rules and international electromagnetic emissions standards. This device is not intended for use in residential or domestic environments due to potential interference to radio communications. The MS621dn is a Class B device.

¹Average standard page yield value declared in accordance with ISO/IEC 19752. ²"Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³"Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds. ⁵Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details. ⁶Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁷Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity.