

OVERVIEW

Upgradeable Metered rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet while delivering a view of real-time view of power usage from a local LED display.

Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform metered rPDUs to monitored rPDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.



Part #: UI10016L

Model Number: MU01D1R0-10L137-2C20A9H00-S

Category: Metered

Sub Category: Upgradeable

Power Configuration: 16A OR 20A, 120V OR 208V OR 230V, 1.9kW or 3.3kW or 3.6kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary:

rPDU, Metered Upgradeable, 16A OR 20A, 120V OR 208V OR 230V, 1.9kW or 3.3kW or 3.6kW, Horizontal, (10) Locking IEC C13, C20, Black Powder Coat.

Monitoring:

Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Vertiv rPDU Scanner app.

Plug Form:

C20

Receptacle:Locking IEC C13
(Quantity: 10)**Chassis Color Options:**

To discuss color options, contact your local sales representative.

Product Specification and Options**System Features**

Monitoring	Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Vertiv rPDU Scanner app.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
VLC Support	Yes
Quantity Of Inputs	1
Voltage	100-240V
Current	16A or 20A
VA per Input (Load Capacity)	1.9kW (120V), 3.3kW (208V), 3.6kW (230V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Scrolling / Rotatable Digital Display	Yes
Power Entry Location	Left Rear
Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Rear	10
- U-Lock Color ID	1 Circuit = Orange
- Style	Individual
- Voltage per Receptacle/Socket	100-120V or 208-240V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years

Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	Complies with IEC 60950-1 (CB Certificate Available)
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	UL & c-UL Listed 60950
Certification/Agency Approvals	China RoHS
Certification/Agency Approvals	C _μ Mark
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in / 44mm x 432mm x 216mm
Shipped Weight	10lbs (4.54kg)