

I10056L

Model Number: MN01D4W1-36PT68-3TL6A0A10-S
Category: Metered
Sub Category: Upgradeable
Power Configuration: 30A, 208V, 4.9kW
Physical Configuration: 72in / 1829mm, Vertical



Description: The I10056L provides real-time power metrics to help prevent overloads and safely optimize load levels. Using Visible Light Communication (VLC) technology, I10056L optically transmits power usage data from its LED display to a handheld device over the Geist Mobile App, presenting comprehensive real-time power usage data down to the phase and circuit levels. With the Geists Upgradeable hot-swap technology, users may easily transform Metered PDUs to Monitored by replacing the Interchangeable Monitoring Device (IMD) module, without causing any interruption.

Product Summary: I10056L - Metered, Upgradeable, 30A, 208V, Vertical, (30) Locking IEC C13, (6) Locking IEC C19, breaker, 10 ft power cord with L6-30P, Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app. Black Powder Coat.


Monitoring: Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app.

Plug Form:



L6-30P

Receptacle:



Locking IEC C13
(Quantity: 30)



Locking IEC C19
(Quantity: 6)

Chassis Colors Options:

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

| | |
|---|--|
| Monitoring | Input and Breaker level current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Geist app. |
| Monitoring Level 1 | Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements |
| Monitoring Level 2 | Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy |
| VLC Support | Yes |
| Quantity Of Inputs | 1 |
| Voltage | 208V |
| Current | 30A |
| VA per Input (Load Capacity) | 4.9kW |
| Frequency | 50/60Hz |
| Over Current Protection | (2) 20A Double Pole Magnetic Breakers |
| Switch | Breaker/Switch Combination |
| Scrolling / Rotatable Digital Display | Yes |
| Power Cable Wire Gauge | 10/3 |
| Power Cable Length | 10ft |
| Power Entry Location | Bottom Front |
| Plug Type | NEMA L6-30P Twistlock |
| Combined Total Receptacle/Socket Quantity | 36 |
| Receptacle/Socket Type #1 | U-Lock IEC C13 |
| - Quantity on Face | 30 |
| - Quantity per Breaker | 15 |
| - U-Lock Color ID | 2 Circuit = Orange, Green |
| - Style | Individual |
| - Voltage per Receptacle/Socket | 208V |
| Receptacle/Socket Type #2 | U-Lock IEC C19 |
| - Quantity on Face | 6 |
| - Quantity per Breaker | 3 |
| - U-Lock Color ID | 2 Circuit = Orange, Green |
| - Style | Individual |
| - Voltage per Receptacle/Socket | 208V |
| Internal RMS Voltage Sensor | Yes |
| Internal RMS Current Sensor | Yes |
| Maximum Operating Temperature | 60C / 140F |
| Heavy Steel - Powder Coat Finish | Black |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

| | |
|---|---|
| Configuration | 72in / 1829mm Vertical Rackmount |
| 7938 Vertical Mounting Bracket Kit | Yes |
| Toolless Mounting Hardware - Center to Center Spacing | 61.25in and 64.75in |
| Made in the USA | Yes |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | FCC Part 15 Class A Conformance |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (LxWxD) | 72in x 2in x 2in |
| Shipped Weight | 16lbs (7.26kg) |

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com