



ST900U STANDBY UPS SYSTEM

Offers significant energy savings, battery backup and surge protection.

The CyberPower ST900U uninterruptible power supply (UPS) safeguards a home office PC and other electronics (modem, wireless router, gaming console, and cablebox/DVR) from surges, spikes, sags, brownouts and other power abnormalities. Two USB charging ports keep phones and tablets operating during a power outage, and PowerPanel® Personal management software makes it easy to control and monitor your UPS.

A Three-Year Warranty ensures that this UPS has passed our highest quality standards in design, assembly, material or workmanship and further protection is offered by a \$125,000 Connected Equipment Guarantee.



TYPICAL APPLICATIONS

- Desktop Computers
- Personal Electronics

FEATURES

- 900 VA/500 W
- 12 Standard Outlets
- Standby Topology
- Full-time Surge Protection and Battery Backup
- Three-Year Warranty

SPECIFICATIONS

GENERAL	
UPS Topology	Standby
Energy Saving	Yes
ENERGY STAR® Qualified	Yes
INPUT	
Voltage	96 - 140 VAC
Frequency Range	47 - 63 Hz
Circuit Breaker	15 A
Plug Type	NEMA 5-15P
Cord Length	5 ft
OUTPUT	
VA	900 VA
Watts	500 W
On Battery Voltage	120 VAC ± 5%
On Battery Frequency	50/60 Hz ± 1%
On Battery Waveform	Simulated Sine Wave

OUTPUT CONT.	
Outlet Type	NEMA 5-15R
Outlets - Total	12
Outlets - Battery & Surge Protected	6
Outlets - Surge-Only Protect	6
Outlets - Widely Spaced	4
Overload Protection	Internal Circuitry Limiting Circuit Breaker
USB Charging Ports	2 @ 2.1A Shared
BATTERY	
Runtime at Half Load (min)	7.5
Runtime at Full Load (min)	2
Battery Type	Sealed Lead-Acid
Battery Size	12V/7.2Ah
Battery Quantity	1
User Replaceable	Yes

ST900U STANDBY UPS SYSTEM



SPECIFICATIONS CONT.

BATTERY CONT.

Typical Recharge Time	8 hours
-----------------------	---------

SURGE PROTECTION & FILTERING

Surge Suppression	890
-------------------	-----

EMI/RFI Filtration	Yes
--------------------	-----

MANAGEMENT & COMMUNICATIONS

HID Compliant USB Port	Yes
------------------------	-----

Cable Management	Yes
------------------	-----

LED Indicators	Power On
----------------	----------

Audible Alarms	On Battery, Low Battery, Overload, Fault
----------------	--

Software	PowerPanel® Personal
----------	----------------------

PHYSICAL

Keyhole Mounting Slots	Yes
------------------------	-----

Dimensions (WxHxD) (in.)	12.2 × 3.1 × 7
--------------------------	----------------

Weight (lbs.)	7.7
---------------	-----

ENVIRONMENTAL

Operating Humidity	0 - 95% (non-condensing)
--------------------	--------------------------

Operating Temperature	32 - 104 °F (0 - 40 °C)
-----------------------	-------------------------

CERTIFICATIONS

Safety	UL1778, cUL, FCC DOC Class B, CEC
--------	-----------------------------------

Environmental	RoHS Compliant
---------------	----------------

WARRANTY

Product Warranty	Three-Year Limited
------------------	--------------------

Connected Equipment Guarantee	Lifetime
-------------------------------	----------

CEG Amount	\$125,000
------------	-----------