

UI10014L

Model Number: MU01X1R0-10L137-2C20A9H00-S
Category: Basic
Sub Category: Upgradeable
Power Configuration: 16A OR 20A, 120V OR 208V OR 230V, 1.9kW or 3.3kW or 3.6kW
Physical Configuration: 19in / 483mm, Horizontal



Description: UI10014L provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

Product Summary: UI10014L - Basic, Upgradeable, 16A OR 20A, 100-120V OR 208-240V, Horizontal, (10) Locking IEC C13, C20, No Monitoring (Upgradeable with IMD module). Black Powder Coat.


Monitoring: No Monitoring (Upgradeable with IMD module)

Plug Form:



C20

Receptacle:



Locking IEC C13
(Quantity: 10)

Chassis Colors Options:



Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	100-240V
Current	16A or 20A
VA per Input (Load Capacity)	1.9kW (120V), 3.3kW (208V), 3.6kW (230V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Entry Location	Left Rear
Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Rear	10
- U-Lock Color ID	1 Circuit = Orange
- Style	Individual
- Voltage per Receptacle/Socket	100-120V or 208-240V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	Complies with IEC 60950-1 (CB Certificate Available)
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	UL & c-UL Listed 60950
Certification/Agency Approvals	China RoHS
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in / 44mm x 432mm x 216mm
Shipped Weight	12lbs (5.44kg)